

Technical drawing of a mechanical part showing a side view and a cross-section.

Side View Dimensions:

- Top diameter: $\pm .002$ [± 0.05] .050 [1.27] DIA. TYP.
- Second diameter from top: $\pm .002$ [± 0.05] .038 [0.97] DIA. TYP.
- Third diameter from top: .186 [4.72]
- Fourth diameter from top: .104 [2.64]
- Fifth diameter from top: .022 [0.56]
- Sixth diameter from top: .082 [2.08]
- Seventh diameter from top: .164 [4.17]
- Eighth diameter from top: $\pm .002$ [± 0.05] .072 [1.83] DIA.
- Ninth diameter from top: $\pm .002$ [± 0.05] .093 [2.36] DIA.

Other Dimensions:

- Length of the top section: .020 [0.51] TYP.
- Length of the section below the fourth diameter: L

Cross-section: A circular profile with concentric circles.

Table:

PART

PART NO.	'L' DIM.
1583-1	.051 [1.30]
1583-2	.082 [2.08]
1583-3	.113 [2.87]
1583-4	.145 [3.68]

ASTORIA, N.Y. 11105-2017

TERMINAL

BRASS

TIN PLATE

BOONE

2.12.02

LN

SCALE

TOLERANCES

INCH	[MM]
------	------

DECIMAL	$\pm .005$	$[\pm 0.15]$
---------	------------	--------------

ANGULAR $\pm 1^\circ$
UNLESS OTHERWISE SPECIFIED

CODE

DWG NO.	
---------	--

DATE _____

DESCRIPTION

REV.

1583-

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Keystone Electronics:](#)

[1583-3](#)