






ACTUAL SIZE



NOTE:

1. SHELL: MAT'L- PHOSPHOR BRONZE
FINISH- TIN PLATE, OVER NICKEL PLATE
2. INSULATOR: MAT'L- LCP, UL94V-0
3. CONTACT: MAT'L- PHOSPHOR BRONZE
FINISH ON CONTACT AREAS-
GOLD PLATE, OVER NICKEL PLATE
FINISH ON SOLDER TAIL-
TIN PLATE, OVER NICKEL PLATE

4. ELECTRICAL SPECIFICATIONS:

RATED VOLTAGE- 30V AC (rms)
CONTACT CURRENT RATING: 1A MAX.
CONTACT CURRENT RESISTANCE: 30 millioms MAX,
INSULATION RESISTANCE: 1000 Megohms Min.
DIELECTRIC WITHSTANDING: .500V AC
OPERATING TEMPERATURE: 32° [0°C] TO 104° [40°C]

KEYSTONE ELECTRONICS CORP.

www.keyelco.com • ASTORIA, N.Y. 11105-2017 • Tel (718) 956-8900

PART NAME

IEEE 1394 'FIREWIRE' HORIZONTAL SOCKET

MATERIAL

AS NOTED

FINISH

AS NOTED

DRN BY

BOONE

DATE

7.1.99

APP'D

RH

SCALE

3X

TOLERANCES

INCH

[MM]

DECIMAL

± .010 [± 0.25]

ANGULAR

± 1°

UNLESS OTHERWISE SPECIFIED

CODE

C

DWG NO.

929

4.19.24	CHANGE AS PER PCN 24-026	C
5.19.16	CHANGE AS PER ECN 16-059	B
6.7.05	CHANGE AS PER ECN 05-031	A
DATE	DESCRIPTION	REV.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Keystone Electronics:](#)

[929](#)