

NOTES:

TAPE AND REEL SPECIFICATIONS:

1. TAPE:

MAT'L - ALL CONDUCTIVE POLYSTYRENE CARRIER

ANSI/EIA-481 STANDARD

.945 [24.0] WIDE; .630 [16.0] PITCH

2. REEL:

15.0 [380.8] DIA. 1000 PIECES OF

PART NO. 934 PER REEL.






3. MYLAR TAPE ADDED TO

TOP SURFACE OF EACH PART

5.05.16	CHANGE AS PER ECN 16-052	C
7.09.12	CHANGE AS PER ECN 12-084	B
12.01.11	CHANGE AS PER ECN 11-160	A
DATE	DESCRIPTION	REV.

KEYSTONE ELECTRONICS CORP.			
www.keyelco.com • ASTORIA, N.Y. 11105-2017 • Tel (718) 956-8900			
PART NAME			
USB MINI SOCKET ON TAPE			
MATERIAL			
AS NOTED			
FINISH		DRN BY	DATE
AS NOTED		BOONE	12.19.06
		APP'D	SCALE
		LN	1X
TOLERANCES	INCH [MM]	CODE	DWG NO.
DECIMAL	±.015 [±0.38]	C	
ANGULAR	± 1°		
UNLESS OTHERWISE SPECIFIED			
934TR			

DATE	DESCRIPTION	REV.
5.31.11	CHANGE AS PER ECN 11-075	A
3.21.16	CHANGE AS PER ECN 16-039	B



MOUNTING DETAIL

Notes:

- Shell: Mat'l: Brass,
Finish: Nickel Plate
- Insulator: Mat'l: LCP
- Contacts: Mat'l: Phosphor Bronze
- Finish: Gold Plate over Nickel on contact area.
Tin Plate over nickel on solder Tail.

Electrical Specifications

- Contact Resistance: 50 milliohms Max.
- Insulation Resistance: 500 Mega Ω min.
- Dielectric Voltage: 100V AC
- max. current : 1 Amp



ACTUAL SIZE

KEYSTONE ELECTRONICS CORP.			
www.keyelco.com • ASTORIA, N.Y. 11105-2017 • Tel (718) 956-8900			
PART NAME			
USB MINI TYPE HORIZONTAL SOCKET			
MATERIAL			
AS NOTED			
FINISH		DRN BY	DATE
AS NOTED		NT	12.17.08
TOLERANCES		APPD	SCALE
INCH [MM]		LN	5X
DECIMAL $\pm .010$ [± 0.25]		CODE	
ANGULAR $\pm 1^\circ$		C	
UNLESS OTHERWISE SPECIFIED		DWG NO.	
		934	

THIS DOCUMENT IS THE PROPERTY OF KEYSTONE ELECTRONICS CORP. AND SHALL NOT BE REPRODUCED, DISTRIBUTED OR USED AS A BASIS FOR MANUFACTURE WITHOUT PRIOR WRITTEN PERMISSION FROM KEYSTONE ELECTRONICS CORP.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Keystone Electronics:](#)

[934TR](#)