





THIS DOCUMENT IS THE PROPERTY OF  
KEYSTONE ELECTRONICS CORP. AND  
SHALL NOT BE REPRODUCED, DISTRIBUTED  
OR USED AS A BASIS FOR MANUFACTURE  
WITHOUT PRIOR WRITTEN PERMISSION  
FROM KEYSTONE ELECTRONICS CORP.

**ACTUAL SIZE**



**NOTE:**

**1. PLASTIC HOUSING:**

MAT'L- PBT

RATED UL 94V-0, COLOR- BLACK

**2. CONTACT: MAT'L PHOSPHOR BRONZE Ø0.18 [0.46]**

FINISH- GOLD PLATE, OVER NICKEL

**3. DIELECTRIC WITHSTANDING VOLTAGE:**

1000 VAC FOR 1 MIN.

**4. STORAGE TEMPERATURE:**

-40°F (-40°C) TO +176°F (+85°C)

**OPERATION TEMPERATURE:**

-4°F (-20°C) TO 167°F (+75°C)

**5. VOLTAGE RATING: 125 VAC Rms.**

CURRENT RATING- 1.5 Amps

CONTACT RESISTANCE- 30 mΩ MAX.

INSULATION RESISTANCE- 500 MΩ MIN. @500 VDC

DIELECTRIC STRENGTH: 1000 VAC Rms 60Hz. 1Min.

1.08.21 UPDATE PER NEW TOOLING  
CHANGE AS PER ECN 21-015

A

KEYSTONE ELECTRONICS CORP.			
www.keyelco.com • NEW HYDE PARK, NY 11040 • Tel (516) 328-7500			
PART NAME			
MODULAR KEYSTONE JACK, 8P8C			
MATERIAL			
AS NOTED			
FINISH		DRN BY	DATE
AS NOTED		NT	4.08.15
		APP'D	SCALE
		RH	2.5X
TOLERANCES	INCH [MM]	CODE	DWG NO.
DECIMAL	± .005 [± 0.13]	C	
ANGULAR	± 1°		
UNLESS OTHERWISE SPECIFIED			

**943**

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Keystone Electronics:](#)

[943](#)