

## CLAUDIA-90

~90° wide beam

### TECHNICAL SPECIFICATIONS:

Dimensions	279.3 x 29.3 mm
Height	8.1 mm
Fastening	clips
ROHS compliant	yes ⓘ


### MATERIAL SPECIFICATIONS:

Component	Type	Material	Colour	Finish
CLAUDIA-90	Linear lens	PMMA	clear	



### ORDERING INFORMATION:

Component	Qty in box	MOQ	MPQ	Box weight (kg)
C16613_CLAUDIA-90 » Box size: 400 x 300 x 300 mm	228	96	12	6.6



See also our general installation guide: [www.ledil.com/installation\\_guide](http://www.ledil.com/installation_guide)



### PHOTOMETRIC DATA (MEASURED):





LED J Series 2835  
FWHM / FWTM 72.0° / 99.0°  
Efficiency 94 %  
Peak intensity 0.7 cd/lm  
LEDs/each optic 2  
Light colour White  
Required components:




LED LUXEON 3030 2D (Square LES)  
FWHM / FWTM 74.0° / 99.0°  
Efficiency 91 %  
Peak intensity 0.7 cd/lm  
LEDs/each optic 2  
Light colour White  
Required components:



LED LinLED 280x26mm 1300lm 840 2C 42V Opt G1  
FWHM / FWTM 76.5° / 100.0°  
Efficiency 95 %  
Peak intensity 0.6 cd/lm  
LEDs/each optic 1  
Light colour White  
Required components:





LED Duris S5 (2 chip)  
FWHM / FWTM 77.0° / 99.0°  
Efficiency 94 %  
Peak intensity 0.6 cd/lm  
LEDs/each optic 2  
Light colour White  
Required components:



## PHOTOMETRIC DATA (MEASURED):

### SAMSUNG


LED LM301B  
FWHM / FWTM 81.0° / 103.0°  
Efficiency 94 %  
Peak intensity 0.6 cd/lm  
LEDs/each optic 2  
Light colour Tunable White  
Required components:




### PHOTOMETRIC DATA (SIMULATED):




LED J Series 2835  
FWHM / FWTM 81.0° / 98.0°  
Efficiency 94 %  
Peak intensity 0.7 cd/lm  
LEDs/each optic 1  
Light colour White  
Required components:




LED LUXEON 2835 Line  
FWHM / FWTM 83.0° / 100.0°  
Efficiency 94 %  
Peak intensity 0.6 cd/lm  
LEDs/each optic 1  
Light colour White  
Required components:



LED NF2x757G  
FWHM / FWTM 82.0° / 99.0°  
Efficiency 94 %  
Peak intensity 0.6 cd/lm  
LEDs/each optic 1  
Light colour White  
Required components:



LED NFMW48xA  
FWHM / FWTM 80.0° / 102.0°  
Efficiency 94 %  
Peak intensity 0.6 cd/lm  
LEDs/each optic 1  
Light colour White  
Required components:




#### PHOTOMETRIC DATA (SIMULATED):

##### OSRAM

Opto Semiconductors


LED Duris E 2835  
FWHM / FWTM 83.0° / 100.0°  
Efficiency 94 %  
Peak intensity 0.6 cd/lm  
LEDs/each optic 1  
Light colour White  
Required components:



##### OSRAM


Opto Semiconductors

LED Duris S8  
FWHM / FWTM 78.0° / 100.0°  
Efficiency 94 %  
Peak intensity 0.7 cd/lm  
LEDs/each optic 1  
Light colour White  
Required components:




##### SAMSUNG

LED LM28xB Series  
FWHM / FWTM 73.0° / 102.0°  
Efficiency 92 %  
Peak intensity 0.7 cd/lm  
LEDs/each optic 4  
Light colour White  
Required components:



##### SAMSUNG


LED LM28xB Series  
FWHM / FWTM 77.0° / 98.0°  
Efficiency 94 %  
Peak intensity 0.7 cd/lm  
LEDs/each optic 2  
Light colour White  
Required components:




### PHOTOMETRIC DATA (SIMULATED):

#### SAMSUNG

LED LM28xB Series  
FWHM / FWTM 81.0° / 98.0°  
Efficiency 94 %  
Peak intensity 0.7 cd/lm  
LEDs/each optic 1  
Light colour White  
Required components:



LED SEOUL DC 3528  
FWHM / FWTM 82.0° / 100.0°  
Efficiency 94 %  
Peak intensity 0.6 cd/lm  
LEDs/each optic 1  
Light colour White  
Required components:



### GENERAL INFORMATION:

NOTE: The typical beam angle will be changed by different color, chip size and chip position tolerance. The typical total beam angle is the full angle measured where the luminous intensity is half of the peak value.

### MATERIALS:

As part of our continuous research and improvement processes, and to ensure the best possible quality and availability of our products, LEDiL reserves the right to change material grades without notice.

### PRODUCT DATA USER AGREEMENT AND DISCLAIMER:

The measured data in the provided downloadable LEDiL Product Datasheets and Mechanical 2D-Drawings is rounded and provided as reference for planning. LEDiL Oy's optical specifications have been verified by conducting performance testing of the products in accordance with the company's quality system. The reported data are averaged results of multiple measurements with typical variation. LEDiL Oy reserves the right to without prior notification make changes and improvements to its products.

LEDiL Oy assumes neither warranty, nor guarantee nor any other liability of any kind for the contents and correctness of the provided data. The provided data has been generated with highest diligence but the provided data may in reality not represent the complete possible variation range of all intrinsic parameters. Therefore, in certain cases a deviation from the provided data could occur.

LEDiL Oy reserves the right to undertake technical changes of its products without further notification which could lead to changes in the provided data. LEDiL Oy assumes no liability of any kind for the possible deviation from any provided data or any other damage resulting from the usage of the provided data.

The user agrees to this disclaimer and user agreement with the download or usage of the provided files.

#### LEDiL Oy

Joensuunkatu 13  
FI-24240 SALO  
Finland

#### LEDiL Inc.

228 West Page Street  
Suite D  
Sycamore IL 60178  
USA

#### Ledil Optics Technology (Shenzhen) Co., Ltd.

# 405 , Block B  
Casic Motor Building  
Shenzhen 518057  
P.R.CHINA

#### Local sales and technical support

[www.ledil.com/  
where\\_to\\_buy](http://www.ledil.com/where_to_buy)

#### Shipping locations

Salo, Finland  
Hong Kong, China

#### Distribution Partners

[www.ledil.com/  
where\\_to\\_buy](http://www.ledil.com/where_to_buy)



# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Ledil:

C16613\_CLAUDIA-90