

## AMY-45-W

~36° wide beam

## SPECIFICATION:

Dimensions	Ø 45.0 mm
Height	10 mm
ROHS compliant	yes ⓘ


## MATERIALS:

Component	Type	Material	Colour	Finish
AMY-45-W	Single lens	PMMA		



## ORDERING INFORMATION:

Component	Qty in box	MOQ	MPQ	Box weight (kg)
C17792_AMY-45-W » Box size: 480 x 280 x 300 mm	1035	180	45	10.0





See also our general installation guide: [www.ledil.com/installation\\_guide](http://www.ledil.com/installation_guide)


### OPTICAL RESULTS (MEASURED):





LED V11 HD Gen 8  
FWHM / FWTM 35.0° / 62.0°  
Efficiency 87 %  
Peak intensity 1.9 cd/lm  
LEDs/each optic 1  
Light colour White  
Required components:  
Bender Wirth: 633d Hekla



LED V6 HD Gen 7  
FWHM / FWTM 36.0° / 56.0°  
Efficiency 87 %  
Peak intensity 2.1 cd/lm  
LEDs/each optic 1  
Light colour White  
Required components:  
F15255\_HEKLA-SOCKET-C





LED V9 HD Gen7  
FWHM / FWTM 35.0° / 58.0°  
Efficiency 84 %  
Peak intensity 2 cd/lm  
LEDs/each optic 1  
Light colour White  
Required components:  
F15859\_HEKLA-SOCKET-I



### CITIZEN



LED CLL02x/CLU02x (LES10)  
FWHM / FWTM 35.0° / 60.0°  
Efficiency 84 %  
Peak intensity 2 cd/lm  
LEDs/each optic 1  
Light colour White  
Required components:  
F17435\_HEKLA-G2-C





#### OPTICAL RESULTS (MEASURED):

#### CITIZEN



LED CLU700/701/702/703  
 FWHM / FWTM 36.0° / 56.0°  
 Efficiency 86 %  
 Peak intensity 2.1 cd/lm  
 LEDs/each optic 1  
 Light colour White  
 Required components:  
 F17435\_HEKLA-G2-C





LED CMA1516  
 FWHM / FWTM 35.0° / 59.0°  
 Efficiency 84 %  
 Peak intensity 2 cd/lm  
 LEDs/each optic 1  
 Light colour White  
 Required components:  
 F17436\_HEKLA-G2-D



LED CMT14xx  
 FWHM / FWTM 35.0° / 60.0°  
 Efficiency 84 %  
 Peak intensity 2 cd/lm  
 LEDs/each optic 1  
 Light colour White  
 Required components:  
 F17435\_HEKLA-G2-C





LED CMU10xx  
 FWHM / FWTM 35.0° / 61.0°  
 Efficiency 88 %  
 Peak intensity 2 cd/lm  
 LEDs/each optic 1  
 Light colour White  
 Required components:  
 BJB: 47.360.1020



### OPTICAL RESULTS (MEASURED):


#### LUMILEDS

LED LUXEON CoB 1202/1203  
FWHM / FWTM 35.0° / 59.0°  
Efficiency 83 %  
Peak intensity 2 cd/lm  
LEDs/each optic 1  
Light colour White  
Required components:  
F17437\_HEKLA-G2-H





#### LUMILEDS

LED LUXEON CoB 1202s  
FWHM / FWTM 36.0° / 57.0°  
Efficiency 87 %  
Peak intensity 2.1 cd/lm  
LEDs/each optic 1  
Light colour White  
Required components:  
F15848\_HEKLA-SOCKET-G





#### LUMILEDS

LED LUXEON CX Plus CoB M02 / M03 (Gen2)  
FWHM / FWTM 35.0° / 59.0°  
Efficiency 87 %  
Peak intensity 2 cd/lm  
LEDs/each optic 1  
Light colour White  
Required components:  
F15256\_HEKLA-SOCKET-D



#### LUMILEDS



LED LUXEON CX Plus CoB S01 (Gen2)  
FWHM / FWTM 36.0° / 56.0°  
Efficiency 88 %  
Peak intensity 2.1 cd/lm  
LEDs/each optic 1  
Light colour White  
Required components:  
F15956\_HEKLA-SOCKET-J




#### OPTICAL RESULTS (MEASURED):





LED CxM-6 (13.5x13.5)  
 FWHM / FWTM 36.0° / 56.0°  
 Efficiency 86 %  
 Peak intensity 2.1 cd/lm  
 LEDs/each optic 1  
 Light colour White  
 Required components:  
 F17435\_HEKLA-G2-C





LED CxM-9 (13.5x13.5)  
 FWHM / FWTM 35.0° / 60.0°  
 Efficiency 84 %  
 Peak intensity 2 cd/lm  
 LEDs/each optic 1  
 Light colour White  
 Required components:  
 F17435\_HEKLA-G2-C



LED COB S-Type (LES 7)  
 FWHM / FWTM 36.0° / 57.0°  
 Efficiency 87 %  
 Peak intensity 2.1 cd/lm  
 LEDs/each optic 1  
 Light colour White  
 Required components:  
 F15848\_HEKLA-SOCKET-G





LED COB T-Type  
 FWHM / FWTM 36.0° / 56.0°  
 Efficiency 87 %  
 Peak intensity 2.1 cd/lm  
 LEDs/each optic 1  
 Light colour White  
 Required components:  
 F15848\_HEKLA-SOCKET-G



### OPTICAL RESULTS (MEASURED):



#### SAMSUNG

LED LC003D / LC006D / LC009D / LC013D  
FWHM / FWTM 36.0° / 62.0°  
Efficiency 94 %  
Peak intensity 2 cd/lm  
LEDs/each optic 1  
Light colour White  
Required components:





SEOUL SEMICONDUCTOR

LED MJT COB LES 6  
FWHM / FWTM 36.0° / 56.0°  
Efficiency 86 %  
Peak intensity 2.1 cd/lm  
LEDs/each optic 1  
Light colour White  
Required components:  
F17435\_HEKLA-G2-C



SEOUL SEMICONDUCTOR


LED MJT COB LES 9.8  
FWHM / FWTM 35.0° / 60.0°  
Efficiency 84 %  
Peak intensity 2 cd/lm  
LEDs/each optic 1  
Light colour White  
Required components:  
F17435\_HEKLA-G2-C




### OPTICAL RESULTS (SIMULATED):

#### CITIZEN

LED CLU712/713  
FWHM / FWTM 34.0° / 61.0°  
Efficiency 92 %  
Peak intensity 2.1 cd/lm  
LEDs/each optic 1  
Light colour White  
Required components:  
F17438\_HEKLA-G2-I



LED CMA1825  
FWHM / FWTM 34.0° / 67.0°  
Efficiency 88 %  
Peak intensity 1.8 cd/lm  
LEDs/each optic 1  
Light colour White  
Required components:  
F15254\_HEKLA-SOCKET-B



### GENERAL INFORMATION:

NOTE: The typical beam angle will be changed by different color, chip size and chip position tolerance. The typical total beam angle is the full angle measured where the luminous intensity is half of the peak value.

Due to use of high power COB's with this product, special attention to proper thermal design is highly recommended. LEDiL has no liability for direct, indirect or consecutive damages arising from the LEDiL products being used outside of the recommended temperature range.

### MATERIALS:

As part of our continuous research and improvement processes, and to ensure the best possible quality and availability of our products, LEDiL reserves the right to change material grades without notice.

### PRODUCT DATA USER AGREEMENT AND DISCLAIMER:

The measured data in the provided downloadable LEDiL Product Datasheets and Mechanical 2D-Drawings is rounded and provided as reference for planning. LEDiL Oy's optical specifications have been verified by conducting performance testing of the products in accordance with the company's quality system. The reported data are averaged results of multiple measurements with typical variation. LEDiL Oy reserves the right to without prior notification make changes and improvements to its products.

LEDiL Oy assumes neither warranty, nor guarantee nor any other liability of any kind for the contents and correctness of the provided data. The provided data has been generated with highest diligence but the provided data may in reality not represent the complete possible variation range of all intrinsic parameters. Therefore, in certain cases a deviation from the provided data could occur.

LEDiL Oy reserves the right to undertake technical changes of its products without further notification which could lead to changes in the provided data. LEDiL Oy assumes no liability of any kind for the possible deviation from any provided data or any other damage resulting from the usage of the provided data.

The user agrees to this disclaimer and user agreement with the download or usage of the provided files.

#### LEDiL Oy

Joensuunkatu 13  
FI-24240 SALO  
Finland

#### LEDiL Inc.

228 West Page Street  
Suite D  
Sycamore IL 60178  
USA

#### Ledil Optics Technology (Shenzhen) Co., Ltd.

# 405 , Block B  
Casic Motor Building  
Shenzhen 518057  
P.R.CHINA

#### Local sales and technical support

[www.ledil.com/  
where\\_to\\_buy](http://www.ledil.com/where_to_buy)

#### Shipping locations

Salo, Finland  
Hong Kong, China

#### Distribution Partners

[www.ledil.com/  
where\\_to\\_buy](http://www.ledil.com/where_to_buy)

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Ledil:

[C17792\\_AMY-45-W](#)