



RLA Series

Features


- 85°C, standard low leakage current series
- 2,000 hours assured
- RoHS compliance



Specifications

Items	Performance																																					
Category Temperature Range	-40°C ~ +85°C																																					
Capacitance Tolerance	±20% (at 120 Hz, 20°C)																																					
Leakage Current (at 20°C)	I = 0.002CV or 0.4 (μA) whichever is greater (after 2 minutes) Where, C = rated capacitance in μF, V = rated DC working voltage in V																																					
Tanδ (at 120 Hz, 20°C)	<table><tr><td>Rated Voltage</td><td>6.3</td><td>10</td><td>16</td><td>25</td><td>35</td><td>50</td><td>63</td><td>100</td></tr><tr><td>Tanδ (max)</td><td>0.24</td><td>0.21</td><td>0.16</td><td>0.14</td><td>0.12</td><td>0.10</td><td>0.09</td><td>0.08</td></tr></table> When the capacitance exceeds 1,000μF, 0.02 shall be added every 1,000μF increase.									Rated Voltage	6.3	10	16	25	35	50	63	100	Tanδ (max)	0.24	0.21	0.16	0.14	0.12	0.10	0.09	0.08											
Rated Voltage	6.3	10	16	25	35	50	63	100																														
Tanδ (max)	0.24	0.21	0.16	0.14	0.12	0.10	0.09	0.08																														
Low Temperature Characteristics (at 120 Hz)	Impedance ratio shall not exceed the values given in the table below. <table><tr><td colspan="2">Rated Voltage</td><td>6.3</td><td>10</td><td>16</td><td>25</td><td>35</td><td>50</td><td>63</td><td>100</td></tr><tr><td rowspan="2">Impedance Ratio</td><td>Z(-25°C)/Z(+20°C)</td><td>5</td><td>4</td><td>2</td><td>2</td><td>2</td><td>2</td><td>2</td><td>2</td></tr><tr><td>Z(-40°C)/Z(+20°C)</td><td>10</td><td>8</td><td>6</td><td>4</td><td>4</td><td>3</td><td>3</td><td>3</td></tr></table>									Rated Voltage		6.3	10	16	25	35	50	63	100	Impedance Ratio	Z(-25°C)/Z(+20°C)	5	4	2	2	2	2	2	2	Z(-40°C)/Z(+20°C)	10	8	6	4	4	3	3	3
Rated Voltage		6.3	10	16	25	35	50	63	100																													
Impedance Ratio	Z(-25°C)/Z(+20°C)	5	4	2	2	2	2	2	2																													
	Z(-40°C)/Z(+20°C)	10	8	6	4	4	3	3	3																													
Endurance	<table><tr><td>Test Time</td><td>2,000 Hrs</td></tr><tr><td>Capacitance Change</td><td>Within ±20% of initial value</td></tr><tr><td>Tanδ</td><td>Less than 200% of specified value</td></tr><tr><td>Leakage Current</td><td>Within specified value</td></tr></table> * The above specifications shall be satisfied when the capacitors are restored to 20°C after the rated voltage applied with rated ripple current for 2,000 hours at 85°C.									Test Time	2,000 Hrs	Capacitance Change	Within ±20% of initial value	Tanδ	Less than 200% of specified value	Leakage Current	Within specified value																					
Test Time	2,000 Hrs																																					
Capacitance Change	Within ±20% of initial value																																					
Tanδ	Less than 200% of specified value																																					
Leakage Current	Within specified value																																					
Shelf Life Test	<table><tr><td>Test Time</td><td>1,000 Hrs</td></tr><tr><td>Capacitance Change</td><td>Within ±20% of initial value</td></tr><tr><td>Tanδ</td><td>Less than 200% of specified value</td></tr><tr><td>Leakage Current</td><td>Within specified value</td></tr></table> * The above specifications shall be satisfied when the capacitors are restored to 20°C after exposing them for 1,000 hours at 85°C without voltage applied.									Test Time	1,000 Hrs	Capacitance Change	Within ±20% of initial value	Tanδ	Less than 200% of specified value	Leakage Current	Within specified value																					
Test Time	1,000 Hrs																																					
Capacitance Change	Within ±20% of initial value																																					
Tanδ	Less than 200% of specified value																																					
Leakage Current	Within specified value																																					
Ripple Current and Frequency Multipliers	<table><tr><th>Cap.(μF) \ Freq.(Hz)</th><th>60 (50)</th><th>120</th><th>500</th><th>1k</th><th>10k up</th></tr><tr><td>≤ 100</td><td>0.70</td><td>1.00</td><td>1.35</td><td>1.55</td><td>2.00</td></tr><tr><td>100 < C ≤ 1,000</td><td>0.83</td><td>1.00</td><td>1.23</td><td>1.32</td><td>1.50</td></tr><tr><td>1,000 <</td><td>0.90</td><td>1.00</td><td>1.10</td><td>1.12</td><td>1.15</td></tr></table>									Cap.(μF) \ Freq.(Hz)	60 (50)	120	500	1k	10k up	≤ 100	0.70	1.00	1.35	1.55	2.00	100 < C ≤ 1,000	0.83	1.00	1.23	1.32	1.50	1,000 <	0.90	1.00	1.10	1.12	1.15					
Cap.(μF) \ Freq.(Hz)	60 (50)	120	500	1k	10k up																																	
≤ 100	0.70	1.00	1.35	1.55	2.00																																	
100 < C ≤ 1,000	0.83	1.00	1.23	1.32	1.50																																	
1,000 <	0.90	1.00	1.10	1.12	1.15																																	

Diagram of Dimensions



Lead Spacing and Diameter						Unit: mm	
ϕ D	5	6.3	8	10	12.5	16	18
P	2.0	2.5	3.5	5.0	5.0	7.5	7.5
ϕ d	0.5		0.6			0.8	
α	L<20: 1.5, L $\geq$ 20: 2.0						
β	0.5						



Dimension: $\phi D \times L(\text{mm})$

Ripple Current: mA/rms at 120 Hz, 85°C

Dimension and Permissible Ripple Current

Cap.(μF)	Contents	6.3V (0J)		10V (1A)		16V (1C)		25V (1E)		35V (1V)		50V (1H)		63V (1J)		100V (2A)	
		$\phi D \times L$	mA	$\phi D \times L$	mA	$\phi D \times L$	mA	$\phi D \times L$	mA	$\phi D \times L$	mA	$\phi D \times L$	mA	$\phi D \times L$	mA	$\phi D \times L$	mA
2.2	2R2											5×11	29			5×11	33
3.3	3R3											5×11	35			5×11	40
4.7	4R7							5×11	31	5×11	40	5×11	42	5×11	45	5×11	48
10	100					5×11	44	5×11	54	5×11	58	5×11	65	5×11	70	6.3×11	80
22	220			5×11	59	5×11	75	5×11	80	5×11	87	5×11	95	6.3×11	115	8×11.5	135
33	330	5×11	55	5×11	84	5×11	90	5×11	97	5×11	105	6.3×11	125	6.3×11	140	10×12.5	195
47	470	5×11	79	5×11	100	5×11	110	5×11	115	6.3×11	145	6.3×11	150	8×11.5	190	10×16	255
100	101	5×11	130	5×11	145	6.3×11	180	6.3×11	190	8×11.5	240	8×11.5	255	10×12.5	320	12.5×20	450
220	221	6.3×11	230	6.3×11	250	8×11.5	300	8×11.5	320	10×12.5	420	10×16	490	10×20	565	16×25	810
330	331	6.3×11	280	8×11.5	350	8×11.5	370	10×12.5	470	10×16	570	10×20	650	12.5×20	765	16×25	990
470	471	8×11.5	380	8×11.5	415	10×12.5	520	10×16	620	10×20	740	12.5×20	860	12.5×25	990	16×31.5	1,250
1,000	102	10×12.5	650	10×16	790	10×20	910	12.5×20	1,090	12.5×25	1,300	16×25	1,530	16×31.5	1,700		
2,200	222	12.5×20	1,150	12.5×20	1,240	12.5×25	1,420	16×25	1,660	16×31.5	1,890	18×35.5	2,160				
3,300	332	12.5×20	1,380	12.5×25	1,590	16×25	1,840	16×31.5	2,070	18×35.5	2,340						
4,700	472	16×25	1,880	16×25	1,980	16×31.5	2,260	18×35.5	2,520	18×40	2,690						

Part Numbering System

RLA Series	470 μF	±20%	6.3V	Bulk Package	Gas Type	8 ϕ × 11.5L	Pb-free and PET sleeve
RLA	471	M	0J	BK	-	0811	
Series Name	Capacitance	Capacitance Tolerance	Rated Voltage	Lead Configuration and Package	Rubber Type	Case Size	Lead Wire and Sleeve type

Note: For more details, please refer to "Part Numbering System (Radial Type)" on page 13.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Lelon:](#)

[RLA222M1EBK-1625P](#) [RLA100M1CBK-0511P](#) [RLA100M1HBK-0611P](#) [RLA100M1VBK-0511P](#) [RLA101M1ABK-0511P](#) [RLA101M1EBK-0611P](#) [RLA101M1HBK-1016P](#) [RLA101M1VBK-0811P](#) [RLA102M1ABK-1020P](#) [RLA102M1CBK-1020P](#) [RLA102M1EBK-1320P](#) [RLA102M1HBK-1625P](#) [RLA102M1VBK-1325P](#) [RLA220M1CBK-0511P](#) [RLA220M1HBK-0611P](#) [RLA220M1VBK-0511P](#) [RLA221M1ABK-0611P](#) [RLA221M1CBK-0811P](#) [RLA221M1EBK-0811P](#) [RLA221M1VBK-1012P](#) [RLA222M1ABK-1320P](#) [RLA2R2M1HBK-0511P](#) [RLA330M1CBK-0511P](#) [RLA330M1VBK-0511P](#) [RLA331M1ABK-0811P](#) [RLA332M1CBK-1625P](#) [RLA3R3M1HBK-0511P](#) [RLA470M1HBK-0811P](#) [RLA470M1VBK-0611P](#) [RLA471M1ABK-0811P](#) [RLA471M1CBK-1012P](#) [RLA471M1HBK-1320P](#) [RLA471M1VBK-1020P](#) [RLA4R7M1HBK-0511P](#) [RLA4R7M1VBK-0511P](#) [RLAR47M1HBK-0511P](#) [RLA101M1CBK-0611P](#) [RLA222M1VBK-1632P](#) [RLA470M1CBK-0511P](#)