



OCV Series

Features

- 105°C, 2,000 hours assured
- Ultra low ESR, solid capacitors of SMD type
- RoHS compliance




Marking color: Blue

Specifications

Items	Performance				
Category Temperature Range	-55°C ~ +105°C				
Capacitance Tolerance	±20% (at 120 Hz, 20°C)				
Leakage Current (at 20°C)*	Rated voltage applied, after 2 minutes at 20°C. See Standard Ratings				
Tanδ (at 120 Hz, 20°C)	See Standard Ratings				
ESR (at 100k ~ 300k Hz, 20°C)	See Standard Ratings				
Endurance	Test Time		2,000 Hrs		
	Capacitance Change		Within ±20% of initial value		
	Tanδ		Less than 150% of specified value		
	ESR		Less than 150% of specified value		
	Leakage Current		Within specified value		
* The above specifications shall be satisfied when the capacitors are restored to 20°C after the rated voltage applied for 2,000 hours at 105°C.					
Moisture Resistance	Test Time		1,000 Hrs		
	Capacitance Change		Within ±20% of initial value		
	Tanδ		Less than 150% of specified value		
	ESR		Less than 150% of specified value		
	Leakage Current		Within specified value		
* The above specifications shall be satisfied when the capacitors are restored to 20°C after subjecting them at 60°C, 90 ~ 95% RH for 1,000 hours. Leakage current should be tested after voltage treatment*.					
Resistance to Soldering Heat * (Please refer to page 26 for reflowsoldering conditions)	Capacitance Change		Within ±10% of initial value		
	Tanδ		Within specified value		
	ESR		Within specified value		
	Leakage Current		Within specified value		
Ripple Current and Frequency Multipliers	Frequency (Hz)	120 ≤ f < 1k	1k ≤ f < 10k	10k ≤ f < 100k	100k ≤ f < 500k
	Multiplier	0.05	0.3	0.7	1.0

* For any doubt about measured values, measure the leakage current again after the following voltage treatment.
Voltage treatment: DC rated voltage is applied to the capacitors for 2 hours at 105 °C.

Diagram of Dimensions



Lead Spacing and Diameter



Unit: mm

φ D	L	A	B	C	W	P ± 0.2
5	5.7 ± 0.3	5.3	5.3	5.9	0.5 ~ 0.8	1.5
6.3	5.9 +0.1/-0.3	6.6	6.6	7.2	0.5 ~ 0.8	2.0
6.3	7.0 ± 0.2	6.6	6.6	7.2	0.5 ~ 0.8	2.0
8	6.7 ± 0.3	8.3	8.3	9.0	0.7 ~ 1.1	3.1
8	12.0 ± 0.5	8.3	8.3	9.0	0.7 ~ 1.1	3.1
10	7.7 ± 0.3	10.3	10.3	11.0	0.7 ~ 1.3	4.7
10	9.9 +0.1/-0.3	10.3	10.3	11.0	0.7 ~ 1.3	4.7
10	12.6 +0.1/-0.4	10.3	10.3	11.0	0.7 ~ 1.3	4.7

Marking

φ D = 5 ~ 6.3

φ D = 8 ~ 10





Dimension: ϕ D×L(mm)

Ripple Current: mA/rms at 100k Hz, 105°C

Standard Ratings

Rated Volt. (V)	Surge Voltage (V)	Capacitance (μ F)	Size ϕ D×L(mm)	Tan δ (120 Hz, 20°C)	L C (μ A)	E S R (m Ω /at 100k ~ 300k Hz, 20°C max.)	Rated R. C. (mA/rms at 100k Hz, 105°C)
2.5V (0E)	2.9	220	6.3 × 5.9	0.12	110	25	2,500
		560	8 × 6.7	0.12	280	23	3,100
		680	8 × 12	0.18	340	12	4,770
		1,000	10 × 7.7	0.12	500	19	4,240
		1,200	10 × 9.9	0.18	750	13	5,200
		1,500	10 × 12.6	0.18	750	10	5,500
4V (0G)	4.6	150	5 × 5.7	0.12	120	30	1,490
			6.3 × 5.9		120	26	2,450
		220	8 × 6.7		176	25	3,020
		330	8 × 6.7		264	25	3,020
		470	10 × 7.7		376	20	4,130
		560	8 × 12	0.18	448	12	4,770
		680	10 × 7.7	0.12	544	20	4,130
		820	10 × 9.9	0.18	656	13	5,200
		1,200	10 × 12.6	0.18	960	10	5,500
6.3V (0J)	7.2	82	6.3 × 5.9	0.12	103	27	2,400
			5 × 5.7		126	35	1,380
		100	6.3 × 5.9		126	27	2,400
			6.3 × 7		151	30	2,010
		150	6.3 × 7		189	30	2,250
			8 × 6.7		189	25	3,020
		220	6.3 × 7		277	30	2,250
			8 × 6.7		277	25	3,020
		330	10 × 7.7	0.15	416	20	4,130
		470	8 × 12		592	12	4,770
		560	10 × 9.9		706	16	4,700
		820	10 × 12.6		1,033	10	5,500
10V (1A)	12.0	47	5 × 5.7	0.12	94	40	1,270
		56	6.3 × 5.9	0.10	112	31	2,250
		150	8 × 6.7	0.10	300	27	2,800
		330	8 × 12	0.15	660	14	4,420
			10 × 7.7	0.10	660	24	3,770
		470	10 × 9.9	0.15	940	18	4,400
		560	10 × 12.6	0.15	1,120	12	5,300
16V (1C)	18.0	22	5 × 5.7	0.12	70	45	1,210
		47	6.3 × 5.9	0.10	150	50	1,650
		82	8 × 6.7	0.10	262	30	2,700
		180	8 × 12	0.15	576	16	4,360
			10 × 7.7	0.10	576	26	3,430
		220	10 × 9.9	0.15	704	20	4,200
		330	10 × 12.6	0.15	792	14	5,050
		820	10 × 12.6	0.12	2,624	18	4,200



Dimension: ϕ D×L(mm)

Ripple Current: mA/rms at 100k Hz, 105°C

Standard Ratings

Rated Volt. (V)	Surge Voltage (V)	Capacitance (μ F)	Size ϕ D×L(mm)	Tan δ (120 Hz, 20°C)	L C (μ A)	E S R (m Ω /at 100k ~ 300k Hz, 20°C max.)	Rated R. C. (mA/rms at 100k Hz, 105°C)
20V (1D)	23.0	22	6.3 × 5.9	0.10	88	50	1,650
		47	8 × 6.7		188	45	2,000
		82	10 × 7.7		328	40	2,500
		100	8 × 12	0.15	400	24	3,320
			10 × 9.9		400	25	3,700
		150	10 × 12.6		600	20	4,320
		330	10 × 12.6	0.12	1,320	26	2,700
25V (1E)	29.0	6.8	6.3 × 5.9	0.10	170	80	1,200
		10	8 × 6.7		125	60	1,500
		22	10 × 7.7		275	50	2,000
		33	8 × 12	0.12	413	30	2,980
		56	10 × 12.6		700	28	3,800
		270	10 × 12.6		1,350	27	2,700
35V (1V)	40.0	39	8 × 12	0.12	273	31	2,100
		68	10 × 12.6	0.12	476	28	2,700

Part Numbering System

OCV Series	470 μ F	±20%	6.3V	Carrier Tape		8 ϕ × 12L	Pb-free and Coated Case
OCV	471	M	0J	TR	-	0812	
Series Name	Capacitance	Capacitance Tolerance	Rated Voltage	Package Type	Terminal Type	Case Size	Lead Wire and Case Type

Note: For more details, please refer to "Part Numbering System (SMD Type)" on page 15.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Lelon:

<u>OCV561M1ATR-1013</u>	<u>OCV6R8M1ETR-0606</u>	<u>OCV820M0JTR-0606</u>	<u>OCV820M1CTR-0807</u>	<u>OCV101M0JTR-0606</u>
<u>OCV101M1DTR-0812</u>	<u>OCV122M0ETR-1010</u>	<u>OCV151M0GTR-0606</u>	<u>OCV151M0JTR-0607</u>	<u>OCV151M1ATR-0807</u>
<u>OCV151M1DTR-1013</u>	<u>OCV152M0ETR-1013</u>	<u>OCV181M1CTR-0812</u>	<u>OCV181M1CTR-1008</u>	<u>OCV220M1DTR-0606</u>
<u>OCV221M0ETR-0606</u>	<u>OCV221M0JTR-0607</u>	<u>OCV221M0JTR-0807</u>	<u>OCV330M1ETR-0812</u>	<u>OCV331M0GTR-0807</u>
<u>OCV331M0JTR-1008</u>	<u>OCV331M1ATR-0812</u>	<u>OCV331M1ATR-1008</u>	<u>OCV331M1CTR-1013</u>	<u>OCV470M1DTR-0807</u>
<u>OCV471M1ATR-1010</u>	<u>OCV561M0GTR-0812</u>	<u>OCV561M1ATR-1008</u>	<u>OCVZ221M0JTR-0604</u>	<u>OCV101M1ETR-1013</u>
<u>OCV151M1CTR-1008</u>	<u>OCV221M1CTR-0810</u>	<u>OCV271M1CTR-0812</u>	<u>OCV331M1CTR-0810</u>	<u>OCV471M0JTR-1008</u>
<u>OCV680M1ATR-0606</u>	<u>OCV331M1CTR-0812</u>	<u>OCV100M1ETR-0807</u>	<u>OCV821M1CTR-1013</u>	