




High Temperature Radial Electrolytic Capacitors HTRL Series

FEATURES

- Excellent temperature performance
- 105°C high operating temperature
- Satisfies characteristic W of JIS-C-5141 standard
- RoHS Compliant



CHARACTERISTICS

Item			Characteristics											
Operating Temperature Range			-40°C ~ +105°C											
Capacitance Tolerance			±20%, 120Hz, 20°C											
Leakage Current	6.3WV ~ 100WV	I = 0.01CWV or 3μA whichever is greater after 2 minutes of applied rated DC working voltage at 20°C Where: C = rated capacitance in μF; WV = rated DC working voltage												
	160WV ~ 250WV	CWV ≤ 1,000: I = 0.03CWV +15μA, C= rated capacitance in μF CWV > 1,000: I = 0.02CWV +25μA, WV= rated DC working voltage in V												
Dissipation Factor (Tan δ, at 20°C 120Hz)			Working voltage (WV)		6.3	10	16	25	35	50	63	100	160	250
			Tan δ		0.23	0.20	0.16	0.14	0.12	0.10	0.09	0.08	0.12	0.17
			For capacitors whose capacitance exceeds 1,000μF, the specification of tan δ is increased by 0.02 for every addition of 1,000μF											
Surge Voltage			Working voltage (WV)		6.3	10	16	25	35	50	63	100	160	250
			Surge voltage (SV)		8	13	20	32	44	63	79	125	200	300
Low Temperature Characteristics			Working voltage (WV)		6.3	10	16	25	35	50	63	100	160	250
			Impedance ratio @ 120Hz	Z(-25°C)/ Z(+20°C)	øD < 16	4	3	3	2	2	2	2	3	8
					øD ≥ 16	6	4	4	3	3	3	3	3	8
				Z(-40°C)/ Z(+20°C)	øD < 16	8	6	6	4	4	3	3	4	10
					øD ≥ 16	12	10	8	8	8	8	6	6	4
Life Test			When returned to +20°C after 2,000 hours application of working voltage at +105°C, the capacitor will meet the following limits: Capacitance change is ≤ ±20% of initial value; tan δ is < 200% of initial specified value; leakage current is ≤ initial specified value											
Shelf Life Test			When returned to +20°C after 1,000 hours at +105°C with no voltage applied, the capacitor will meet the following limits: Capacitance change is ≤ ±20% of initial value; tan δ is < 200% of initial specified value; leakage current is ≤ initial specified value											

PART NUMBERING SYSTEM

1	4	0	-	H	T	R	L	1	6	V	1	0	0	-	R	C
Prefix				Series				Voltage Actual Value			Capacitance (μF) Actual Value				Suffix (RoHS Compliant)	

RIPPLE CURRENT AND FREQUENCY MULTIPLIERS

6.3WV ~ 100WV Capacitance (μF)	Frequency (Hz)				
	60	120	500	1K	≥10K
<100	0.70	1.0	1.30	1.40	1.50
100 ~ 1000	0.75	1.0	1.20	1.30	1.35
>1000	0.80	1.0	1.10	1.12	1.15

Working Voltage (All Capacitances)	Frequency (Hz)					
	60	120	500	1K	10K	≥20K
160WV ~ 250WV	0.80	1.0	1.10	1.10	1.30	1.35


RIPPLE CURRENT AND TEMPERATURE MULTIPLIERS

Temperature (°C)	45	70	85	105
Multiplier (6.3WV ~ 100WV)	1.95	1.78	1.40	1.00
Multiplier (160WV ~ 250WV)	2.05	1.45	1.00	1.00

Specifications are subject to change without notice. No liability or warranty implied by this information. Environmental compliance based on producer documentation.

High Temperature Radial Electrolytic Capacitors HTRL Series

■ DIMENSIONS AND PERMISSIBLE RIPPLE CURRENT



Lead Spacing and Diameter (mm)

ϕD	5	6.3	8	10	13	16	18	22
P	2.0	2.5	3.5	5.0	5.0	7.5	7.5	7.5
ϕd	0.5	0.5	0.5	0.6	0.6	0.8	0.8	1.0
β	0.5	0.5	0.5	0.5	0.5	1.0	1.0	1.0
α	1.0 if $L \leq 16$; 2.0 if $L \geq 20$							

Value (μF)	Working Voltage; Dimensions: $\phi D \times L$ (mm); Ripple Current: mA/RMS @ 120Hz, 105°C									
	6.3		10		16		25		35	
	$\phi D \times L$	mA	$\phi D \times L$	mA	$\phi D \times L$	mA	$\phi D \times L$	mA	$\phi D \times L$	mA
10					5 x 11	35	5 x 11	43	5 x 11	46
22			5 x 11	49	5 x 11	58	5 x 11	62	5 x 11	71
33	5 x 11	54	5 x 11	60	5 x 11	71	5 x 11	76	6.3 x 11	90
47	5 x 11	65	5 x 11	76	5 x 11	85	5 x 11	97	6.3 x 11	110
100	5 x 11	95	5 x 11	105	6.3 x 11	133	6.3 x 11	142	8 x 11	180
220	6.3 x 11	160	6.3 x 11	175	8 x 11	215	8 x 11	236	10 x 12	300
330	8 x 11.5	195	8 x 11.5	245	8 x 11	270	10 x 12	335	10 x 20	400
470	8 x 11.5	270	8 x 11.5	290	10 x 12	370	10 x 12	440	10 x 16	520
680	10 x 12.5	325	10 x 16	395	10 x 20	465	--	--	--	--
1000	10 x 12.5	460	10 x 16	550	10 x 20	640	13 x 20	770	13 x 20	920
2200	10 x 20	810	13 x 20	869	13 x 25	1000	16 x 25	1170	16 x 32	1340
3300	13 x 20	960	13 x 20	1100	16 x 25	1300	16 x 36	1460	18 x 36	1650
4700	16 x 25	1330	16 x 25	1400	16 x 32	1600	18 x 36	1780	18 x 40	1920

Value (μF)	Working Voltage; Dimensions: $\phi D \times L$ (mm); Ripple Current: mA/RMS @ 120Hz, 105°C									
	50		63		100		160		250	
	$\phi D \times L$	mA	$\phi D \times L$	mA	$\phi D \times L$	mA	$\phi D \times L$	mA	$\phi D \times L$	mA
0.1	5 x 11	3.2	5 x 11	3.5	5 x 11	4				
0.22	5 x 11	4.9	5 x 11	5.1	5 x 11	6				
0.33	5 x 11	6	5 x 11	7.5	5 x 11	8				
0.47	5 x 11	7.1	5 x 11	9.0	5 x 11	9.0				
1	5 x 11	13	5 x 11	15	5 x 11	15	5 x 11	17	6.3 x 11	27
2.2	5 x 11	20	5 x 11	30	5 x 11	30	6.3 x 11	29	6.3 x 11	35
3.3	5 x 11	30	5 x 11	31	5 x 11	31	6.3 x 11	36	8 x 11.5	50
4.7	5 x 11	33	5 x 11	36	6.3 x 11	40	6.3 x 11	43	8 x 13	60
10	5 x 11	50	5 x 11	54	8 x 11	66	10 x 12.5	87	10 x 16	115
22	6.3 x 11	78	6.3 x 11	86	8 x 11	99	10 x 20	158	13 x 20	255
33	8 x 11	96	8 x 11.5	114	10 x 12.5	148	10 x 20	190	13 x 25	348
47	8 x 11	130	8 x 11.5	141	10 x 12	180	13 x 26	265	13 x 25	468
100	8 x 11	188	10 x 12	235	13 x 20	320	16 x 25	485	16 x 36	610
220	10 x 20	355	10 x 20	450	16 x 25	570	16 x 32	660		
330	10 x 20	460	13 x 20	540	16 x 32	700	18 x 36	820		
470	13 x 25	610	16 x 25	720	18 x 36	880				
1000	16 x 25	1080	16 x 32	1210	22 x 40	1760				
2200	18 x 36	2120	18 x 40	2340						
3300	22 x 40	2290								

Specifications are subject to change without notice. No liability or warranty implied by this information. Environmental compliance based on producer documentation.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Xicon:

[140-HTRL16V4700](#) [140-HTRL25V4.7](#) [140-HTRL25V470](#) [140-HTRL100V470](#) [140-HTRL16V100-TB](#) [140-HTRL35V100](#) [140-HTRL100V100](#) [140-HTRL160V1.0](#) [140-HTRL35V220](#) [140-HTRL250V4.7](#) [140-HTRL16V2200](#) [140-HTRL35V33](#) [140-HTRL100V.47](#) [140-HTRL35V100-TB](#) [140-HTRL25V1000](#) [140-HTRL35V1000](#) [140-HTRL35V47](#) [140-HTRL35V10](#) [140-HTRL100V0.22](#) [140-HTRL50V1.0-TB](#) [140-HTRL25V33](#) [140-HTRL25V10](#) [140-HTRL50V2.2-TB](#) [140-HTRL50V1000](#) [140-HTRL10V680](#) [140-HTRL25V22](#) [140-HTRL25V47](#) [140-HTRL25V100-TB](#) [140-HTRL63V2.2-RC](#) [140-HTRL160V4.7-RC](#) [140-HTRL50V2.2-RC](#) [140-HTRL100V4.7-RC](#) [140-HTRL100V.47-RC](#) [140-HTRL250V4.7-RC](#) [140-HTRL25V33-RC](#) [140-HTRL35V33-RC](#) [140-HTRL50V33-RC](#) [140-HTRL250V1.0-RC](#) [140-HTRL50V10-RC](#) [140-HTRL35V10-RC](#) [140-HTRL25V10-RC](#) [140-HTRL63V3.3-RC](#) [140-HTRL25V470-RC](#) [140-HTRL100V0.22-RC](#) [140-HTRL35V470-RC](#) [140-HTRL16V4700-RC](#) [140-HTRL50V470-RC](#) [140-HTRL16V470-RC](#) [140-HTRL50V1.0-RC](#) [140-HTRL50V150-RC](#) [140-HTRL50V100-RC](#) [140-HTRL10V100-RC](#) [140-HTRL16V100-RC](#) [140-HTRL35V100-RC](#) [140-HTRL25V100-RC](#) [140-HTRL63V100-RC](#) [140-HTRL16V47-RC-TB](#) [140-HTRL50V2.2-RC-TB](#) [140-HTRL16V47](#) [140-HTRL16V22](#) [140-HTRL16V470](#) [140-HTRL100V1.0](#) [140-HTRL25V220](#) [140-HTRL25V10-TB](#) [140-HTRL35V10-TB](#) [140-HTRL50V10-TB](#) [140-HTRL50V4.7](#) [140-HTRL50V470](#) [140-HTRL10V100](#) [140-HTRL16V220](#) [140-HTRL100V22](#) [140-HTRL100V10](#) [140-HTRL50V2200](#) [140-HTRL63V4.7](#) [140-HTRL25V100](#) [140-HTRL16V47-TB](#) [140-HTRL50V47-TB](#) [140-HTRL35V330](#) [140-HTRL160V100](#) [140-HTRL35V470](#) [140-HTRL16V1000](#) [140-HTRL50V33](#) [140-HTRL16V100](#) [140-HTRL63V1000](#) [140-HTRL50V47](#) [140-HTRL16V330](#) [140-HTRL16V680](#) [140-HTRL100V680](#) [140-HTRL50V10](#) [140-HTRL250V22](#) [140-HTRL250V33](#) [140-HTRL250V47](#) [140-HTRL250V10](#) [140-HTRL160V22](#) [140-HTRL160V10](#) [140-HTRL16V220-TB](#) [140-HTRL50V100](#) [140-HTRL63V100](#) [140-HTRL63V2.2](#) [140-HTRL250V100](#)