

PRELIMINARY SPEC



ATTENTION
OBSERVE PRECAUTIONS
FOR HANDLING
ELECTROSTATIC
DISCHARGE
SENSITIVE
DEVICES

Part Number: AAD1-9090SY9ZC/2

Super Bright Yellow

Features

- Super high flux output and high luminance.
- Designed for high current operation.
- Low thermal resistance.
- Low voltage DC operated.
- Superior ESD protection.
- Package: 500pcs/reel.
- Not reflow compatible.
- The component is internally protected with silicone gel.
- RoHS compliant.



Applications

- traffic signaling.
- backlighting (illuminated advertising , general lighting).
- interior and exterior automotive lighting.
- substitution of micro incandescent lamps.
- portable light source (e.g. bicycle flashlight).
- signal and symbol luminaire for orientation.
- marker lights (e.g. steps, exit ways, etc).
- decorative and entertainment lighting.
- indoor and outdoor commercial and residential architectural lighting.


Application Note

Static electricity and surge damage the LEDS.

It is recommended to use a wrist band or anti-electrostatic glove when handling the LEDs.

All devices, equipment and machinery must be electrically grounded.

Package Dimensions



Notes:

1. All dimensions are in millimeters (inches).
2. Tolerance is $\pm 0.25(0.01")$ unless otherwise noted.
3. Specifications are subject to change without notice.
4. The device has a single mounting surface. The device must be mounted according to the specifications.



Selection Guide

Part No.	Dice	Lens Type	luminous Intensity Iv (cd)@ 500 mA [2]		Φ_v (lm) @ 500 mA [2]		Viewing Angle [1]
			Min.	Typ.	Min.	Typ.	2 θ 1/2
AAD1-9090SY9ZC/2	Super Bright Yellow (AlGaInP)	WATER CLEAR	16	20	46	58	100°

Notes:

1. θ 1/2 is the angle from optical centerline where the luminous intensity is 1/2 the optical centerline value.
2. Luminous intensity / luminous flux: +/-15%.

Absolute Maximum Ratings at TA=25°C

Parameter	Symbol	Value	Unit
Power dissipation	P _t	1.28	W
Junction temperature	T _j	110	°C
Operating Temperature	T _{op}	-40 To +100	°C
Storage Temperature	T _{stg}	-40 To +100	°C
DC Forward Current [1]	I _F	500	mA
Peak Forward Current [2]	I _{FM}	700	mA
Thermal resistance [1]	R _{th j-slug}	12	°C/W
Electrostatic Discharge Threshold (HBM)		8000	V
Iron Soldering [3]	350°C For 3 Seconds		

Notes:

1. Results from mounting on MCPCB.
2. 1/10 Duty Cycle, 0.1ms Pulse Width.
3. 1.29mm distance from solder joint to package.







Electrical / Optical Characteristics at TA=25°C

Parameter	Symbol	Value	Unit
Wavelength at peak emission I _F =500mA [Typ.]	λ_{peak}	598	nm
Dominant Wavelength I _F =500mA [Typ.]	λ_{dom} [1]	591	nm
Spectral bandwidth at 50% $\Phi_{REL MAX}$ I _F =500mA [Typ.]	$\Delta\lambda$	23	nm
Forward Voltage I _F =500mA [Min.]	V _F [2]	2.0	V
Forward Voltage I _F =500mA [Typ.]		2.5	
Forward Voltage I _F =500mA [Max.]		3.1	
Temperature coefficient of λ_{peak} I _F =500mA, -10°C ≤ T ≤ 100°C [Typ.]	TC λ_{peak}	0.12	nm/°C
Temperature coefficient of λ_{dom} I _F =500mA, -10°C ≤ T ≤ 100°C [Typ.]	TC λ_{dom}	0.07	nm/°C
I _F =500mA, -10°C ≤ T ≤ 100°C [Typ.]	TC _v	-2.6	mV/°C

Notes:

1. Wavelength: +/-1nm.
2. Forward Voltage: +/-0.1V.


AAD1-9090SY9ZC/2



AAD1-9090SY9ZC/2


Recommended Soldering Pattern

(Units : mm; Tolerance: ± 0.1)




Tape Specifications

(Units : mm)





AAD1-9090SY9ZC/2
Recommended Solder Steps



PACKING & LABEL SPECIFICATIONS

AAD1-9090SY9ZC/2



Kingbright	
P/NO: AAD1-9090xxx	
QTY: 500 pcs	Q.C. Q C
S/N: XXXX	XX XX XXXX PASSED
CODE: XXX	
LOT NO:	
	
XXXXXXXXXXXXXXXXXXXXXXXXXXXX	
RoHS Compliant	

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Kingbright:](#)

[AAD1-9090SY9ZC/2](#)