









L934MD/2	L934RK/2	L130WCP/2	L934RZ/3
			

Part No.	Emitting Color + Material	$\lambda_D$ (nm)	Lens Type	Iv (mcd) @10mA *20mA		Viewing Angle	Dimension
				Min.	Typ.		

L934MD/2ID	GaAsP/GaP	625	red diffused	8	25	60°	<p>T-1 (3mm) Bi-Level</p> 
L934MD/2GD	GaP	568	green diffused	8	20	60°	
L934MD/2YD	GaAsP/GaP	588	yellow diffused	5	15	60°	
L934MD/2SRD	GaAlAs	640	red diffused	*100	*300	60°	

L934RK/2ID	GaAsP/GaP	625	red diffused	8	25	60°	<p>T-1 (3mm) Bi-Level</p> 
L934RK/2GD	GaP	568	green diffused	8	20	60°	
L934RK/2YD	GaAsP/GaP	588	yellow diffused	5	15	60°	
L934RK/2SRD	GaAlAs	640	red diffused	*100	*300	60°	

L130WCP/2EGW	GaAsP/GaP	625	white diffused	*8	*30	60°	<p>T-1 (3mm) Bi-Level</p> 
	GaP	568		*8	*25		
L130WCP/2EYW	GaAsP/GaP	625	white diffused	*8	*30	60°	
	GaAsP/GaP	588		*8	*20		
L130WCP/2GYW	GaP	568	white diffused	*8	*25	60°	
	GaAsP/GaP	588		*8	*20		

L934RZ/3ID	GaAsP/GaP	625	red diffused	8	25	60°	<p>T-1 (3mm) Tri-Level</p> 
L934RZ/3GD	GaP	568	green diffused	8	20	60°	
L934RZ/3YD	GaAsP/GaP	588	yellow diffused	5	15	60°	
L934RZ/3SRD	GaAlAs	640	red diffused	*100	*300	60°	

## NOTES:

- All dimensions are in millimeters (inches)
- Tolerance is  $\pm 0.25\text{mm}$  (0.01") unless otherwise noted.

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Kingbright:](#)

[L934MD/2ID](#) [L934MD/2GD](#) [L934MD/2YD](#)