

28.5 GHz Surface Mount Bandpass Filter

B285LB2S

DESCRIPTION

One of DLI's surface mount catalog bandpass filters designed for the 5G band. This filter utilizes DLI's low loss temperature stable materials which offer small size and minimal performance variation over temperature.

DLI's catalog BPF's are offered in a variety of frequency bands, which offers a drop-in solution with highly repeatable performance.

FEATURES

- Small Size
- Shielded Component
- Surface Mount Package
- Moisture Sensitivity Level: MSL 1
- Frequency Stable over Temperature
- Operating & Storage Temp: -55°C to +125°C
- 50Ω Characteristic Impedance

Packaging and Ordering information:

To request Tape and Reel packaging, please order part number B285LB2S-T

SPECIFICATIONS* (based on simulated model)

Parameter	Frequency Range (GHz)	Min	Typ.	Max
Insertion Loss (dB)	27.5 - 29.5	—	2.9	3.5
Return Loss (dB)		10	15	—
Low Side Rejection (dB)	DC - 25.0	50	55	—
	25.0 - 25.75	40	45	—
	25.8 - 26.0	30	35	—
	26.0 - 26.7	10	12	—
High Side Rejection (dB)	30.3 - 31.0	10	15	—
	31.0 - 32.0	40	45	—
	32.0 - 39.0	50	55	—
Size (L x W x H)	0.330(L) X 0.120(W) X 0.079(H) in 8.32(L) X 3.0(W) X 2.0(H) mm			


*Electrical specifications at room temperature. Insertion loss shall vary up to ±0.5 dB over temperature.

28.5 GHz Surface Mount Bandpass Filter

B285LB2S

COMPEX • DLI • JOHANSON MFG
NOVACAP • SYFER • VOLTRONICS
www.knowlescapacitors.com

RF Measured Performance




28.5 GHz Surface Mount Bandpass Filter

B285LB2S

COMPEX • DLI • JOHANSON MFG
NOVACAP • SYFER • VOLTRONICS
www.knowlesc capacitors.com

Physical Dimensions

Units = inches (in)




28.5 GHz Surface Mount Bandpass Filter

B285LB2S

COMPEX • DLI • JOHANSON MFG
NOVACAP • SYFER • VOLTRONICS
www.knowlesc capacitors.com

PCB Pattern Recommendations

Unit : mil



Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Knowles:](#)

[B285LB2S](#)