

16GHz 2-way Wilkinson Power Divider

PDW06401

DESCRIPTION

DLI's 16GHz 2-way power divider / combiner offers unmatched size and performance in a surface mount configuration. This power divider utilizes DLI's low loss temperature stable materials which offer small size and minimal performance variation over temperature.

FEATURES


- Small Size
- Frequency Stable over Temperature
- Solder Surface Mount Package
- Excellent Repeatability
- Moisture Sensitivity Level: MSL1
- Operating & Storage Temp: -55°C to +125°C
- Characteristic Impedance: 50Ω

SPECIFICATIONS*

Parameter	Frequency Range (GHz)	Min	Typ.	Max
Nominal Power Splitting (dB)	15 - 17		3.0	
Nominal Phase Shift (Deg)			0.0	
Amplitude Balance (dB)				± .25
Phase Balance (Deg)				± 5.0
Excess Insertion Loss (dB)				0.5
Return Loss (dB)		20	25	
Isolation (dB)		18	20	
Input Power (W)				TBD

*Electrical specifications based on typical probed performance at room temperature. Insertion loss shall vary ±0.5dB over temperature.

Typical Measured Performance




16GHz 2-way Wilkinson Power Divider


PDW06401

Physical Dimensions

Units = inches



Recommended PCB Layout



- 50Ω trace dimensions are application specific.
- Ensure adequate grounding beneath the part.



Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Knowles:](#)

[PDW06401](#) [PDW06401-T](#)