




## features




- High reliability with  $\Delta R$  of  $\pm 0.1\%$  in the long-term reliability test
- Endurance at 85°C (3,000h):  $\Delta R$  of  $\pm 0.1\%$
- Operating temperature range  $\sim 155^\circ\text{C}$
- Rated ambient temperature: 85°C
- High precision type  $\pm 0.05\%$  is available
- Low current noise
- High reliability and high stability at elevated temperatures
- Improved moisture resistance by glass passivation layer
- Sulfur resistance verified according to ASTM B 809-95
- Products meet EU RoHS requirements
- AEC-Q200 Tested

## dimensions and construction



Type (Inch Size Code)	Dimensions inches (mm)				
	L	W	c	d	t
<b>1E</b> (0402)	.039 <sup>+0.004</sup> <sub>-.002</sub> (1.0 <sup>+0.1</sup> <sub>-0.05</sub> )	.020±.002 (0.5±0.05)	.010±.004 (0.25±0.1)	.010 <sup>+0.002</sup> <sub>-.004</sub> (0.25 <sup>+0.05</sup> <sub>-0.1</sub> )	.014±.002 (0.35±0.05)
<b>1J</b> (0603)	.063±.008 (1.6±0.2)	.031±.004 (0.8±0.1)	.012±.004 (0.3±0.1)	.012±.004 (0.3±0.1)	.018±.004 (0.45±0.1)
<b>2A</b> (0805)	.079±.008 (2.0±0.2)	.049±.008 (1.25±0.2)	.016±.008 (0.4±0.2)	.012 <sup>+0.008</sup> <sub>-.004</sub> (0.3 <sup>+0.2</sup> <sub>-0.1</sub> )	.02±.004 (0.5±0.1)
<b>2B</b> (1206)	.126±.008 (3.2±0.2)	.063±.008 (1.6±0.2)	.02±.012 (0.5±0.3)	.016 <sup>+0.008</sup> <sub>-.004</sub> (0.4 <sup>+0.2</sup> <sub>-0.1</sub> )	.024±.004 (0.6±0.1)
<b>2E</b> (1210)		.098±.008 (2.5±0.2)			

## Derating Curve



For resistors operated at an ambient temperature of 85°C or above, a power rating shall be derated in accordance with the above derating curve.

When the terminal part temperature of the resistor exceeds the rated terminal part temperature shown above, the power shall be derated according to the derating curve. Please refer to "Introduction of the derating curves based on the terminal part temperature" on the beginning of our catalog before use.

## ordering information

RN73H	2B	T	TD	1002	B	25
Type	Size	Termination Material	Packaging	Nominal Resistance	Resistance Tolerance	T.C.R. (ppm/°C)
	1E 1J 2A 2B 2E	T: Sn G: Au (1E, 1J only)	TP: 0402 only: 7" 2mm pitch punched paper TD: 0603, 0805, 1206, 1210: 7" 4mm pitch punched paper TE: 0805, 1206, 1210: 7" embossed plastic For further information on packaging, please refer to Appendix A	3 significant figures + 1 multiplier "R" indicates decimal on value <100Ω	A: $\pm 0.05\%$ B: $\pm 0.1\%$ C: $\pm 0.25\%$ D: $\pm 0.5\%$ F: $\pm 1.0\%$	05 10 25 50 100

Specifications given herein may be changed at any time without prior notice. Please confirm technical specifications before you order and/or use.

8/20/24

## long term precision thin (metal) film flat chip resistors (high reliability, for automotive)

### applications and ratings

Part Designation	Power Rating @ 85°C	Rated Ambient Temp.	Rated Terminal Part Temp.	T.C.R. (ppm/°C) Max.	Resistance Range (Ω) E-24, E-96, E-192*					Maximum Working Voltage	Maximum Overload Voltage
					(A±0.05%)	(B±0.1%)	(C±0.25%)	(D±0.5%)	(F±1.0%)		
RN73H1E	0.063W	85°C	90°C	±5	—	220~10k	—	—	—	50V	100V
				±10	—	47~100k	47~100k	47~100k	47~100k		
				±25	—	47~300k	47~300k	47~300k	47~300k		
	0.1W	85°C	105°C	±50	—	47~300k	47~300k	10~300k	10~300k	50V	100V
				±5	—	220~10k	—	—	—		
				±10	—	47~100k	47~100k	47~100k	47~100k		
RN73H1J	0.1W	85°C	95°C	±25	—	47~300k	47~300k	47~300k	47~300k	75V	150V
				±50	—	47~300k	47~300k	47~300k	47~300k		
				±100	—	—	—	10~1M	10~1M		
	0.125W	85°C	105°C	±5	100~59k	100~59k	—	—	—	75V	150V
				±10	47~59k	47~360k	47~360k	47~360k	47~360k		
				±25	47~59k	47~1M	47~1M	47~1M	47~1M		
RN73H2A	0.125W	85°C	100°C	±50	—	15~1M	15~1M	10~1M	10~1M	150V	300V
				±100	—	—	—	10~1M	10~1M		
				±5	100~100k	100~100k	—	—	—		
	0.25W	85°C	105°C	±10	47~100k	47~1M	47~1M	47~1M	47~1M	150V	300V
				±25	47~100k	47~1.5M	47~1.5M	47~1.5M	47~1.5M		
				±50	—	47~1.5M	47~1.5M	47~1.5M	47~1.5M		
RN73H2B	0.25W	85°C	110°C	±100	—	—	—	47~1.5M	47~1.5M	200V	400V
				±5	100~300k	100~300k	—	—	—		
				±10	47~300k	47~1M	47~1M	47~1M	47~1M		
	0.4W	85°C	105°C	±25	47~300k	47~1M	47~1M	47~1M	47~1M	200V	400V
				±50	—	47~1M	47~1M	47~1M	47~1M		
				±100	—	—	—	47~1M	47~1M		
RN73H2E	0.25W	85°C	110°C	±10	100~510k	100~510k	100~510k	100~510k	100~510k	200V	400V
				±25	51~510k	15~1M	15~1M	10~1M	10~1M		
				±50	—	15~1M	15~1M	10~1M	10~1M		
	0.5W	85°C	105°C	±100	—	—	—	10~1M	10~1M	200V	400V
				±10	100~510k	100~510k	100~510k	100~510k	100~510k		
				±25	51~510k	47~1M	47~1M	47~1M	47~1M		
±50	—	47~1M	47~1M	47~1M	47~1M	47~1M	47~1M	47~1M	47~1M		

\* No marking on E-192 values. Operating Temperature: -55°C to +155°C. If any questions arise whether to use the "Rated Ambient Temperature" or the "Rated Terminal Part Temperature" in your usage conditions, please give priority to the "Rated Terminal Part Temperature".

### environmental applications - Performance Characteristics

Parameter	Requirement $\Delta R \pm(\%+0.05\Omega)$		Test Method
	Limit	Typical	
Resistance	Within specified tolerance	—	25°C
T.C.R.	Within specified T.C.R.	—	+25°C/+125°C: T.C.R. +5 (x10 <sup>-6</sup> /K); +25°C/-55°C and +25°C/+155°C: others
Overload (Short time)	Standard Mode: ±0.05%	±0.01%	Rated Voltage x 2.5 or Max. overload voltage, whichever is less, for 5 seconds
	Power Mode: ±0.05%	±0.01%	1E, 1J: Rated voltage x2.0 or Max overload voltage, whichever is less, for 5 seconds 2A,2B, 2E: Rated voltage x1.5 or Max overload voltage, whichever is less, for 5 seconds
Resistance to Solder Heat	±0.5%**	±0.01%	260°C ± 5°C, 10 seconds ± 1 second
Rapid Change of Temperature	±0.1%**	±0.02%	1E, 1J, 2A: -55°C (30 minutes), +155°C (30 minutes), 1000 cycles 2B, 2E: -55°C (30 minutes), +155°C (30 minutes), 500 cycles
Moisture Resistance	Standard Mode: ±0.1%**	±0.05%	85°C±2°C, 85%±5%RH, 1000h. Rated voltage or Max working voltage, whichever is less. 1.5h ON/0.5h OFF cycle
	Power Mode: ±0.1%**	±0.04%	85°C±2°C, 85%±5%RH, 1000h. Rated power x0.1 or Max working voltage, whichever is less
Endurance at 85°C	Standard Mode: 0.1%	±0.03%	Rated terminal part temp. ±2°C or Rated ambient temp. 85°C±2°C, 3000h 1.5h ON/0.5h OFF cycle
	Power Mode: ±0.2%	±0.04%	Rated terminal part temp. ±2°C or Rated ambient temp. 85°C±2°C, 3000h 1.5h ON/0.5h OFF cycle
High Temperature Exposure	±0.1%**	±0.05%	+155°C, 1000 hours

#### Precautions for Use

- The property and electrostatically measured taping materials are used for the components, but attention should be paid to the fact that there is some danger the parts absorb on the top tapes to cause a failure in the mounting and the parts are destructed by static electricity (1J, 2A, 2B, 2E: 1kV and more, 1E: 0.5kV and more at Human Body Model 100pF, 1.5kΩ) to change the resistance in the conditions of an excessive dryness or after the parts are given vibration for a long time as they are packaged on the tapes. Similarly, care should be given not to apply the excessive static electricity when mounting on the boards.
- ionic impurities such as flux etc. that are attached to these products or those mounted onto a PCB, negatively affect their moisture resistance, corrosion resistance, etc. The flux may contain ionic substances like chlorine, acid, etc. while perspiration and saliva include ionic impurities like sodium (Na<sup>+</sup>), chlorine (Cl<sup>-</sup>) etc. Therefore these kinds of ionic substances may induce electrical corrosion when they invade into the products. Either thorough washing or using RMA solder and flux are necessary since lead free solder contains ionic substances. Washing process is needed, before putting on moisture proof material in order to prevent electrical corrosion.
- The upper electrodes could be peeled off when a heat-resistant masking tape is attached to the mounted chip resistors and then detached from them. It is confirmed that the adhesiveness gets stronger due to the exposure to heat under mounting. Accordingly, we recommend the use of masking tape be refrained. If the use of heat-resistant masking tape is unavoidable, please make sure that the adhesives on the tape do not directly come in contact with the product.
- When high-pressure shower cleaning is implemented, there is a possibility of exfoliation of the top electrodes caused by the water pressure stress so please avoid the implementation.
- If the implementation is unavoidable, then please evaluate the products beforehand.

\*\* Depends on resistance value, please contact KOA Speer for details.

For Surface Temperature Rise Graph see Environmental Applications. Additional environmental applications can also be found at [www.koaspeer.com](http://www.koaspeer.com)  
Specifications given herein may be changed at any time without prior notice. Please confirm technical specifications before you order and/or use. 8/20/24

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[KOA Speer:](#)

[RN73H1ETTP4810C10](#) [RN73H1ETTP4870D10](#) [RN73H1ETTP7410B10](#) [RN73H1ETTP8450C10](#)  
[RN73H1ETTP8760F10](#) [RN73H1ETTP5761D10](#) [RN73H1ETTP8200C10](#) [RN73H1ETTP8761B10](#)  
[RN73H1ETTP4641D10](#) [RN73H1ETTP6120B10](#) [RN73H1ETTP6341D10](#) [RN73H1ETTP6810C10](#)  
[RN73H1ETTP7060C10](#) [RN73H1ETTP7681B10](#) [RN73H1ETTP8350F10](#) [RN73H1ETTP5170D10](#)  
[RN73H1ETTP6490C10](#) [RN73H1ETTP7500D10](#) [RN73H1ETTP7680F10](#) [RN73H1ETTP8351B10](#)  
[RN73H1ETTP4640B10](#) [RN73H1ETTP5050D10](#) [RN73H1ETTP5300F10](#) [RN73H1ETTP5490C10](#)  
[RN73H1ETTP5620D10](#) [RN73H1ETTP5691B10](#) [RN73H1ETTP6260F10](#) [RN73H1ETTP6340B10](#)  
[RN73H1ETTP7411D10](#) [RN73H1ETTP7961B10](#) [RN73H1ETTP8061C10](#) [RN73H1ETTP4930C10](#)  
[RN73H1ETTP5100C10](#) [RN73H1ETTP5301B10](#) [RN73H1ETTP5361C10](#) [RN73H1ETTP5690F10](#)  
[RN73H1ETTP5830B10](#) [RN73H1ETTP6261B10](#) [RN73H1ETTP7230C10](#) [RN73H1ETTP7771C10](#)  
[RN73H1ETTP7960F10](#) [RN73H1ETTP5230C10](#) [RN73H1ETTP5760B10](#) [RN73H1ETTP6121D10](#)  
[RN73H1ETTP6651C10](#) [RN73H1ETTP6980F10](#) [RN73H1ETTP4531D10](#) [RN73H1ETTP6981B10](#)  
[RN73H1ETTP7870D10](#) [RN73H1ETTP8160C10](#) [RN73H1ETTP5231C10](#) [RN73H1ETTP5420F10](#)  
[RN73H1ETTP5761B10](#) [RN73H1ETTP6341C10](#) [RN73H1ETTP6730C10](#) [RN73H1ETTP6801D10](#)  
[RN73H1ETTP7060B10](#) [RN73H1ETTP4751C10](#) [RN73H1ETTP5421B10](#) [RN73H1ETTP5760F10](#)  
[RN73H1ETTP6490B10](#) [RN73H1ETTP8161C10](#) [RN73H1ETTP4640F10](#) [RN73H1ETTP5831B10](#)  
[RN73H1ETTP6190B10](#) [RN73H1ETTP7231C10](#) [RN73H1ETTP8560B10](#) [RN73H1ETTP4641B10](#)  
[RN73H1ETTP4870C10](#) [RN73H1ETTP4990D10](#) [RN73H1ETTP5051D10](#) [RN73H1ETTP5830F10](#)  
[RN73H1ETTP6570C10](#) [RN73H1ETTP7590C10](#) [RN73H1ETTP8350D10](#) [RN73H1ETTP5690D10](#)  
[RN73H1ETTP6421B10](#) [RN73H1ETTP6651B10](#) [RN73H1ETTP8201C10](#) [RN73H1ETTP8250C10](#)  
[RN73H1ETTP4811C10](#) [RN73H1ETTP5050B10](#) [RN73H1ETTP5300D10](#) [RN73H1ETTP6200C10](#)  
[RN73H1ETTP6260D10](#) [RN73H1ETTP6420F10](#) [RN73H1ETTP7870C10](#) [RN73H1ETTP8451C10](#)  
[RN73H1ETTP5100B10](#) [RN73H1ETTP5111C10](#) [RN73H1ETTP5171D10](#) [RN73H1ETTP6040C10](#)  
[RN73H1ETTP6120F10](#) [RN73H1ETTP6191D10](#) [RN73H1ETTP7771B10](#) [RN73H1ETTP8060F10](#)  
[RN73H1ETTP8561D10](#) [RN73H1ETTP4590C10](#) [RN73H1ETTP5490B10](#) [RN73H1ETTP5600D10](#)