



LEOPARD IMAGING INC

LI-OV9712-USB-M8

Data Sheet

Key Features

- Support YUV 720P streaming
- MJPEG compression
- USB 2.0 compliance
- Size: 22mm x 19.5mm
- Low cost with high quality
- Customized based on customer's specs




Lens Specification

- Focusing Range Capability: 5mm to infinity
- The lens is adjustable, the shortest focus can be 5mm
- Focal Length: 2.35 mm
- F Number: 2.5
- Fov (D/H/V): 106 °/89 °/49 °
- TV Distortion: <-40%
- Sensor: OV9712


Interface (SM05B-SRSS-TB)

5 Pin USB Connector (SM05B-SRSS-TB)	
Pin No.	Name
1	USB_5V
2	USB_DM
3	USB_DP
4	GND
5	Shield_Ground


Dimensions



Top View



Side View



Bottom View



Leopard Imaging Inc.

1130 Cadillac Ct., Milpitas, CA 95035, USA
Phone: +1-408-263-0988
Fax: +1-408-217-1960
Email: sales@leopardimaging.com
Website: www.leopardimaging.com
www.leopard-security.com

Specification

General Behavior		
Video Resolution @ Frame rate	1280 x 720	YUV @ 10 fps
	800 x 600	YUV @ 18 fps
	640 x 480	YUV @ 30 fps
	352 x 288	YUV @ 30 fps
	320 x 240	YUV @ 30 fps
	160 x 120	YUV @ 30 fps
	1280 x 720	MJPEG @ 30 fps
	800 x 600	MJPEG @ 30 fps
	640 x 480	MJPEG @ 30 fps
	352 x 288	MJPEG @ 30 fps
	320 x 240	MJPEG @ 30 fps
	160 x 120	MJPEG @ 30 fps
Adjustment	The following can be adjusted manually: Brightness, Contrast, Hue, Saturation, Sharpness, Gamma, White Balance (default: Auto), Backlight Comp, Gain, Exposure (default: Auto).	
Interface (Optical)		
Sensor specification	OmniVision OV9712 sensor	
Shutter	Rolling	
Format	1/4”	
Resolution	H:1280, V: 800	
Pixel size	H: 3.0 um, V: 3.0 um	
Lens	M8 lens	
Interface (Electrical)		
Interface	USB 2.0	
Supply voltage	USB 2.0 +5 VDC power source	
Current consumption	Approx. 140 mA at 5 VDC	
Interface (Mechanical)		
Dimensions	L: 22 mm, W: 19.5 mm, H: 14.7 mm	
Mass	2 g	
Environmental		
Max. temperature (operation)	0 °C ~ 50 °C (32 °F~ 122 °F)	
Max. temperature (storage)	-20 °C ~ 80 °C (-4 °F~176 °F)	
Max. humidity (operation)	20 % ~ 80 %, relative, non-condensing	
Max. humidity (storage)	20 % ~ 80 %, relative, non-condensing	



Leopard Imaging Inc.

1130 Cadillac Ct., Milpitas, CA 95035, USA
 Phone: +1-408-263-0988
 Fax: +1-408-217-1960
 Email: sales@leopardimaging.com
 Website: www.leopardimaging.com
 www.leopard-security.com

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Leopard Imaging:](#)

[LI-OV9712-USB-M8](#)