



UNIVERSAL SERIAL BUS: KUSBXHT Series

High Temperature Flag Style USB Type B

Product Features

High Retention Force
Through Hole PCB Mount
Compatible with Many Computer Peripherals
Supports Hot Plugging
Contact Area with Gold Plating

Performance Specifications

Materials and Finish

Insulator

High Temperature, Thermoplastic, ULV-0 Rated,
Orange Color

Shell

Stainless Steel, Nickel Plated

Contact Material

Phosphor Bronze

Contact Plating

See Drawing

Electrical Characteristics

Rated Current

1.5A

Rated Voltage

30V DC

Insulation Resistance

1000 Megohms Min.

Dielectric Withstanding Voltage

500V AC For 1 Minute

Contact Resistance

30 milliohms Max.

Mechanical Characteristics

Durability: 1500 Mating Cycles Min.

Mating Force: 35N Max.

Extraction Force: 15N Min.

Operating Temperature: -55°C to +85°C

2D Drawing	IGES	STEP	3D PDF
Solder Profile	CofC RoHS Compliant	CofC REACH Compliant	UL Plastic File
Certificate of Origin	Check Stock	Request a Sample	Send Us An Email

Generated Part Number

Part Number Builder

	-				
Series		Type	Insulator Color	Plating Option	Other Option

Series

KUSBXHT - Universal Serial Bus, High Temperature

Type

SLAS1N - A Type, Flag Style

Insulator Color Option

O - Orange

Plating option

Blank - Gold Flash

30 - 30µ" Gold Plating

Option


HRF - High Retention Force

Contact Kycon for Other Options

KUSBXHT

Dimensions in mm

KUSBXHT-SLAS1N-O-HRF



Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Kycon:](#)

[KUSBXHT-SLAS1N-O-HRF](#) [KUSBXHT-SLAS1N-O30-HRF](#)