Connector: SMA Jack (Female Socket)				
Termination: PCB Board Edge, End Launch				
Part Number		CONSMA003.031	CONSMA003.031-G	
Connector Part	Material	Finish	Finish	
Bodies	Body: Brass	Nickel	Gold	
Center Contact	Socket: Be Cu	Gold	Gold	
Insulator	PTFE	N/A	N/A	

	REVISIONS			
RE	DESCRIPTION	DATE	APPV	
A	INITIAL RELEASE OF LINX INTERNAL DRAWING	01/MAR/19	CLL	





NOTES: (UNLESS OTHERWISE SPECIFIED)

- 1. ALL DIMENSIONS ARE IN mm [INCHES].
- 2. DIMENSIONS APPLY AFTER FINISHING.
- MANUFACTURE TO BE COMPLIANT WITH EU RoHS DIRECTIVE, USE MATERIALS THAT DO NOT CONTAIN REACH SUBSTANCES OF VERY HIGH CONCERN >1000ppm, AND USE DRC CONFLICT-FREE SOURCED MATERIALS.
- 4. SAFETY BREAK ALL SHARP CORNERS AND EDGES 0.5 MAXIMUM.
- 5 SEE TABLE I FOR ELECTRICAL SPECIFICATIONS. (SHEET 2)
- 6 SEE TABLE II FOR ENVIRONMENTAL SPECIFICATIONS. (SHEET 2)
- 7 SEE TABLE III FOR MECHANICAL SPECIFICATIONS. (SHEET 2)
- 8. SEE PARTSLIST. "*" INDICATES FINISH TYPE.





SEE SHEET 1 FOR REVISIONS

5 TABLE I

Electrical Data	Detail
Impedance	50 Ω
Frequency Range	0 to 18 GHz
Insulation Resistance	5 000 M Ω min.
Voltage Rating	500 V RMS
Contact Resistance	Center: $\leq 2.0 \text{ m} \Omega$ Outer: $\leq 2.0 \text{ m} \Omega$
VSWR	≤ 1.2 : 1 @ 6 GHz

6 TABLE II

Environmental Data	Detail
Corrosion (Salt spray)	ASTM B-117
Thermal Shock	MIL-STD-202 Method 107 test condition B
Vibration	MIL-STD-202 Method 204 test condition D
Mechanical Shock	MIL-STD-202 Method 213 test condition I
Temperature Range	-65 °C to +165 °C
Environmental Compliance	RoHS

7 TABLE III

Mechanical Data	Detail
Mounting Type	PCB Board Edge, End Launch
Fastening Type	1/4"-36 Threaded Coupling
Interface In Accordance With	MIL-STD 348A
Recommended Torque	0.57 N·m (5.0 in lbs)
Coupling Nut Retention	60 lbs. min.
Connector Durability	500 cycles min.
Weight	1.3 g (0.05 oz)



SHEET 2 OF 2

DO NOT SCALE DRAWING



Reflow Soldering

Reflow soldering is the most common method of attaching surface mount electronic components to a circuit board. The goal of the reflow process is to melt the solder and heat the conductive surfaces, without overheating or damaging any electrical components. In the conventional reflow soldering process, there are four distinct stages, or zones, having specific thermal profiles: preheat, thermal soak, reflow, and cooling. For high-volume assembly, surface mount components are generally auto-placed by machine.

Reflow Temperature Profile

The single most critical stage in the automated assembly process is the reflow stage. The reflow profile for any given component should be closely followed because excessive temperatures or transport times during reflow can irreparably damage the component. Assembly personnel need to pay careful attention to the oven's profile to ensure that it meets the requirements necessary to successfully reflow all components while still remaining within the limits mandated by components requiring shorter flow periods.



Copyright © 2018 Linx Technologies

159 Ort Lane, Merlin, OR 97532 Phone: +1 541 471 6256 Fax: +1 541 471 6251 www.linxtechnologies.com

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Linx Technologies: