


## Product Brief



# HDP Industrial Series Remote Adhesive-Mount Dual-Band WiFi Antenna

The Linx HDP industrial series offers rugged remote-mount dipole antennas having excellent performance for single- and dual-band WiFi/WLAN as well as other 2.4 GHz or 5 GHz ISM and U-NII frequency band applications.

The dual-band HDP industrial antennas are durable, low profile, IP67 ratable, and UV protected. They mount permanently to non-conductive surfaces using the integrated adhesive patch and connect using 2 meters of RG-174/U low-loss cable terminated in an SMA plug (male pin), or RP-SMA plug (female socket) connector for FCC Part 15 compliant applications.



## Features

- Performance at 2.4 GHz
  - VSWR:  $\leq 1.5$
  - Peak Gain: 4.3 dBi
  - Efficiency: 37%
- Performance at 5 GHz
  - VSWR:  $\leq 1.4$
  - Peak Gain: 2.3 dBi
  - Efficiency: 15%
- Low profile
  - 104.0 mm x 17.0 mm x 4.2 mm
- Durable UV protected enclosure rated at IP67 for heavy-duty outdoor use
- Low-loss RG-174/U coaxial cable for improved performance at higher frequencies
- SMA plug (male pin), or RP-SMA plug (female socket) connector

## Applications

- Single- and dual-band WiFi/WLAN
  - 802.11b/g
  - WiFi 4 (802.11n)
  - WiFi 5 (802.11ac)
  - U-NII bands 1-4
- ISM Applications:
  - Bluetooth®
  - ZigBee®
- Internet of Things (IoT) devices
- Smart Home networking
- Sensing and remote monitoring

## Ordering Information

Part Number	Description
ANT-2/5-HDP-2000-SMA	Remote adhesive-mount dual-band WiFi antenna with 2 m of RG-174/U low-loss coaxial cable terminated in an SMA plug (male pin)
ANT-2/5-HDP-2000-RPS	Remote adhesive-mount dual-band WiFi antenna with 2 m of RG-174/U low-loss coaxial cable terminated in an RP-SMA plug (female socket)

Available from Linx Technologies and select distributors and representatives.

Table 1. Electrical Specifications

ANT-2/5-HDP-2000	2.4 GHz		5 GHz	
Frequency Range	2.4 GHz to 2.485 GHz		5.15 GHz to 5.85 GHz	
VSWR (max)	1.5		1.4	
Peak Gain (dBi)	4.3		2.3	
Average Gain (dBi)	-4.6		-8.6	
Efficiency (%)	37		15	
Polarization	Linear	Radiation	Omnidirectional	
Impedance	50 Ω	Max Power	10 W	
Wavelength	1/2-wave	Electrical Type	Dipole	

Table 2. Mechanical Specifications

ANT-2/5-HDP-2000	Dual Band WiFi
Connection	SMA plug (male pin) or RP-SMA plug (female socket)
Cable	2.0 m (78.74 in) of RG-174/U low-loss coaxial cable
Operating Temp. Range	-40 °C to +85 °C
Weight	42.0 g (1.48 oz)
Dimensions	104.0 mm x 17.0 mm x 5.5 mm (4.09 in x 0.67 in x 0.22 in)

## VSWR

Figure 1 provides the voltage standing wave ratio (VSWR) across the antenna bandwidth. VSWR describes the power reflected from the antenna back to the radio. A lower VSWR value indicates better antenna performance at a given frequency. Reflected power is also shown on the right-side vertical axis as a gauge of the percentage of transmitter power reflected back from the antenna.




Figure 1. ANT-2/5-HDP-2000 Antenna VSWR, with Frequency Band Highlights

Website: <http://linxtechnologies.com> • Phone: +1 (541) 471-6256 • E-MAIL: [info@linxtechnologies.com](mailto:info@linxtechnologies.com) • Linx Offices: 159 Ort Lane, Merlin, OR, US 97532

Linx Technologies reserves the right to make changes to the product(s) or information contained herein without notice. No liability is assumed as a result of their use or application. No rights under any patent accompany the sale of any such product(s) or information.

Wireless Made Simple is a registered trademark of Linx Acquisitions LLC. Bluetooth is a registered trademark of Bluetooth SIG, Inc. ZigBee is a registered trademark of ZigBee Alliance, Inc. Other product and brand names may be trademarks or registered trademarks of their respective owners.

Copyright © 2021 Linx Technologies. All Rights Reserved.



# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Linx Technologies:](#)

[ANT-2/5-HDP-2000-RPS](#) [ANT-2/5-HDP-2000-SMA](#)