



# **LED Display**

## **Product Data Sheet**

### **LTD-4708JF**

Spec No.: DS30-2001-321

Effective Date: 05/07/2002

Revision: -

**LITE-ON DCC**

**RELEASE**

**BNS-OD-FC001/A4**

**LITE-ON Technology Corp. / Optoelectronics**

No.90,Chien 1 Road, Chung Ho, New Taipei City 23585, Taiwan, R.O.C.

Tel: 886-2-2222-6181 Fax: 886-2-2221-1948 / 886-2-2221-0660

<http://www.liteon.com/opto>

**FEATURES**

- \* 0.4-INCH (10.0-mm) DIGIT HEIGHT.
- \* CONTINUOUS UNIFORM SEGMENTS.
- \* LOW POWER REQUIREMENT.
- \* EXCELLENT CHARACTERS APPEARANCE.
- \* HIGH BRIGHTNESS & HIGH CONTRAST.
- \* WIDE VIEWING ANGLE.
- \* SOLID STATE RELIABILITY.
- \* CATEGORIZED FOR LUMINOUS INTENSITY.


**DESCRIPTION**

The LTD-4708JF is a 0.4-inch (10.0-mm) digit height dual digit seven-segment display. This device utilizes AlInGaP Yellow Orange LED chips, which are made from AlInGaP on a non-transparent GaAs substrate, and has a gray face and white segments.

**DEVICE**


| PART NO.              | DESCRIPTION                               |
|-----------------------|-------------------------------------------|
| AlInGaP Yellow Orange | Duplex Common Cathode<br>Rt. Hand Decimal |
| LTD-4708JF            |                                           |

## PACKAGE DIMENSIONS



NOTES: All dimensions are in millimeters. Tolerances are ± 0.25-mm (0.01") unless otherwise noted.

## INTERNAL CIRCUIT DIAGRAM



**PIN CONNECTION**

| <b>No.</b> | <b>CONNECTION</b>        |
|------------|--------------------------|
| 1          | ANODE C                  |
| 2          | ANODE D.P.               |
| 3          | ANODE E                  |
| 4          | COMMON CATHODE (DIGIT 2) |
| 5          | ANODE D                  |
| 6          | ANODE F                  |
| 7          | ANODE G                  |
| 8          | ANODE B                  |
| 9          | COMMON CATHODE (DIGIT 1) |
| 10         | ANODE A                  |

**ABSOLUTE MAXIMUM RATING AT Ta=25°C**

| PARAMETER                                                                            | MAXIMUM RATING                           | UNIT               |
|--------------------------------------------------------------------------------------|------------------------------------------|--------------------|
| Power Dissipation Per Segment                                                        | 70                                       | mW                 |
| Peak Forward Current Per Segment<br>( 1/10 Duty Cycle, 0.1ms Pulse Width )           | 60                                       | mA                 |
| Continuous Forward Current Per Segment                                               | 25                                       | mA                 |
| Derating Linear From 25 <sup>0</sup> C Per Segment                                   | 0.33                                     | mA/ <sup>0</sup> C |
| Reverse Voltage Per Segment                                                          | 5                                        | V                  |
| Operating Temperature Range                                                          | -35 <sup>0</sup> C to +85 <sup>0</sup> C |                    |
| Storage Temperature Range                                                            | -35 <sup>0</sup> C to +85 <sup>0</sup> C |                    |
| Solder Temperature 1/16 inch Below Seating Plane for 3 Seconds at 260 <sup>0</sup> C |                                          |                    |

**ELECTRICAL / OPTICAL CHARACTERISTICS AT Ta=25°C**

| PARAMETER                         | SYMBOL           | MIN. | TYP. | MAX. | UNIT | TEST CONDITION       |
|-----------------------------------|------------------|------|------|------|------|----------------------|
| Average Luminous Intensity        | I <sub>V</sub>   | 320  | 850  |      | μcd  | I <sub>F</sub> =1mA  |
| Peak Emission Wavelength          | λ <sub>p</sub>   |      | 611  |      | nm   | I <sub>F</sub> =20mA |
| Spectral Line Half-Width          | Δλ               |      | 17   |      | nm   | I <sub>F</sub> =20mA |
| Dominant Wavelength               | λ <sub>d</sub>   |      | 605  |      | nm   | I <sub>F</sub> =20mA |
| Forward Voltage Per Segment       | V <sub>F</sub>   |      | 2.05 | 2.6  | V    | I <sub>F</sub> =1mA  |
| Reverse Current Per Segment       | I <sub>R</sub>   |      |      | 100  | μA   | V <sub>R</sub> =5V   |
| Luminous Intensity Matching Ratio | I <sub>v-m</sub> |      |      | 2:1  |      | I <sub>F</sub> =1mA  |

Note: Luminous intensity is measured with a light sensor and filter combination that approximates the CIE (Commision Internationale De L'Eclariage) eye-response curve.

## TYPICAL ELECTRICAL / OPTICAL CHARACTERISTIC CURVES

(25°C Ambient Temperature Unless Otherwise Noted)




Fig1. RELATIVE INTENSITY VS. WAVELENGTH




Fig2. RELATIVE LUMINOUS EFFICIENCY (LUMINOUS INTENSITY PER UNIT CURRENT) VS. PEAK CURRENT




Fig3. FORWARD CURRENT VS. FORWARD VOLTAGE




Fig4. RELATIVE LUMINOUS INTENSITY VS. FORWARD CURRENT




Fig5. MAX. ALLOWABLE DC CURRENT VS. AMBIENT TEMPERATURE.




Fig6. MAX. PEAK CURRENT VS. DUTY CYCLE % (REFRESH RATE 1KHz)

NOTE : JF=AlInGaP YELLOW ORANGE

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[LITEON:](#)

[LTD-4708JF](#)