



# IR Emitter and Detector Product Data Sheet

LTR-323DB

Spec No.: DS-50-94-0022

Effective Date: 06/10/2010

Revision: C

**LITE-ON DCC**


**RELEASE**

BNS-OD-FC001/A4

## FEATURES

- \* FAST SWITCHING TIME
- \* THE LENS IS FOR HIGH SENSITIVITY
- \* LOW JUNCTION CAPACITANCE
- \* HIGH CUT-OFF FREQUENCY

## PACKAGE DIMENSIONS



### NOTES:

1. All dimensions are in millimeters (inches).
2. Tolerance is  $\pm 0.25\text{mm} (.010\text{'})$  unless otherwise noted.
3. Protruded resin under flange is  $1.5\text{mm} (.059\text{'})$  max.
4. Lead spacing is measured where the leads emerge from the package.
5. Specifications are subject to change without notice.



# LITE-ON TECHNOLOGY CORPORATION.

Property of Lite-On Only

## ABSOLUTE MAXIMUM RATINGS AT TA=25°C

| PARAMETER  | MAXIMUM RATING      | UNIT |
|--|---------------------|------|
| Power Dissipation                                      | 150                 | mW   |
| Reverse Voltage  | 30                  | V    |
| Operating Temperature Range                            | -40°C to + 85°C     |      |
| Storage Temperature Range                              | -55°C to + 100°C    |      |
| Lead Soldering Temperature<br>[1.6mm(.063") From Body] | 260°C for 5 Seconds |      |

## ELECTRICAL OPTICAL CHARACTERISTICS AT TA=25°C

| PARAMETER                         | SYMBOL             | MIN. | TYP. | MAX. | UNIT | TEST CONDITION   |
|-----------------------------------|--------------------|------|------|------|------|--|
| Reverse Break Down Voltage        | V <sub>(BR)R</sub> | 30   |      |      | V    | I <sub>R</sub> = 100 μA<br>E <sub>e</sub> = 0mW/cm <sup>2</sup>            |
| Reverse Dark Current Voltage      | I <sub>D(R)</sub>  |      |      | 30   | nA   | V <sub>R</sub> = 10V<br>E <sub>e</sub> = 0mW/cm <sup>2</sup>               |
| Open Circuit Voltage              | V <sub>OC</sub>    |      | 350  |      | mV   | λ = 940nm<br>E <sub>e</sub> = 0.5mW/cm <sup>2</sup>                        |
| Rise Time                         | T <sub>r</sub>     |      | 50   |      | nsec | V <sub>R</sub> = 10V<br>λ = 940nm<br>R <sub>L</sub> = 1KΩ                  |
| Fall Time                         | T <sub>f</sub>     |      | 50   |      | nsec |  |
| Short Circuit Current             | I <sub>S</sub>     | 8    | 13   |      | μA   | V <sub>R</sub> = 5V<br>λ = 940nm<br>E <sub>e</sub> = 0.1mW/cm <sup>2</sup> |
| Total Capacitance                 | C <sub>T</sub>     |      | 25   |      | P    | V <sub>R</sub> = 3V<br>f = 1MHZ<br>E <sub>e</sub> = 0mW/cm <sup>2</sup>    |
| Wavelength of the Max Sensitivity | λ <sub>S MAX</sub> |      | 900  |      | nm   |  |

## TYPICAL ELECTRICAL / OPTICAL CHARACTERISTICS CURVES

(25°C Ambient Temperature Unless Otherwise Noted)




Fig.1 DARK CURRENT VS. REVERSE VOLTAGE  
TA=25° C, Ee=0mW/cm<sup>2</sup>




Fig.2 CAPACITANCE VS. REVERSE VOLTAGE  
F=1MHZ; Ee=0mW/cm<sup>2</sup>




Fig.3 PHOTOCURRENT VS. AMBIENT TEMPERATURE




Fig.4 DARK CURRENT AMBIENT TEMPERATURE  
VR=10, Ee=0mW/cm<sup>2</sup>

## TYPICAL ELECTRICAL / OPTICAL CHARACTERISTICS CURVES

(25°C Ambient Temperature Unless Otherwise Noted)




Fig.5 RELATIVE SPECTRAL SENSITIVITY VS WAVELENGTH




Fig.6 PHOTOCURRENT VS IRRADIANCE  $\lambda = 940$  nm




Fig.7 SENSITIVITY DIAGRAM




Fig.8 TOTAL POWER DISSIPATION VS AMBIENT TEMPERATURE

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Lite-On:](#)

[LTR-323DB](#)