HB-2X2-O

~20° + 115° oval beam for aisle lighting

TECHNICAL SPECIFICATIONS:

Dimensions	50.0 mm
Height	10.6 mm
Fastening	glue, pin, screw
ROHS compliant	yes

MATERIAL SPECIFICATIONS:

Component	Type	Material	Colour	Finish
HB-2X2-O	Multi-lens	PMMA	clear	

ORDERING INFORMATION:

Component	Qty in box	MOQ	MPQ	Box weight (kg)
C13749_HB-2X2-O » Box size: 480 x 280 x 300 mm	800	160	160	10.4

LEDiL is a registered trademark of LEDiL Oy in the European Union, USA, and certain other countries.


50
25.4
Ø3.2
50
1.2
2.5
10.6
25.4
Ø2
Led position
45
center to center
25.4
Oval beam direction
Ø2
Ø3.2
Isometric view
INDEX
PART NO
DESCRIPTION
MATERIAL
COLOUR
1
HB-2X2-0
Tolerances if not otherwise shown
According to DIN ISO 2768-1
Linear measures:
Up to 30mm class B, otherwise class C.
According to DIN ISO 2768-2
Form and position: class L
Ledil Oy
Salorankatu 10
FIN 24240 SALO
Finland
THIRD ANGLE PROJECTION:
DRAWING TITLE
HB-2X2-0
This drawing is the property of LEDiL Oy. It may not be reproduced, copied or communicated without a written agreement with LEDiL Oy.
SIZE
A3
PART NUMBER
-
SCALE 3:2
WEIGHT -
SHEET 1/1

PHOTOMETRIC DATA (MEASURED):

COMET ELECTRONICS

LED	QUICK FLUX XTP 2x4 xxx LS G5
FWHM	21.0 + 111.0°
Efficiency	94 %
Peak intensity	1.3 cd/lm
LEDs/each optic	1
Light colour	White
Required components:	





COMET ELECTRONICS

LED	QUICK FLUX XTP 2x6 xxx LS G5
FWHM	22.0 + 111.0°
Efficiency	94 %
Peak intensity	1.2 cd/lm
LEDs/each optic	1
Light colour	White
Required components:	





CREE

LED	XD16
FWHM	29.0 + 116.0°
Efficiency	94 %
Peak intensity	1 cd/lm
LEDs/each optic	4
Light colour	White
Required components:	



CREE

LED	XD16
FWHM	19.0 + 127.0°
Efficiency	93 %
Peak intensity	1.4 cd/lm
LEDs/each optic	1
Light colour	White
Required components:	





LEDiL is a registered trademark of LEDiL Oy in the European Union, USA, and certain other countries.

PHOTOMETRIC DATA (MEASURED):

CREE

LED	XHP35 HD
FWHM	29.0 + 117.0°
Efficiency	94 %
Peak intensity	0.9 cd/lm
LEDs/each optic	1
Light colour	White

Required components:



CREE

LED	XM-L
FWHM	28.0 + 108.0°
Efficiency	94 %
Peak intensity	1 cd/lm
LEDs/each optic	1
Light colour	White

Required components:





CREE

LED	XM-L2
FWHM	30.0 + 106.0°
Efficiency	94 %
Peak intensity	1 cd/lm
LEDs/each optic	1
Light colour	White

Required components:



CREE

LED	XP-G
FWHM	26.0 + 115.0°
Efficiency	94 %
Peak intensity	1.1 cd/lm
LEDs/each optic	1
Light colour	White

Required components:



LEDiL is a registered trademark of LEDiL Oy in the European Union, USA, and certain other countries.

PHOTOMETRIC DATA (MEASURED):

CREE

LED	XP-G2
FWHM	27.0 + 112.0°
Efficiency	94 %
Peak intensity	1.2 cd/lm
LEDs/each optic	1
Light colour	White

Required components:





CREE

LED	XP-L HD
FWHM	29.0 + 117.0°
Efficiency	94 %
Peak intensity	0.9 cd/lm
LEDs/each optic	1
Light colour	White

Required components:





CREE

LED	XP-L HI
FWHM	25.0 + 123.0°
Efficiency	94 %
Peak intensity	1.1 cd/lm
LEDs/each optic	1
Light colour	White

Required components:



CREE

LED	XP-L2
FWHM	28.0 + 117.0°
Efficiency	94 %
Peak intensity	0.9 cd/lm
LEDs/each optic	1
Light colour	White

Required components:



LEDiL is a registered trademark of LEDiL Oy in the European Union, USA, and certain other countries.

PHOTOMETRIC DATA (MEASURED):

LG Innotek

LED	H35C1 (LEMWA33)
FWHM	23.0 + 110.0°
Efficiency	94 %
Peak intensity	1.2 cd/lm
LEDs/each optic	1
Light colour	White
Required components:	





LUMILEDS

LED	LUXEON 5050 Round LES
FWHM	29.0 + 114.0°
Efficiency	94 %
Peak intensity	0.9 cd/lm
LEDs/each optic	1
Light colour	White
Required components:	



LUMILEDS

LED	LUXEON MZ
FWHM	28.0 + 103.0°
Efficiency	94 %
Peak intensity	1.1 cd/lm
LEDs/each optic	1
Light colour	White
Required components:	



LUMILEDS

LED	LUXEON R
FWHM	25.0 + 105.0°
Efficiency	94 %
Peak intensity	1.2 cd/lm
LEDs/each optic	1
Light colour	White
Required components:	



LEDiL is a registered trademark of LEDiL Oy in the European Union, USA, and certain other countries.

PHOTOMETRIC DATA (MEASURED):

LUMILEDS

LED	LUXEON Rebel ES
FWHM	25.0 + 106.0°
Efficiency	94 %
Peak intensity	1.2 cd/lm
LEDs/each optic	1
Light colour	White
Required components:	





LUMILEDS

LED	LUXEON T
FWHM	26.0 + 110.0°
Efficiency	94 %
Peak intensity	1.2 cd/lm
LEDs/each optic	1
Light colour	White
Required components:	





LUMILEDS

LED	LUXEON TX
FWHM	24.0 + 118.0°
Efficiency	94 %
Peak intensity	1.1 cd/lm
LEDs/each optic	1
Light colour	White
Required components:	





LUMILEDS

LED	LUXEON V
FWHM	26.0 + 108.0°
Efficiency	94 %
Peak intensity	1 cd/lm
LEDs/each optic	1
Light colour	White
Required components:	



LEDiL is a registered trademark of LEDiL Oy in the European Union, USA, and certain other countries.

PHOTOMETRIC DATA (MEASURED):

LUMINUS

LED	SST-10-B130
FWHM	18.0 + 104.0°
Efficiency	97 %
Peak intensity	1.6 cd/lm
LEDs/each optic	1
Light colour	Deep Red
Required components:	



NICHIA

LED	NCSxx19B
FWHM	23.0 + 113.0°
Efficiency	94 %
Peak intensity	1.4 cd/lm
LEDs/each optic	1
Light colour	White
Required components:	





NICHIA

LED	NVSW219D
FWHM	25.0 + 107.0°
Efficiency	94 %
Peak intensity	1.2 cd/lm
LEDs/each optic	1
Light colour	White
Required components:	



NICHIA

LED	NVSW319B
FWHM	25.0 + 113.0°
Efficiency	94 %
Peak intensity	1.1 cd/lm
LEDs/each optic	1
Light colour	White
Required components:	



LEDiL is a registered trademark of LEDiL Oy in the European Union, USA, and certain other countries.

PHOTOMETRIC DATA (MEASURED):

NICHIA

LED	NVSW3x9A
FWHM	25.0 + 134.0°
Efficiency	93 %
Peak intensity	0.4 cd/lm
LEDs/each optic	1
Light colour	White
Required components:	



NICHIA

LED	NVSW3x9A
FWHM	24.0 + 119.0°
Efficiency	94 %
Peak intensity	1.1 cd/lm
LEDs/each optic	1
Light colour	White
Required components:	



NICHIA

LED	NVSxE21A
FWHM	17.0 + 125.0°
Efficiency	94 %
Peak intensity	1.7 cd/lm
LEDs/each optic	1
Light colour	White
Required components:	





NICHIA

LED	NVSxx19A
FWHM	24.0 + 105.0°
Efficiency	94 %
Peak intensity	1.2 cd/lm
LEDs/each optic	1
Light colour	White
Required components:	





LEDiL is a registered trademark of LEDiL Oy in the European Union, USA, and certain other countries.

PHOTOMETRIC DATA (MEASURED):

NICHIA

LED	NVSxx19B/NVSxx19C
FWHM	26.0 + 108.0°
Efficiency	94 %
Peak intensity	1.2 cd/lm
LEDs/each optic	1
Light colour	White
Required components:	



NICHIA

LED	NWSx229A
FWHM	27.0 + 118.0°
Efficiency	94 %
Peak intensity	1 cd/lm
LEDs/each optic	1
Light colour	White
Required components:	



OSRAM

LED	PrevaLED Brick HP 2x8
FWHM	23.0 + 111.0°
Efficiency	94 %
Peak intensity	1.3 cd/lm
LEDs/each optic	1
Light colour	White
Required components:	





OSRAM
Opto Semiconductors

LED	OSLON Square CSSRM2/CSSRM3
FWHM	23.0 + 111.0°
Efficiency	94 %
Peak intensity	1.3 cd/lm
LEDs/each optic	1
Light colour	White
Required components:	





LEDiL is a registered trademark of LEDiL Oy in the European Union, USA, and certain other countries.

PHOTOMETRIC DATA (MEASURED):

OSRAM
Opto Semiconductors

LED	OSLON Square PC
FWHM	25.0 + 124.0°
Efficiency	91 %
Peak intensity	1.1 cd/lm
LEDs/each optic	1
Light colour	White
Required components:	



PHILIPS

LED	Fortimo FastFlex LED 2x8 DA G4
FWHM	21.0 + 108.0°
Efficiency	94 %
Peak intensity	1.3 cd/lm
LEDs/each optic	1
Light colour	White
Required components:	





SAMSUNG

LED	HiLOM RH16 (LH351C)
FWHM	23.0 + 106.0°
Efficiency	94 %
Peak intensity	1.2 cd/lm
LEDs/each optic	1
Light colour	White
Required components:	



SAMSUNG

LED	LH351B
FWHM	23.0 + 113.0°
Efficiency	94 %
Peak intensity	1.2 cd/lm
LEDs/each optic	1
Light colour	White
Required components:	



LEDiL is a registered trademark of LEDiL Oy in the European Union, USA, and certain other countries.

PHOTOMETRIC DATA (MEASURED):

SAMSUNG

LED	LH351C
FWHM	24.0 + 111.0°
Efficiency	94 %
Peak intensity	1.1 cd/lm
LEDs/each optic	1
Light colour	White
Required components:	





SAMSUNG

LED	LH351D
FWHM	27.0 + 116.0°
Efficiency	94 %
Peak intensity	1 cd/lm
LEDs/each optic	1
Light colour	White
Required components:	



SAMSUNG

LED	LH351Z
FWHM	26.0 + 117.0°
Efficiency	94 %
Peak intensity	1.1 cd/lm
LEDs/each optic	1
Light colour	White
Required components:	



SEOUL SEMICONDUCTOR

LED	Z5M3
FWHM	23.0 + 113.0°
Efficiency	94 %
Peak intensity	1.1 cd/lm
LEDs/each optic	1
Light colour	White
Required components:	





LEDiL is a registered trademark of LEDiL Oy in the European Union, USA, and certain other countries.

PHOTOMETRIC DATA (MEASURED):

SEOUL SEMICONDUCTOR

LED	Z5M4
FWHM	22.0 + 97.0°
Efficiency	98 %
Peak intensity	1.3 cd/lm
LEDs/each optic	1
Light colour	White

Required components:





SEOUL SEMICONDUCTOR

LED	Z8Y22
FWHM	21.0 + 121.0°
Efficiency	94 %
Peak intensity	1.2 cd/lm
LEDs/each optic	1
Light colour	White

Required components:





SEOUL SEMICONDUCTOR

LED	Z8Y22P
FWHM	23.0 + 121.0°
Efficiency	94 %
Peak intensity	1.1 cd/lm
LEDs/each optic	1
Light colour	White

Required components:



TOSHIBA
Leading Innovation

LED	TL1L4
FWHM	24.0 + 119.0°
Efficiency	89 %
Peak intensity	1.1 cd/lm
LEDs/each optic	1
Light colour	White

Required components:



LEDiL is a registered trademark of LEDiL Oy in the European Union, USA, and certain other countries.

PHOTOMETRIC DATA (MEASURED):

TRIDONIC

LED	RLE 2x4 2000lm HP EXC2 OTD
FWHM	22.0 + 113.0°
Efficiency	94 %
Peak intensity	1.3 cd/lm
LEDs/each optic	1
Light colour	White
Required components:	

TRIDONIC

LED	RLE 2x8 4000lm HP EXC2 OTD
FWHM	22.0 + 113.0°
Efficiency	94 %
Peak intensity	1.3 cd/lm
LEDs/each optic	1
Light colour	White
Required components:	



TRIDONIC

LED	RLE G1 49x121mm 2000lm xxx EXC OTD
FWHM	23.0 + 104.0°
Efficiency	94 %
Peak intensity	1.3 cd/lm
LEDs/each optic	1
Light colour	White
Required components:	



TRIDONIC

LED	RLE G1 49x133mm 2000lm xxx EXC OTD
FWHM	23.0 + 104.0°
Efficiency	94 %
Peak intensity	1.3 cd/lm
LEDs/each optic	1
Light colour	White
Required components:	



LEDiL is a registered trademark of LEDiL Oy in the European Union, USA, and certain other countries.

PHOTOMETRIC DATA (MEASURED):

TRIDONIC

LED	RLE G1 49x223mm 4000lm xxx EXC OTD
FWHM	23.0 + 104.0°
Efficiency	94 %
Peak intensity	1.3 cd/lm
LEDs/each optic	1
Light colour	White

Required components:





TRIDONIC

LED	RLE G1 49x245mm 4000lm xxx EXC OTD
FWHM	23.0 + 104.0°
Efficiency	94 %
Peak intensity	1.3 cd/lm
LEDs/each optic	1
Light colour	White

Required components:



LEDiL is a registered trademark of LEDiL Oy in the European Union, USA, and certain other countries.

PHOTOMETRIC DATA (SIMULATED):

CREE

LED	J Series 5050
FWHM	30.0 + 97.0°
Efficiency	94 %
Peak intensity	1 cd/lm
LEDs/each optic	1
Light colour	White

Required components:



CREE

LED	XHP35 HI
FWHM	101.0 + 27.0°
Efficiency	94 %
Peak intensity	1.2 cd/lm
LEDs/each optic	1
Light colour	White

Required components:



CREE

LED	XP-E2
FWHM	93.0 + 18.0°
Efficiency	94 %
Peak intensity	1.6 cd/lm
LEDs/each optic	1
Light colour	White

Required components:



CREE

LED	XP-G2
FWHM	21.0 + 98.0°
Efficiency	91 %
Peak intensity	1.2 cd/lm
LEDs/each optic	1
Light colour	White

Required components:

Transparent protective cover



LEDiL is a registered trademark of LEDiL Oy in the European Union, USA, and certain other countries.

PHOTOMETRIC DATA (SIMULATED):

CREE

LED	XP-G2 HE
FWHM	28.0 + 103.0°
Efficiency	94 %
Peak intensity	1 cd/lm
LEDs/each optic	1
Light colour	White
Required components:	



CREE

LED	XP-G3
FWHM	103.0 + 29.0°
Efficiency	94 %
Peak intensity	1.1 cd/lm
LEDs/each optic	1
Light colour	White
Required components:	



CREE

LED	XQ-E HI
FWHM	96.0 + 14.0°
Efficiency	%
LEDs/each optic	1
Light colour	White
Required components:	

CREE

LED	XT-E HE
FWHM	100.0 + 24.0°
Efficiency	94 %
LEDs/each optic	1
Light colour	White
Required components:	



LEDiL is a registered trademark of LEDiL Oy in the European Union, USA, and certain other countries.

PHOTOMETRIC DATA (SIMULATED):

LUMILEDS

LED	LUXEON 5050 Round LES
FWHM	30.0 + 96.0°
Efficiency	88 %
Peak intensity	0.9 cd/lm
LEDs/each optic	1
Light colour	White

Required components:

Transparent protective cover



LUMILEDS

LED	LUXEON 5050 Square LES
FWHM	30.0 + 98.0°
Efficiency	95 %
Peak intensity	0.9 cd/lm
LEDs/each optic	1
Light colour	White

Required components:



NICHIA

LED	NV4WB35AM
FWHM	28.0 + 100.0°
Efficiency	95 %
Peak intensity	1 cd/lm
LEDs/each optic	1
Light colour	White

Required components:



OSRAM
Opto Semiconductors

LED	Duris S8
FWHM	36.0 + 98.0°
Efficiency	87 %
Peak intensity	0.7 cd/lm
LEDs/each optic	1
Light colour	White

Required components:

Transparent protective cover



LEDiL is a registered trademark of LEDiL Oy in the European Union, USA, and certain other countries.

PHOTOMETRIC DATA (SIMULATED):

OSRAM Opto Semiconductors

LED	OSCONIQ P 3030
FWHM	14.0 + 92.0°
Efficiency	95 %
Peak intensity	1.6 cd/lm
LEDs/each optic	1
Light colour	White
Required components:	



OSRAM Opto Semiconductors

LED	OSCONIQ P 3737 (2W version)
FWHM	99.0 + 19.0°
Efficiency	94 %
Peak intensity	1.3 cd/lm
LEDs/each optic	1
Light colour	White
Required components:	



OSRAM Opto Semiconductors

LED	OSCONIQ P 3737 (3W version)
FWHM	100.0 + 30.0°
Efficiency	94 %
Peak intensity	1 cd/lm
LEDs/each optic	1
Light colour	White
Required components:	



OSRAM Opto Semiconductors

LED	OSCONIQ P 3737 Flat
FWHM	22.0 + 98.0°
Efficiency	96 %
Peak intensity	1.2 cd/lm
LEDs/each optic	1
Light colour	White
Required components:	



LEDiL is a registered trademark of LEDiL Oy in the European Union, USA, and certain other countries.

PHOTOMETRIC DATA (SIMULATED):

PHILIPS

LED	Fortimo FastFlex LED 2x8 DAX G4
FWHM	103.0 + 29.0°
Efficiency	94 %
Peak intensity	1.1 cd/lm
LEDs/each optic	1
Light colour	White
Required components:	



SEOUL SEMICONDUCTOR

LED	SEOUL DC 5050 6V
FWHM	33.0 + 98.0°
Efficiency	94 %
Peak intensity	0.9 cd/lm
LEDs/each optic	1
Light colour	White
Required components:	



SEOUL SEMICONDUCTOR

LED	Z5M1/Z5M2
FWHM	22.0 + 97.0°
Efficiency	94 %
Peak intensity	1.2 cd/lm
LEDs/each optic	1
Light colour	White
Required components:	



SEOUL SEMICONDUCTOR

LED	Z8Y22T
FWHM	21.0 + 96.0°
Efficiency	94 %
Peak intensity	1.2 cd/lm
LEDs/each optic	1
Light colour	White
Required components:	



LEDiL is a registered trademark of LEDiL Oy in the European Union, USA, and certain other countries.

GENERAL INFORMATION:

NOTE: The typical beam angle will be changed by different color, chip size and chip position tolerance. The typical total beam angle is the full angle measured where the luminous intensity is half of the peak value.

MATERIALS:

As part of our continuous research and improvement processes, and to ensure the best possible quality and availability of our products, LEDiL reserves the right to change material grades without notice.

PRODUCT DATA USER AGREEMENT AND DISCLAIMER:

The measured data in the provided downloadable LEDiL Product Datasheets and Mechanical 2D-Drawings is rounded and provided as reference for planning. LEDiL Oy's optical specifications have been verified by conducting performance testing of the products in accordance with the company's quality system. The reported data are averaged results of multiple measurements with typical variation. LEDiL Oy reserves the right to without prior notification make changes and improvements to its products.

LEDiL Oy assumes neither warranty, nor guarantee nor any other liability of any kind for the contents and correctness of the provided data. The provided data has been generated with highest diligence but the provided data may in reality not represent the complete possible variation range of all intrinsic parameters. Therefore, in certain cases a deviation from the provided data could occur.

LEDiL Oy reserves the right to undertake technical changes of its products without further notification which could lead to changes in the provided data. LEDiL Oy assumes no liability of any kind for the possible deviation from any provided data or any other damage resulting from the usage of the provided data.

The user agrees to this disclaimer and user agreement with the download or usage of the provided files.

LEDiL Oy
Joensuunkatu 13
FI-24240 SALO
Finland

LEDiL Inc.
228 West Page Street
Suite D
Sycamore IL 60178
USA

Local sales and technical support
www.ledil.com/
where_to_buy

Shipping locations
Salo, Finland
Hong Kong, China

Distribution Partners
www.ledil.com/
where_to_buy

LEDiL is a registered trademark of LEDiL Oy in the European Union, USA, and certain other countries.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Ledil:
C13749_HB-2X2-O