

ELLA-30-M

~28° wide beam. Assembly with black holder.

SPECIFICATION:

Dimensions	Ø 32.0
Height	20 mm
Fastening	tape
ROHS compliant	yes ⓘ


MATERIALS:

Component	Type	Material	Colour	Finish	Length (mm)
ELLA-30-M	Reflector	HTPC	metal		
OLGA-HLD	Holder	PC	black		
SPUTNIK-TAPE3	Tape	Acrylic foam tape	black		



ORDERING INFORMATION:

Component	Qty in box	MOQ	MPQ	Box weight (kg)
CA17281_ELLA-30-M » Box size: 480 x 280 x 300 mm	792	264	66	5.6




See also our general installation guide: www.ledil.com/installation_guide

OPTICAL RESULTS (MEASURED):




LED XHP35 HD
FWHM / FWTM 17.0° / 33.0°
Efficiency 89 %
Peak intensity 6.4 cd/lm
LEDs/each optic 1
Light colour/type White
Required components:



Light distribution files




LED XP-L2
FWHM / FWTM 16.0° / 34.0°
Efficiency 87 %
Peak intensity 6.3 cd/lm
LEDs/each optic 1
Light colour/type White
Required components:



Light distribution files



LED LUXEON 5050 Square LES
FWHM / FWTM 19.0° / 37.0°
Efficiency 91 %
Peak intensity 5.5 cd/lm
LEDs/each optic 1
Light colour/type White
Required components:




Light distribution files

OPTICAL RESULTS (MEASURED):





LED NFMW48xA
 FWHM / FWTM 19.0° / 37.0°
 Efficiency 91 %
 Peak intensity 5.4 cd/lm
 LEDs/each optic 1
 Light colour/type White
 Required components:



Light distribution files





LED Duris S8
 FWHM / FWTM 21.0° / 40.0°
 Efficiency 91 %
 Peak intensity 4.8 cd/lm
 LEDs/each optic 1
 Light colour/type White
 Required components:



Light distribution files



LED WICOP 5050
 FWHM / FWTM 24.0° / 43.0°
 Efficiency 86 %
 Peak intensity 3.8 cd/lm
 LEDs/each optic 1
 Light colour/type White
 Required components:




Light distribution files

OPTICAL RESULTS (SIMULATED):




LED XHP35.2 HD
FWHM / FWTM 21.0° / 39.0°
Efficiency 85 %
Peak intensity 1.4 cd/lm
LEDs/each optic 1
Light colour/type White
Required components:



Light distribution files




LED XHP50.3 HD
FWHM / FWTM 20.0° / 40.0°
Efficiency 91 %
Peak intensity 4.7 cd/lm
LEDs/each optic 1
Light colour/type White
Required components:



Light distribution files



LED XP-G4
FWHM / FWTM 14.0° / 31.0°
Efficiency 91 %
Peak intensity 7.5 cd/lm
LEDs/each optic 1
Light colour/type White
Required components:




Light distribution files

OPTICAL RESULTS (SIMULATED):




LED XP-G4 HI
FWHM / FWTM 12.0° / 30.0°
Efficiency 87 %
Peak intensity 8.6 cd/Im
LEDs/each optic 1
Light colour/type White
Required components:



Light distribution files




LED XP-L2
FWHM / FWTM 18.0° / 37.0°
Efficiency 88 %
Peak intensity 5.2 cd/Im
LEDs/each optic 1
Light colour/type White
Required components:



Light distribution files



LED LUXEON 5050 Round LES
FWHM / FWTM 18.0° / 38.0°
Efficiency 89 %
Peak intensity 5.3 cd/Im
LEDs/each optic 1
Light colour/type White
Required components:




Light distribution files

OPTICAL RESULTS (SIMULATED):





LED	LUXEON 5050 Square LES
FWHM / FWTM	19.0° / 39.0°
Efficiency	91 %
Peak intensity	5 cd/lm
LEDs/each optic	1
Light colour/type	White
Required components:	



Light distribution files




LED	SST-25-W
FWHM / FWTM	13.0° / 30.0°
Efficiency	93 %
Peak intensity	8.7 cd/lm
LEDs/each optic	1
Light colour/type	White
Required components:	



Light distribution files



LED	NFMW48xA
FWHM / FWTM	21.0° / 41.0°
Efficiency	90 %
Peak intensity	4.6 cd/lm
LEDs/each optic	1
Light colour/type	White
Required components:	




Light distribution files

OPTICAL RESULTS (SIMULATED):




LED NV4WB35AM
 FWHM / FWTM 16.0° / 34.0°
 Efficiency 89 %
 Peak intensity 6.4 cd/lm
 LEDs/each optic 1
 Light colour/type White
 Required components:



Light distribution files



LED Duris S8
 FWHM / FWTM 22.0° / 43.0°
 Efficiency 90 %
 Peak intensity 4.3 cd/lm
 LEDs/each optic 1
 Light colour/type White
 Required components:



Light distribution files

GENERAL INFORMATION:

NOTE: The typical beam angle will be changed by different color, chip size and chip position tolerance. The typical total beam angle is the full angle measured where the luminous intensity is half of the peak value.

MATERIALS:

As part of our continuous research and improvement processes, and to ensure the best possible quality and availability of our products, LEDiL reserves the right to change material grades without notice.

PRODUCT DATA USER AGREEMENT AND DISCLAIMER:

The measured data in the provided downloadable LEDiL Product Datasheets and Mechanical 2D-Drawings is rounded and provided as reference for planning. LEDiL Oy's optical specifications have been verified by conducting performance testing of the products in accordance with the company's quality system. The reported data are averaged results of multiple measurements with typical variation. LEDiL Oy reserves the right to without prior notification make changes and improvements to its products.

LEDiL Oy assumes neither warranty, nor guarantee nor any other liability of any kind for the contents and correctness of the provided data. The provided data has been generated with highest diligence but the provided data may in reality not represent the complete possible variation range of all intrinsic parameters. Therefore, in certain cases a deviation from the provided data could occur.

LEDiL Oy reserves the right to undertake technical changes of its products without further notification which could lead to changes in the provided data. LEDiL Oy assumes no liability of any kind for the possible deviation from any provided data or any other damage resulting from the usage of the provided data.

The user agrees to this disclaimer and user agreement with the download or usage of the provided files.

LEDiL Oy

Joensuunkatu 7
FI-24240 SALO
Finland

LEDiL Inc.

228 West Page Street
Suite D
Sycamore IL 60178
USA

Ledil Optics Technology (Shenzhen) Co., Ltd.

405 , Block B
Casic Motor Building
Shenzhen 518057
P.R.CHINA

Local sales and technical support

[www.ledil.com/
where_to_buy](http://www.ledil.com/where_to_buy)

Shipping locations

Poznan, Poland
Hong Kong, China

Distribution Partners

[www.ledil.com/
where_to_buy](http://www.ledil.com/where_to_buy)

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Ledil:](#)

[CA17281_ELLA-30-M](#)