

Data Sheet

LL01CR-CSS1226L06

▶ LED Solution Provider *XLamp XP-G2*

■ Features & Typical Applications

- Wall washer Lighting
- Available with 1 beam angle
- Optimized Uniformity
- Lens without Holder

■ Table of Contents


General Information & Product Nomenclature.....	P.2
Optical Specifications	P.3
Mechanical Specifications	P.4
Package Specifications.....	P.5

LL01CR-CSS1226L06

General Information

- Lens Material : PMMA 8N
- Operating Temperature range -40°C~+70°C(upper limit +80°C).
- Storage Temperature range -40°C~+70°C(upper limit +80°C).
 * Average transmittance in visible spectrum 400nm~700nm>90%.
- Usage and Maintenance:
 1. If necessary, clean lenses with mild soap, water and soft cloth.
 2. Never use any commercial cleaning solvents on lenses, like alcohol.
 3. Please handle or install lenses with wearing gloves, skin oils may damage lens or its optical characteristic.

Product Nomenclature



LL01CR-CSS1226L06


Optical Specifications



► LED Solution Provider *Xlamp XP-G2*



Note: (1) All the results of analysis are based on 0 degrees of elevation.
 (2) Tolerance: $\pm 10\%$.
 (3) Led Luminous Flux(lm): 121($\pm 5\%$).



LL01CR-CSS1226L06






Mechanical Specification

1. Fixing method


Note: (1) All dimensions are in mm.
 (2) All tolerance are ± 0.15 mm unless otherwise specified.

☒ Glue
 ☐ Screw
 ☐ Tape
 ☐ Fixing-ring
 ☐ Frame

2. Lens dimension




3. Lens + Leds assembly instruction



4. Holder dimension


5. View assembly lens with LED:



LL01CR-CSS1226L06

Package Specifications



Item	Quantity	Total	Size(L*W*H)	G.W
plastic box	80 pcs/plastic box	80 pcs	32*29*2.2 cm	3.9g
outer box	12 plastic box/outer box	960 pcs	35*31*21 cm	



LL-0123



80 pcs/plastic box



960 pcs/outer box



Note:

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[LedLink Optics:](#)

[LL01CR-CSS1226L06](#)