





Datasheet

LL01ED-FGxxL06-M2

Available Distribution




LED



Recommad Applications



General Information




- Lens Material PMMA 8N
- Operating Temperature -40°C~+70°C
- UL Flammability HB @1.5mm
- UL RTI Elec 90°C @1.5mm
- Light Transmission Rate 400nm~900nm > 90%
- ✓ If necessary, Clean lenses with mild soap, water and soft cloth.
- ⚠ Never use any commercial cleaning solvents on lenses, like alcohol.
- ⚠ Please handle or install lenses with wearing gloves, skin oils may damage lens or its optical characteristic.

Dimensions

Part Number	Diameter	Height
LL01ED-FGxxL06	Ø43.8	24.22
LL01ED-FGxxL06-M2	Ø46	27.1

*All dimensions are in millimeters.

Packaging Details (SPQ)



Accessories



- Available with Holder LL01ED0010Hx


Mechanical Specification

*All dimensions are in millimeters.

Lens Dimension




LL01ED-FG××L06



Holder Dimension



LL01EDOO10H×




Assembly Instruction

Fixing Method

Part No LL01ED-FG××L06-M2
Holder LL01EDOO10H×



Luminaire
Accessories




Assembly Instruction

Fixing Method

Part No LL01ED-FG××L06-M2
Holder LL01EDOO10H×



Luminaire
Accessories




Assembly Instruction

Fixing Method

Part No LL01ED-FG××L06



Luminaire
Accessories




Assembly Instruction

Fixing Method


Part No LL01ED-FG××L06



Luminaire
Accessories



Photometric Distribution



Details by LED

Part No	Holder	LED Package Size	LED
LL01ED-FGxxL06	-	LES Ø8.7 / 3535	  CREE XPG NICHIA NFCWL036B
LL01ED-FGxxL06-M2	 LL01ED0010Hx	LES Ø6.3~Ø11.7 5050 / 7070 / 9090	      CITIZEN CLU028 CREE MHD-G CREE XML2 CREE MT-G2 CREE XHP50 GEN2 CREE XHP70B    LUMINUS CXM-6 LUMINUS CXM-9 LUMINUS CXM-11

LED	Part No	FWHM	cd / lm	IES
 CITIZEN CLU028	LL01ED-FG10L06-M2	18°	4.0	
	LL01ED-FG38L06-M2	20°	3.2	
 CREE MHD-G	LL01ED-FG10L06-M2	16°	5.2	
	LL01ED-FG38L06-M2	17°	4.2	
 CREE MT-G2	LL01ED-FG10L06-M2	15°	6.5	
	LL01ED-FG38L06-M2	20°	3.6	
 CREE XHP50 GEN2	LL01ED-FG10L06-M2	11°	10.2	
	LL01ED-FG38L06-M2	14°	6.3	
 CREE XHP70B	LL01ED-FG10L06-M2	16°	6.2	
	LL01ED-FG38L06-M2	19°	3.1	
 CREE XML2	LL01ED-FG10L06-M2	8°	16.7	
	LL01ED-FG38L06-M2	12°	8.7	
 CREE XPG	LL01ED-FG10L06	6°	23.8	
	LL01ED-FG38L06	12°	10.1	
 LUMINUS CXM-6	LL01ED-FG10L06-M2	16°	4.7	
	LL01ED-FG38L06-M2	20°	3.0	

LED	Part No	FWHM	cd / lm	IES
 LUMINUS CXM-9	LL01ED-FG10L06-M2	19°	4.2	
	LL01ED-FG38L06-M2	24°	2.6	
 LUMINUS CXM-11	LL01ED-FG10L06-M2	21°	3.2	
	LL01ED-FG38L06-M2	24°	2.2	
 NICHIA NFCWL036B	LL01ED-FG10L06	18°	4.7	
	LL01ED-FG38L06	21°	3.2	

Product Nomenclature

LL 01 ED -FG 10 L06 -M2

Diagram illustrating the structure of a lens code: LL 01 ED -FG 10 L06 -M2. The code is broken down into segments with labels above and below:

- LL: Ledlink
- 01: Led Type
- ED: Lens Angle
- FG: Holder
- 10: Lens Dot Number
- L06: Serial Number
- M2: Type of Material

Ledlink Optics, Inc
Taiwan HQ

15F, No.655, Bannan Rd., Chung-Ho Dist.,
New Taipei City, Taiwan 235

Ledlink Optics (Dongguan) Co., Ltd
Dongguan Factory

No.5, TianKeng Industrial Dist., HengLi Town, DongGuan City,
GuangDong Province, China 523478

Ledlink Optics (Yangzhou) Co., Ltd
Yangzhou Factory

No.180, LinJiang Rd., YangZhou City, Jiangsu Province, China 225009

www.ledlink-optics.com

service@ledlink-optics.com



Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[LedLink Optics:](#)

[LL01ED-FG10L06-M2](#) [LL01ED-FG38L06-M2](#) [LL01ED-FG10L06](#) [LL01ED-FG38L06](#)