




Datasheet

LL01ZZ-DUUxxL02-M2

Available Distribution



LED



Recommend Applications



General Information




- Lens Material PC LEV1700KL
- Operating Temperature -40°C~+110°C
- UL Flammability V-2 @ 1.5mm
- UL RTI Elec 130°C @ 1.5mm
- Light Transmission Rate 400nm~900nm > 90%
- ✓ If necessary, Clean lenses with mild soap, water and soft cloth.
- ⚠ Never use any commercial cleaning solvents on lenses, like alcohol.
- ⚠ Please handle or install lenses with wearing gloves, skin oils may damage lens or its optical characteristic.

Dimensions

Part Number	Diameter	Height
LL01ZZ-DUUxxL02	Ø43.5	12.2
LL01ZZ-DUUxxL02-M2	Ø45	14.7

*All dimensions are in millimeters.

Packaging Details (SPQ)



Accessories




- Available with Holder LL01ZZV120H2
- Available with Connector LL01A00CWJB2 (CREE CXA13xx) LL01A00CXHB2 (CITIZEN CLU701)

Mechanical Specification

*All dimensions are in millimeters.


Lens Dimension

LL01ZZ-DUU×L02




Holder Dimension

LL01ZZV120H2



Connector Dimension

LL01A00CWJB2




Assembly Instruction

Fixing Method

Part No LL01ZZ-DUU×L02-M2
Holder LL01ZZV120H2
Connector LL01A00CWJB2
LED CREE CXA13xx




Luminaire Accessories



Connector Dimension

LL01A00CXHB2




Assembly Instruction

Fixing Method

Part No LL01ZZ-DUU×L02-M2
Holder LL01ZZV120H2
Connector LL01A00CXHB2
LED CITIZEN CLU701



Luminaire Accessories




Assembly Instruction

Fixing Method

Part No LL01ZZ-DUU××L02
LED XICATO XOB-14.5mm




Luminaire
Accessories



Place the bottom of the lens above
heat-sink with distance 3.5 mm.

Photometric Distribution



Details by LED

Part No	Holder	Connector	LED Size	LED
LL01ZZ-DUUxxL02	-	-	LES Ø14.5	 XICATO XOB-14.5mm
LL01ZZ-DUUxxL02-M2	 LL01ZZZV120H2	 LL01A00CWJB2	LES Ø6	 CREE CXA13xx
		 LL01A00CXHB2	LES Ø6	 CITIZEN CLU701

LED	Part No	FWHM	cd / lm	IES
 CITIZEN CLU701	LL01ZZ-DUU15L02-M2	13°	6.4	
	LL01ZZ-DUU24L02-M2	17°	4.8	
	LL01ZZ-DUU38L02-M2	35°	1.8	
	LL01ZZ-DUU60L02-M2	56°	0.9	
 CREE CXA13xx	LL01ZZ-DUU15L02-M2	11°	9.8	
	LL01ZZ-DUU24L02-M2	20°	4.1	
	LL01ZZ-DUU38L02-M2	35°	1.8	
	LL01ZZ-DUU60L02-M2	56°	0.9	
 XICATO XOB-14.5mm	LL01ZZ-DUU15L02	27°	2.3	
	LL01ZZ-DUU24L02	32°	1.8	
	LL01ZZ-DUU38L02	53°	0.9	
	LL01ZZ-DUU60L02	-	-	-

Product Nomenclature

Ledlink Led Type Lens Angle Holder
LL 01 ZZ- DUU 15 L02- M2
Lens Dot Number Serial Number Type of Material

Ledlink Optics, Inc

Taiwan HQ

15F, No.655,Bannan Rd., Chung-Ho Dist.,
New Taipei City, Taiwan 235

Ledlink Optics (Dongguan) Co., Ltd

Dongguan Factory

No.5, TianKeng Industrial Dist., HengLi Town, DongGuan City,
GuangDong Province, China 523478

Ledlink Optics (Yangzhou) Co., Ltd

Yangzhou Factory

No.180, LinJiang Rd., YangZhou City, Jiangsu Province, China 225009

www.ledlink-optics.com

service@ledlink-optics.com



Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[LedLink Optics:](#)

[LL01ZZ-DUU15L02-M2](#) [LL01ZZ-DUU38L02-M2](#) [LL01ZZ-DUU24L02-M2](#) [LL01A00CXHB2](#) [LL01ZZ-DUU15L02](#)