

preliminary


Schottky Diode Gen ²

| | | |
|-----------|---|--------|
| V_{RRM} | = | 45 V |
| I_{FAV} | = | 10 A |
| V_F | = | 0.52 V |

High Performance Schottky Diode
 Low Loss and Soft Recovery
 Single Diode


Part number

DSB10I45PM



Backside: isolated

 E72873



Features / Advantages:

- Very low V_f
- Extremely low switching losses
- Low I_{rm} values
- Improved thermal behaviour
- High reliability circuit operation
- Low voltage peaks for reduced protection circuits
- Low noise switching

Applications:

- Rectifiers in switch mode power supplies (SMPS)
- Free wheeling diode in low voltage converters

Package: TO-220FP

- Isolation Voltage: 2500 V~
- Industry standard outline
- RoHS compliant
- Epoxy meets UL 94V-0
- Soldering pins for PCB mounting
- Base plate: Plastic overmolded tab
- Reduced weight


Disclaimer Notice

Information furnished is believed to be accurate and reliable. However, users should independently evaluate the suitability of and test each product selected for their own applications. Littelfuse products are not designed for, and may not be used in, all applications. Read complete Disclaimer Notice at www.littelfuse.com/disclaimer-electronics.

| Schottky | | | | Ratings | | | |
|------------|--|--|--------------------------------|--------------------------------|------|------|------|
| Symbol | Definition | Conditions | | min. | typ. | max. | Unit |
| V_{RSM} | max. non-repetitive reverse blocking voltage | $T_{VJ} = 25^{\circ}\text{C}$ | | | | 45 | V |
| V_{RRM} | max. repetitive reverse blocking voltage | $T_{VJ} = 25^{\circ}\text{C}$ | | | | 45 | V |
| I_R | reverse current, drain current | $V_R = 45\text{ V}$ | $T_{VJ} = 25^{\circ}\text{C}$ | | | 3.5 | mA |
| | | $V_R = 45\text{ V}$ | $T_{VJ} = 100^{\circ}\text{C}$ | | | 35 | mA |
| V_F | forward voltage drop | $I_F = 10\text{ A}$ | $T_{VJ} = 25^{\circ}\text{C}$ | | | 0.56 | V |
| | | $I_F = 20\text{ A}$ | | | | 0.78 | V |
| | | $I_F = 10\text{ A}$ | $T_{VJ} = 125^{\circ}\text{C}$ | | | 0.52 | V |
| | | $I_F = 20\text{ A}$ | | | | 0.74 | V |
| I_{FAV} | average forward current | $T_C = 115^{\circ}\text{C}$ rectangular $d = 0.5$ | $T_{VJ} = 150^{\circ}\text{C}$ | | | 10 | A |
| V_{F0} | threshold voltage | } for power loss calculation only | | $T_{VJ} = 150^{\circ}\text{C}$ | | 0.30 | V |
| r_F | slope resistance | | | | | 20.8 | mΩ |
| R_{thJC} | thermal resistance junction to case | | | | | 4.5 | K/W |
| R_{thCH} | thermal resistance case to heatsink | | | | 0.5 | | K/W |
| P_{tot} | total power dissipation | $T_C = 25^{\circ}\text{C}$ | | | | 30 | W |
| I_{FSM} | max. forward surge current | $t = 10\text{ ms}; (50\text{ Hz}), \text{ sine}; V_R = 0\text{ V}$ | $T_{VJ} = 45^{\circ}\text{C}$ | | | 260 | A |
| C_J | junction capacitance | $V_R = 5\text{ V}$ $f = 1\text{ MHz}$ | $T_{VJ} = 25^{\circ}\text{C}$ | | 326 | | pF |

preliminary

| Package TO-220FP | | | | Ratings | | | |
|------------------|--|----------------------|-------------------------------------|---------|------|------|------|
| Symbol | Definition | Conditions | | min. | typ. | max. | Unit |
| I_{RMS} | RMS current | per terminal | | | | 35 | A |
| T_{VJ} | virtual junction temperature | | | -55 | | 150 | °C |
| T_{op} | operation temperature | | | -55 | | 125 | °C |
| T_{stg} | storage temperature | | | -55 | | 150 | °C |
| Weight | | | | | 2 | | g |
| M_D | mounting torque | | | 0.4 | | 0.6 | Nm |
| F_C | mounting force with clip | | | 20 | | 60 | N |
| $d_{Spp/App}$ | creepage distance on surface striking distance through air | terminal to terminal | 3.2 | 2.7 | | | mm |
| $d_{Spb/Apb}$ | | terminal to backside | 2.5 | 2.5 | | | mm |
| V_{ISOL} | isolation voltage | t = 1 second | 50/60 Hz, RMS; $I_{ISOL} \leq 1$ mA | 2500 | | | V |
| | | t = 1 minute | | 2100 | | | V |

Product Marking

Part description


D = Diode
 S = Schottky Diode
 B = ultra low VF
 10 = Current Rating [A]
 I = Single Diode
 45 = Reverse Voltage [V]
 PM = TO-220ACFP (2)


| Ordering | Ordering Number | Marking on Product | Delivery Mode | Quantity | Code No. |
|----------|-----------------|--------------------|---------------|----------|----------|
| Standard | DSB10I45PM | DSB10I45PM | Tube | 50 | 504423 |

Equivalent Circuits for Simulation

* on die level


 $T_{VJ} = 150^{\circ}\text{C}$

| | | | |
|---|--------------------|-----------------|----|
|  | | Schottky | |
| $V_{0\max}$ | threshold voltage | 0.3 | V |
| $R_{0\max}$ | slope resistance * | 17.7 | mΩ |

Outlines TO-220FP


Note:
 All metal surface are
 matte pure tin plated
 except trimmed area.

| Dim. | Millimeters | | Inches | |
|------|-------------|-------|-----------|-------|
| | min | max | min | max |
| A | 4.50 | 4.90 | 0.177 | 0.193 |
| A1 | 2.34 | 2.74 | 0.092 | 0.108 |
| A2 | 2.56 | 2.96 | 0.101 | 0.117 |
| b | 0.70 | 0.90 | 0.028 | 0.035 |
| b1 | 1.27 | 1.47 | 0.050 | 0.058 |
| c | 0.45 | 0.60 | 0.018 | 0.024 |
| D | 15.67 | 16.07 | 0.617 | 0.633 |
| d1 | 0 | 1.10 | 0 | 0.043 |
| E | 9.96 | 10.36 | 0.392 | 0.408 |
| e | 2.54 BSC | | 0.100 BSC | |
| H | 6.48 | 6.88 | 0.255 | 0.271 |
| L | 12.68 | 13.28 | 0.499 | 0.523 |
| L1 | 3.03 | 3.43 | 0.119 | 0.135 |
| ØP | 3.08 | 3.28 | 0.121 | 0.129 |
| Q | 3.20 | 3.40 | 0.126 | 0.134 |



Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[IXYS:](#)

[DSB10I45PM](#)