



RESISTANCE @ +25°C = 10,000 Ω \pm 1%
 RESISTANCE/TEMPERATURE CURVE = "G"
 BETA " β " (+25 TO +85°C) = 3,695°K NOMINAL
 DISSIPATION CONSTANT = 0.75 mW/°C NOMINAL (STILL AIR)
 THERMAL TIME CONSTANT = 0.35 SECONDS NOMINAL (STIRRED OIL)
 MAXIMUM TEMPERATURE RATING = +250°C

SEE MANUFACTURING SPECIFICATION (LAYER 1)

NONE	RELEASE TO PRODUCTION	01/11/12	DD
REV	REVISION RECORD	DATE	APP

SCALE	NONE	U.S. SENSOR CORP. © COPYRIGHT 714-639-1000 www.ussensor.com NTC THERMISTOR P/N GP103G4F	
DRAWN BY	DAN DANKERT		
DATE	01/11/12		
REV.	NONE		
LAYER	0 OF 2		

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Littelfuse:](#)

[GP103G4F](#)