

## SUMMARY

### # Wires

Low voltage 4



*Image is for illustrative purpose only*

|                  |                                    |
|------------------|------------------------------------|
| Series           | 2B                                 |
| Termination type | Female solder                      |
| IP rating        | 50                                 |
| AWG wire size    | 28.00 - 20.00                      |
| Cable Ø          | 4.30 - 5.20 mm                     |
| Status           | active                             |
| Matching parts   | <a href="#">FGG.2B.304.CLAD52Z</a> |

### Download

[Request a quote](#)

[Eplan](#)

[Catalog](#)

## TECHNICAL DETAILS

### Mechanics

|                   |   |
|-------------------|---|
| Shell Style/Model | PH*: Free receptacle, cable collet and nut for fitting a bend relief  |
| Keying            | 1 key (alpha=0, plug: male contacts, receptacle: female contacts)   |
| Housing Material  | Brass (chrome plated [SAE AMS 2460]) shell and collet nut, nickel plated [SAE AMS QQ N 290] brass latch sleeve and mid pieces |
| Variant           | Z : Nut for fitting a bend relief   |
| Weight            | 39.35 g   |

### Performance

|               |                           |
|---------------|---------------------------|
| Configuration | 2B.304 : 4 Low Voltage    |
| Insulator     | L: PEEK (UL 94 / V-0/1.5) |
| Rated Current | 15 Amps                   |

### Specifications

Contact Type: Solder  
Contact Dia.: 1.3 mm (0.051in)  
Bucket Dia.: 1 mm (0.039in)  
Max. Solid Conductor: 0.5 mm<sup>2</sup> (AWG 20)  
Max. Stranded Conductor: 0.5 mm<sup>2</sup> (AWG 20)  
R (max): 3.6 mOhm


LEMO products and services are provided "as is". LEMO makes no warranties or representations with regard to LEMO product & services or use of them, express, implied or statutory, including for accuracy, completeness, or security. The user is fully responsible for his products and applications using LEMO components.

Vtest (contact-shell): 1850 V (AC), 2600 V (DC)  
Vtest (contact-contact): 1850 V (AC), 2600 V (DC)

Others

Endurance (Shell): 5000  
Temp (min / max): -55°C / +250°C  
Humidity (max): <=95% [at 60 deg C / 140 F]  
Vibration: 15 g [10 Hz - 2000 Hz]  
Shock Resistance: 100 g [ 6 ms]  
Climatical Category: 50/175/21  
Shielding (min): 75 dB (10 MHz)  
Shielding (min): 40 dB (1 GHz)  
Salt Spray Corrosion: >1000 hr

DRAWINGS



Dimensions

|     | A    | L    | S1   | S2   |
|-----|------|------|------|------|
| mm. | 16.5 | 46   | 13   | 12   |
| in. | 0,65 | 1,81 | 0,51 | 0,47 |

RECOMMENDED BY LEMO

Tools

LEMO products and services are provided “as is”. LEMO makes no warranties or representations with regard to LEMO product & services or use of them, express, implied or statutory, including for accuracy, completeness, or security. The user is fully responsible for his products and applications using LEMO components.

### Cables

|                    |               |       |   |
|--------------------|---------------|-------|---|
| CMN.04.T22.047QGC  | TPR           | Grey  |   |
| CMN.04.T22.048QGZE | TPR (medical) | Grey  |  |
| 140240             | PVC           | Black |  |
| 140250             | PVC           | Grey  |   |
| 40260              | PVC           | Black |  |
| 4080               | PVC           | Grey  |   |
| 4221               | PVC           | Black |  |
| 4280               | PVC           | Black |  |
| 80080              | PVC           | Grey  |   |
| 80082              | PVC           | Red   |   |
| 80084              | PVC           | Black |   |

*LEMO products and services are provided “as is”. LEMO makes no warranties or representations with regard to LEMO product & services or use of them, express, implied or statutory, including for accuracy, completeness, or security. The user is fully responsible for his products and applications using LEMO components.*

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

LEMO:

[PHG.2B.304.CLLD52Z](#)