

262/268/269 Series, MICRO[™] Very Fast-Acting Fuse (High-Reliability)



Agency Approvals

Agency	Agency File Number	Ampere Range	Series
A 1	E10480	0.002A - 5A	262 & 268
(Sft)	29862	0.002A - 5A	262 & 268
QPL	FM07A	0.002A - 5A	269

Description

The 262/268/269 Series are high–reliability MICRO[™] fuses, with a 125V rating, very fast-acting type with high breaking capacity. The 269 series is listed under the Department of Defense Quality Product List.

Features

٠

• Military grade available

Available from very low

ampere of 0.002A to 5A

- Recognized to UL/CSA/ NMX 248-1 and UL/CSA/ NMX 248-14
- Available in plug-in and radial leaded

Applications

Protection of electrical, electronic, and communication equipment having printed circuit boards (PCBs) usable in direct current (DC) and alternating current (AC) (up to 400 hertz (Hz)) circuits capable of withstanding and functioning in extreme conditions found in Spacecraft or Military applications as described in MIL-PRF-23419.

Electrical Characteristics

% of Ampere Rating	Ampere Rating	Opening Time
100%	0.002 – 15	4 Hours, Min.
2000/	0.002 – 0.3	5 Seconds, Max.
200%	0.4 - 5	2 Seconds, Max.

Electrical Characteristics Agency Approvals Ampere Max **Nominal Cold** Interrupting Amp Code Rating Voltage EV. QPL Rating **Resistance** (Ohms) Ð Rating (V) (A) 2000 0.002 0.002 125 Х Х Х 0.005 0.005 125 280 Х Х Х 0.010 94.0 Х 0.010 125 Х Х 0.015 0.015 125 44.0 Х Х Х 0.031 0.031 125 16.45 Х Х Х 0.050 0.050 125 3.20 Х Х Х 0.062 0.062 125 2 2 5 Х Х Х 0.100 0.100 125 1.17 Χ Х Х 0.125 0.125 125 1.0 Х Х Х 0.200 0.200 125 2.30 Х Х Х 0.250 Х 0 2 5 0 Х 125 1.75 Х 0.300 0.300 125 1.25 Х Х Х 10,000A@125VAC/VDC 0.400 0.400 125 0.227 Х Х Х 0.500 0.167 Х 0.500 125 Х Х 0.600 0.600 125 0.140 Х Х Х 0.700 0.700 125 0.114 Х Χ Х 0.750 0.750 125 0.104 Х Х Х 0.800 0.800 125 0.094 Х Х Х 1.00 001.0 125 0.100 Х Х X 01.5 01.5 125 0.063 Х Х Х 2.00 002.0 125 0.046 Х Х Х 3.00 003.0 125 0.034 Х Х Х 4.00 004.0 125 0.019 Х Х Х 0.018 5.00 005.0 125 Х Х

Please contact Littelfuse for Average Time Current Curve.

© 2019 Littelfuse, Inc. Specifications are subject to change without notice. Revised: 11/14/19



Soldering Parameters - Wave Soldering



Recommended Process Parameters:

Wave Parameter	Lead-Free Recommendation	
Preheat: (Depends on Flux Activation Temperature)	(Typical Industry Recommendation)	
Temperature Minimum:	100° C	
Temperature Maximum:	150° C	
Preheat Time:	60-180 seconds	
Solder Pot Temperature:	260° C Maximum	
Solder Dwell Time:	2-5 seconds	

Recommended Hand-Solder Parameters:

Solder Iron Temperature: 350° C +/- 5°C

Heating Time: 5 seconds max.

Note: These devices are not recommended for IR or Convection Reflow process.

Temperature Re-rating Curve



Notes: 1. Rerating depicted in this curve is in addition to the standard derating of 25% for

continuous operation.

2. Please contact Littelfuse for average time current curve.



Axial Lead & Cartridge Fuses MICRO[™] > Very Fast-Acting Fuse > 262/268/269 Series

Product Characteristics

Materials	Gold-Plated Copper Leads, Type II (Fuse cap is also Gold-Plated)		
Weight	262 and 269 Series .36 Grams; 268 Series .48 Grams		
Lead Pull Force	MIL-STD-202, Method 211, Test Condition A (will withstand a 5 lb. axial pull test)		
AQL (Electrical Characteristics)	Certified to 1% AQL		
Sampling	Per MIL-STD-105, Inspection Level II		
Traceability and Identification Records	Controlled by lot number and retained on file for a minimum of three years. Copies of Lot Certification Test data available when requested with order		
Options	Special screening tests, burn-in, etc. can be supplied on special order to meet specific requirements		
Product Marking	262 / 268 Series: Brand logo, current and voltage ratings 269 Series: Brand logo, current and voltage ratings and agency approval mark		
Operating Temperature	-55°C to +125°C		
Shock	(1/500): MILSTD-202, Method 213, Test Condition A (50 G's peak for 11 millisec- onds). (1/200–5): MILSTD-202, Method 213, Test Condition I (100 G's peak for 6 milliseconds)		

Vibration	MILSTD-202, Method 201 (10–55 Hz); MIL- STD-202, Method 204, Test Condition C (55–2000 Hz at 10 G's Peak)		
Salt Spray	MIL-STD-202, Method 101, Test Condition B		
Seal Test	MIL-STD-202, Method 112, Test Condition A		
Insulation Resistance (After Opening)	MIL-STD-202, Method 302, Test Condition A (1/2 Megohm minimum)		
Thermal Shock	MIL-STD-202, Method 107, Test Condition B (–65°C to 125°C)		
Moisture Resistance	MIL-STD-202, Method 106		
Fuses to MIL SPEC	262 Series is available as FM07A on QPL for MIL-PRF-23419/7. To order, change 262 to 269		



Packaging

Packaging Option	Packaging Specification	Quantity	Quantity & Packaging Code
Bulk	N/A	5	V

Part Numbering System



262 Series



Datasheet

268 Series

¥ ا

Datasheet

269 Series

Resources 268 Series



Resources 269 Series

Samples 262 Series



Samples 268 Series



Samples 269 Series

Disclaimer Notice - Information furnished is believed to be accurate and reliable. However, users should independently evaluate the suitability of and test each product selected for their own applications. Littelfuse products are not designed for, and may not be used in, all applications. Read complete Disclaimer Notice at: www.littelfuse.com/disclaimer-electronics.

> © 2019 Littelfuse, Inc. Specifications are subject to change without notice. Revised: 11/14/19

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Littelfuse:

268.002 0262.200V 0262.100VT 0262.031VT 0269.400VT 0268.400VT 0269.200VT 0268.200VT 0269002VT 0269.031V 0268.005VT 0269.005VT 0269.050V 0262.050VT 0262.700V 0269.015V 0269.010V 0268.200V 0262.600V 0262.300VT 0262.500V 0262001V 0262005V 0262.062VT 0262003V 0268.100V 0262004V 0262002V 0268.062V 0268001V 0268005V 0268003V 0268004V 0268002V 0269.700V 0268.031V 0269.500V 026201.5VT 0268.010V 0268.015V 0268.500VT 0269.500VT 0268.250V 0268.050V 0268.010VT 0269.010VT 0262.400VT 0269.600V 0262.800V 0269.300V 0262.250VT 0268.400V 0269005VT 0269001VT 0268.500V 0262.750VT 0262.250V 026801.5V 0269.050VT 0268.050VT 0268.700VT 0269.700VT 0269004VT 0262.300V 0262.600VT 0269.800V 0269.01.V 0269.050VT 0268.050VT 0268.700VT 0269.700VT 0269004VT 0262.300V 0262.600VT 0269.800V 0269001.V 0262001.V 0262002.V 0262003.V 0262004.V 0269005.V 0268001.V 0268002.V 0268003.V 0268004.V 0268005.V 0269002.V 0269003.V 0269004.V 0269005.V 0262.125V 0262.002V 0262.005V 0268003.VT 0268.00VT 0268001.VT 0262.062V 0268004.V 0269005.VT 0269.10VT 0268005.VT 0269.250V 0268003.VT 0262.250VT 0268001.VT 0262.062V 0268004.V 0269005.VT 0269.10VT 0268005.VT 0269.250V 0268003.VT 0262.800VT 0268001.VT 0262.062V 0268001.VT 0269005.VT 0269.050VT 0269005.VT 0269005.V