Axial Lead & Cartridge Fuses

5×20 mm > Time-Lag > 477 Series

477 Series, 5×20 mm, Time-Lag Fuse





Agency Approvals

Agency	Agency File Number	Ampere Range		
PS	Cartridge: NBK040609-JP1021A NBK040609-JP1021C NBK100408-JP1021A Leaded: NBK040609-JP1021B NBK040609-JP1021D NBK100408-JP1021B	1A – 5A 6.3A – 12A 16A 1A – 5A 6.3A – 12A 16A		
	1620077	0.500A – 8A		
c AL °us	E10480	0.500A - 16A		
VDE	40025413	1A, 3.15A		
A	J50248089	10A, 12A, 16A		
Œ	N/A	0.500A – 16A		

Additional Information







Description

400Vdc/500Vac rated, 5x20mm, time-lag, surge withstand ceramic body cartridge fuse.

Features

- Designed to International Available in cartridge and (IEC) Standard for use globally.
- Follow the IEC 60127-2, Sheet 5 specification for time-lag fuses
- axial lead form
- RoHS compliant and lead-free

Applications

High energy and power efficient applications.

Electrical Characteristics for Series

% of Ampere Rating	Ampere Rating	Opening Time	
150%	.58	60 minutes, Minimum	
	1 - 3.15	60 minutes, Minimum	
	4 - 6.3	60 minutes, Minimum	
	8 - 16	30 minutes, Minimum	
	.58	30 minutes, Maximum	
210%	1 - 3.15	30 minutes, Maximum	
210%	4 - 6.3	30 minutes, Maximum	
	8 - 16	30 minutes, Maximum	
	.58	.25 sec., Min.; 80 sec. Max.	
2750/	1 - 3.15	.75 sec., Min.; 80 sec. Max.	
275%	4 - 6.3	.75 sec., Min.; 80 sec. Max.	
	8 - 16	.75 sec., Min.; 80 sec. Max.	
	.58	.05 sec., Min.; 5 sec. Max.	
400%	1 - 3.15	.095 sec., Min.; 5 sec. Max.	
	4 - 6.3	.15 sec., Min.; 5 sec. Max.	
	8 - 16	.15 sec., Min.; 5 sec. Max.	
	.58	.005 sec., Min.; .15 sec. Max.	
1000%	1 - 3.15	.01 sec., Min.; .15 sec. Max.	
1000 70	4 - 6.3	.01 sec., Min.; .15 sec. Max.	
	8 - 16	.01 sec., Min.; .15 sec. Max.	




Electrical Characteristic


	Amp Rating	Volt Rat	ax age ing /)	Interrupting Rating	Nominal Cold Resistance (Milli-ohms)	Nominal Melting I ² t (A ² sec.) [†]	Agency Approvals				
		· ·					PSE	c FL °us	\bigcirc	Δ	VDE
.500	0.5	AC 500	DC 400		1055.900	0.300	~	×*	x**		
.800	0.8	500	400	100A@500VAC 1500A@400VDC	430.000	0.909		X*	x**		
001.	1	500	400		139.400	1.800	X	X*	x**		X
002.	2	500	400		55.200	9.120	Х	X*	x**		
3.15	3.15	500	400		27.700	50.109	Х	X*	X**		X
004.	4	500	400		17.200	52.480	Х	X*	X**		
005.	5	500	400		13.700	76.500	Х	X*	X**		
06.3	6.3	500	400	100A@500VAC	10.970	121.451	Х	X	X**		
008.	8	500	400	500A@400VDC	8.305	203.520	Х	X	X**		
010.	10	500	400		4.950	509.000	Х	X		×	
012.	12	500	400		4.730	576.000	X	X		Х	
016.	16	500	400	100A@500VAC 400A@400VDC	3.100	1331.200	Х	x		X***	

^{*100}A @ 600Vac also available. Add suffix "MXE6P". Example: 0477004.MXE6P.

Temperature Re-rating Curve



Average Time Current Curves



^{**}Semko approval for 100A@500Vac and 200A@400Vdc.
***100A@ 500Vac and 300A@400Vdc for 16A

[†]I2t test at 10x rated current.

Axial Lead & Cartridge Fuses

5×20 mm > Time-Lag > 477 Series

Soldering Parameters - Wave Soldering



Recommended Process Parameters:

Wave Parameter	Lead-Free Recommendation		
Preheat:			
(Depends on Flux Activation Temperature)	(Typical Industry Recommendation)		
Temperature Minimum:	100°C		
Temperature Maximum:	150°C		
Preheat Time:	60-180 seconds		
Solder Pot Temperature:	260°C Maximum		
Solder DwellTime:	2-5 seconds		

Recommended Hand-Solder Parameters:

Solder Iron Temperature: 350°C +/- 5°C

Heating Time: 5 seconds max.


Note: These devices are not recommended for IR or Convection Reflow process.

Product Characteristics

Materials	Body: Ceramic Cap: Nickel-plated Brass Leads: Tin-plated Copper			
Terminal Strength	MIL-STD-202, Method 211, Test Condition A			
Solderability	MIL-STD-202 Method 208			
Product Marking	Cap 1: Brand logo, current and voltage ratings Cap 2: Series and agency approval markings			
Packaging	Available in Bulk (M=1000 pcs/pkg)			


Operating Temperature	−55°C to +125°C		
Thermal Shock	MIL-STD-202, Method 107, Test Condition B (5 cycles, -65°C to +125°C)		
Vibration	MIL-STD-202, Method 201		
Humidity	MIL-STD-202, Method 103, Test Condition A (High RH (95%) and elevated temp (40°C) for 240 hours)		
Salt Spray	MIL-STD-202, Method 101, Test Condition B		

Dimensions



^{*} Ratings above 5A 1.0±0.05 diameter lead.

Part Numbering System



Axial Lead & Cartridge Fuses

5×20 mm > Time-Lag > 477 Series



Packaging								
Packaging Option	ging Option Packaging Specification Quantity Quantity & Packaging Code		Reel Size					
477 Series								
Bulk	N/A	1000	MX	N/A				
Bulk	N/A	1000	MXE	N/A				
Reel and Tape	N/A	1000	MRET1	T1=53mm (2.087")				

Disclaimer Notice - Littelfuse products are not designed for, and shall not be used for, any purpose (including, without limitation, automotive, military, aerospace, medical, life-saving, life-sustaining or nuclear facility applications, devices intended for surgical implant into the body, or any other application in which the failure or lack of desired operation of the product may result in personal injury, death, or property damage) other than those expressly set forth in applicable Littelfuse product documentation. Warranties granted by Littelfuse shall be deemed void for products used for any purpose not expressly set forth in applicable Littelfuse documentation. Littelfuse shall not be liable for any claims or damages arising out of products used in applications not expressly intended by Littelfuse as set forth in applicable Littelfuse documentation. The sale and use of Littelfuse products is subject to Littelfuse Terms and Conditions of Sale, unless otherwise agreed by Littelfuse. Information furnished is believed to be accurate and reliable. However, users should independently evaluate the suitability of and test each product selected for their own applications. Littelfuse products are not designed for, and may not be used in, all applications. Read complete Disclaimer Notice at www.littelfuse.com/disclaimer-electronics.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Littelfuse:

0477.500MXEP 0477.500MXP 0477.800MXEP 0477.800MXP 0477001.MXEP 0477001.MXP 0477002.MXEP 0477002.MXEP 0477004.MXEP 0477004.MXP 0477005.MXEP 0477005.MXEP 0477008.MXEP 0477008.MXEP 0477010.MXEP 0477010.MXEP 0477012.MXEP 0477012.MXEP 0477016.MXEP 0477016.MXEP 0477016.MXEP 047706.3MXEP 047706.3MXEP 047706.3MXEP 0477016.MXEP 0477016.MXEP 0477016.MXEP 0477016.MXEP 0477016.MXEP 0477016.MXEP 0477016.MXEP 0477016.MXEP 0477016.MXEP 0477016.MXET1P 0477016.MXET1P