




LI-AR0234CS-GMSL2-OWL



Address:

48820 Kato Road
Suite 100B
Fremont, CA 94538
USA



Phone:

+1 (408)263-0988

Fax:

+1 (408)217-1960



Sales:

sales@leopardimaging.com

Support:

support@leopardimaging.com

INTRODUCTION

The LI-AR0234CS-GMSL2-OWL is equipped with ON Semiconductor CMOS digital image sensor AR0234CS, capable of producing clear, low noise images in both low-light and bright scenes. This camera outputs 1920 x 1200 RAW data.

SPECIFICATIONS



Sensor	ON Semiconductor CMOS Image Sensor AR0234CS
Optical Format	1/2.6"
Resolution	1920 (H) x 1200 (V) (active pixels)
Pixel Size	3.0 x 3.0 μm
Color / Mono	Color sensor
Frame Rate	120 fps @ full resolution
Shutter	Global shutter
Serializer	Maxim MAX9295A/B
Power Supply Range	9 ~ 19 VDC
FAKRA Connector	FAKRA Z TYPE
Power Consumption	70 mA @ 12 VDC
Operating Temp	-20°C ~ 50°C
Storage Temp	-20°C ~ 105°C
Weight	~ 37.2 g
Size	50.0 (L) x 25.0 (W) x 37.7 (D) mm
Part#	LI-AR0234CS-GMSL2-OWL

APPLICATIONS







- Bar Code Scanner
- Gesture Recognition
- 3D Scanning
- Positional Tracking
- Iris Scanning
- Augmented Reality
- Virtual Reality
- Biometrics
- Machine Vision

LENS SPECIFICATIONS

Focal Length	1.34 $\pm$ 5%
Aperture, F/#	2.0 $\pm$ 5%
Field of View (FOV)	202.0° $\pm$ 3° horizontal
	127.2° $\pm$ 2° vertical
IR Filter	650 nm $\pm$ 10 nm IR cut filter
Lens Mount	M12 x 0.5



DIMENSIONS




Note:


-  marked are important sizes.
- Tolerance for others unmarked is ± 0.3 mm.

Unit: mm

SYSTEM BLOCK DIAGRAM



POWER BLOCK DIAGRAM




USB3.0 CAMERA KIT

LI-USB30-DESER-GMSL2



Top View



Bottom View

LI-AR0234CS-GMSL2-OWL can connect to LI-USB30-DESER-GMSL2 as a USB 3.0 camera.

Part#: LI-USB30-AR0234CS-GMSL2-OWL

SPECIFICATIONS

- USB 3.0 Super Speed support
- UVC compliance
- Global shutter
- Provide customization services
- 12 VDC power supply for camera
- Weight: ~ 104 g
- Single Coax Cable transmit up to 12 meters PoC (Power over Cable)
- Resolution: 1920 x 1200 @ 30 fps
- Support Windows, Linux OS and other OS which include the UVC drivers

BOM

#	Items	QTY
1	LI-AR0234CS-GMSL2-OWL	1
2	LI-USB30-DESER-GMSL2	1
3	3-Meter Fakra Cable	1
4	12 VDC Power Supply	1
5	USB3.0 Cable	1



SDK SUPPORTED

- Camera Tool Source Code in C#
- Capture & Display
- Register Access Function

● REVISION HISTORY

Revision	Description	Release date
1.0	First release.	20 May 2021

48820 Kato Rd, Suite 100B, Fremont, CA 94538, USA

Phone: +1-408-263-0988

Fax: +1-408-217-1960

Email: sales@leopardimaging.com

Website: www.leopardimaging.com



Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Leopard Imaging:](#)

[LI-AR0234CS-GMSL2-OWL](#)