


ISS-105 SERIES

Five-Channel Intrinsically Safe Switch





Wiring Diagram



Description

The ISS-105 is a "smart" five-channel intrinsically safe relay and pump controller. The ISS-105 can be configured for pump-up or pump-down applications or as a five-channel relay covering a wide variety of applications.

The ISS-105 has a long list of features that are needed for multiple pump applications and can indicate low, high and out-of-sequence alarms. If an out-of-sequence alarm occurs, the skipped pump(s) will be started as intended.

The Model ISS-105 can be set-up to do non-alternating control, alternating control and alternating control with one non-alternating pump. The non-alternating pump is intended for use with an emergency or jockey pump. The ISS-105 can start an emergency pump once every 50 cycles to keep it working freely. Using the built-in DIP switches, individual pumps can be disabled when taken out of service for repair or maintenance.

Features & Benefits

- 5 intrinsically-safe input channels meeting UL913 Sixth Edition
- 4 normally open output relays and 1 SPDT output relay
- Field selectable pump control options
- Monitors float sequencing and sends signal to alarm if out-of-sequence condition occurs
- High and/or low alarm options depending on the number of pumps and settings
- Output contacts for audible alarm
- Meets IEC EMC standards for Electrical Fast Transients (EFT), Electrostatic Discharge (ESD) and Radio Frequency Immunity (RFI)
- DIN rail or surface mountable allows flexibility in panel installation
- User-selectable alternator/non-alternator option
- Non-alternating pump option for emergency or jockey applications
- Pump disable switches make it easy to disable individual pumps when they are out for service or repair
- Adjustable lag pump delay for all pumping modes
- Adjustable delay-on-make/break timer in five-channel relay mode
- Finger-safe terminals meet IEC 61000 safety requirements

Ordering Information

MODEL	LINE VOLTAGE	DESCRIPTION
ISS-105	120VAC	Intrinsically-Safe & Pump Controller
ISS-105-ISO	120VAC	Intrinsically-Safe Only
ISS-105-ISO-3	120VAC	3-Channel Intrinsically-Safe Only
ISS-105-ISO-4	120VAC	4-Channel Intrinsically-Safe Only
ISS-105-ISO-F	120VAC	ISO with Fast Trip Relays

Protection Relays Intrinsically Safe Relays

Expertise Applied | Answers Delivered

Specifications

ISS-105

Input Characteristics Supply Voltage Frequency Functional Characteristics Probe Sense Voltage Output Characteristics Relay Output Rating Pilot Duty General Purpose Relay Contact Life (Electrical) Relay Contact Life (Mechanical) General Characteristics

Temperature Range Maximum Input Power Wire range Recommended Terminal Torque Provides Intrinsically-Safe Circuits in the following locations:

Entity Parameters

120VAC 50*/60Hz

5vdc continuous

480VA @ 240VAC, B300 7A @ 240VAC 100,000 cycles min. @ rated load 10,000,000 cycles

-40° to 55°C (-40° to 131°F) 5 W 12 to 20 AWG 3.5 to 4.5 in.-lbs. (max. 4.5 in.-lbs.)

 $\begin{array}{l} \mbox{Division 1 and 2} \\ \mbox{Class I, Groups A,B,C,D;} \\ \mbox{Class I, Groups E,F,G;} \\ \mbox{and Class III} \\ \mbox{V}_{oc} = 16.8V \\ \mbox{I}_{sc} = 1.2mA \\ \mbox{L}_{a} = 100mH \\ \mbox{C}_{a} = 0.39uF \end{array}$

Standards Passed

Electrostatic Discharge (ESD) Radio Frequency Immunity (RFI) Fast Transients

Safety Marks

UL Dimensions

Weight Mounting Method IEC 61000-4-2, Level 3, 6kV contact, 8kV air. IEC 61000-4-3, Level 3, 10V/m IEC 61000-4-4, Level 3, 4kV input power 2kV inputs/outputs

UL913 Sixth Edition (File #E233355) H 94.06 mm (3.703"); W 127.64 mm (5.025"); D 59.69 mm (2.350") 1.2 lbs. (19.2 oz., 544.31 g) 35 mm DIN rail or Surface Mount (#6 or #8 screws)

*Note: 50Hz will increase all delay timers by 20%.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Littelfuse:

ISS-105 ISS-105-ISO-4 ISS-105-ISO ISS-105-ISO-3 ISS-105-ISO-F