



Battrax® Series - Dual Port Negative - MS-013




Agency Approvals

Agency	Agency File Number
	E133083

Pinout Designation



Schematic Symbol



Electrical Characteristics

Part Number	Marking	V_{DRM} @ $I_{DRM}=5\mu A$	V_S @ $100V/\mu s$	I_H	I_S	I_T	V_T @ $I_T=2.2 A$	V_F	Capacitance*	
		V min	V max	mA min	mA max	A max	V max	V max	pF min	pF max
B1101UC4Lxx	B1101UC4	$-V_{REF}I + I-1.2VI$	$-V_{REF}I + I-10VI$	100	100	2.2	4	5	30	200
B1161UC4Lxx	B1161UC4	$-V_{REF}I + I-1.2VI$	$-V_{REF}I + I-10VI$	160	100	2.2	4	5	30	200
B1201UC4Lxx	B1201UC4	$-V_{REF}I + I-1.2VI$	$-V_{REF}I + I-10VI$	200	100	2.2	4	5	30	200

Notes:

- Absolute maximum ratings measured at $T_A = 25^\circ C$ (unless otherwise noted).
- Components are uni-directional
- All electrical characteristics shown are defined from Tip (pin 1 & 6) to Ground (pin 5) and Ring (pin 3 & 4) to Ground (pin 5)
- Components are polarity sensitive and are not appropriate for positive ringing systems.

Description

The Dual Port Negative Battrax® Protection Thyristor Series are programmable SIDACtor® components designed to protect SLICs (Subscriber Line Interface Circuit) from damaging overvoltage transients.

Dual port protection is provided by a programmable device that is referenced to a negative voltage source while internal diodes provide protection from positive surge events.

Features and Benefits

- Low voltage overshoot
- Low on-state voltage
- Does not degrade surge capability after multiple surge events within limit.
- RoHS Compliant and Lead-Free
- Dual-port protection
- Gate trigger tracking device
- Fails short circuit when surged in excess of ratings
- Integrated diode for positive voltage surges
- Pb-free E3 means 2nd level interconnect is Pb-free and the terminal finish material is tin(Sn) (IPC/JEDEC J-STD-609A.01)

Applicable Global Standards

- TIA-968-A
- TIA-968-B
- ITU K.20/21 Enhanced Level
- ITU K.20/21 Basic Level
- GR 1089 Intra-building
- IEC 61000-4-5 2nd edition
- YD/T 1082
- YD/T 993
- YD/T 950

Additional Information



Datasheet



Resources



Samples

- V_{REF} Max Value for the negative Battrax is -200 V.
- XX = Part Number Suffix: 'TP' (Tube Pack) or 'RP' (Reel Pack).

* Off-state capacitance (C_o) is measured across pins 1 & 5, 3 & 5, 4 & 5, and 6 & 5 at 1 MHz with a 2V bias.


Surge Ratings

Series	I _{PP}									I _{TSM} 50/60 Hz	di/dt
	0.2/310 ¹ 0.5/700 ²	2/10 ¹ 2/10 ²	8/20 ¹ 1.2/50 ²	10/160 ¹ 10/160 ²	10/560 ¹ 10/560 ²	5/320 ¹ 9/720 ²	10/360 ¹ 10/360 ²	10/1000 ¹ 10/1000 ²	5/310 ¹ 10/700 ²		
	A min	A min	A min	A min	A min	A min	A min	A min	A min		
C	50	500	400	200	150	200	175	100	200	50	500


Notes:

- 1 Current waveform in μs
 - 2 Voltage waveform in μs
- Peak pulse current rating (I_{PP}) is repetitive and guaranteed for the life of the product that remains in thermal equilibrium.
 - I_{PP} ratings applicable over temperature range of -40°C to +85°C (I_{PP} rating assumes V_{REF} equals -48 V)
 - The component must initially be in thermal equilibrium with -40°C ≤ T_J ≤ +150°C


Thermal Considerations

Package	Symbol	Parameter	Value	Unit
Modified MS-013 6 	T_J	Operating Junction Temperature Range	-40 to +125	°C
	T_S	Storage Temperature Range	-65 to +150	°C
	$R_{\theta JA}$	Thermal Resistance: Junction to Ambient	60	°C/W


V-I Characteristics




$t_r \times t_d$ Pulse Waveform



Normalized V_S Change vs. Junction Temperature




Normalized DC Holding Current vs. Case Temperature



Soldering Parameters

Reflow Condition		Pb-Free assembly (see Fig. 1)
Pre Heat	-Temperature Min ($T_{s(min)}$)	+150°C
	-Temperature Max ($T_{s(max)}$)	+200°C
	-Time (Min to Max) (t_s)	60-180 secs.
Average ramp up rate (Liquidus Temp (T_L) to peak)		3°C/sec. Max.
$T_{s(max)}$ to T_L - Ramp-up Rate		3°C/sec. Max.
Reflow	-Temperature (T_L) (Liquidus)	+217°C
	-Temperature (t_L)	60-150 secs.
Peak Temp (T_p)		+260(+0/-5)°C
Time within 5°C of actual Peak Temp (t_p)		30 secs. Max.
Ramp-down Rate		6°C/sec. Max.
Time 25°C to Peak Temp (T_p)		8 min. Max.
Do not exceed		+260°C




Physical Specifications

Lead Material	Copper Alloy
Terminal Finish	100% Matte-Tin Plated
Body Material	UL Recognized epoxy meeting flammability classification V-0

Environmental Specifications

High Temp Voltage Blocking	80% Rated V_{DRM} (V_{DC} Peak) +125°C or +150°C, 504 or 1008 hrs. MIL-STD-750 (Method 1040) JEDEC, JESD22-A-101
Temp Cycling	-65°C to +150°C, 15 min. dwell, 10 up to 100 cycles. MIL-STD-750 (Method 1051) EIA/JEDEC, JESD22-A104
Biased Temp & Humidity	52 V_{DC} (+85°C) 85%RH, 504 up to 1008 hrs. EIA/JEDEC, JESD22-A-101
High Temp Storage	+150°C 1008 hrs. MIL-STD-750 (Method 1031) JEDEC, JESD22-A-101
Low Temp Storage	-65°C, 1008 hrs.
Thermal Shock	0°C to +100°C, 5 min. dwell, 10 sec. transfer, 10 cycles. MIL-STD-750 (Method 1056) JEDEC, JESD22-A-106
Autoclave (Pressure Cooker Test)	+121°C, 100%RH, 2atm, 24 up to 168 hrs. EIA/JEDEC, JESD22-A-102
Resistance to Solder Heat	+260°C, 30 secs. MIL-STD-750 (Method 2031)
Moisture Sensitivity Level	85%RH, +85°C, 168 hrs., 3 reflow cycles (+260°C Peak). JEDEC-J-STD-020, Level 1

Part Numbering



Part Marking




Figure 1: Dimensions and details of the 100-pin connector. The figure includes a top view, a side view, and a detail view of the 90-degree bend. The top view shows dimensions A, B, C, D, E, and F. The side view shows dimensions G, H, J, and K. The detail view shows the 90-degree bend with dimensions 4°, 96°, and K. The dimensions are in inches and millimeters.

Dimensions	Inches		Millimeters	
	Min	Max	Min	Max
A	0.360	0.364	9.14	9.25
B	0.352	0.356	8.94	9.04
C	0.400	0.412	10.16	10.46
D	0.043	0.045	1.09	1.13
E	0.047	0.055	1.19	1.40
F	0.293	0.297	7.44	7.54
G	0.289	0.293	7.34	7.44
H	0.089	0.093	2.26	2.36
J	0.041	0.049	1.04	1.24
K	0.020	—	0.51	—
BSC*	0.133	0.143	3.38	3.63

Package Type	Description	Quantity	Added Suffix	Industry Standard
U	Modified MS-013 6-pin Tape and Reel Pack	1500	RP	EIA-481-D
	Modified MS-013 6-pin Tube Pack	500 (50 per tube)	TP	N/A

Technical drawing of a circular part with dimensions in inches and millimeters.

Dimensions are in inches (and millimeters)

Direction of Feed

Arbor Hole Dia.

Dimensions shown:

- Top View Diameter: 12.99 (330)
- Side View Height: 0.630 (16.0)
- Top View Hole Diameter: .512 (13.0)
- Top View Hole Position: .157 (4.0) from the left edge, .472 (12.0) from the center.

Technical drawing of a tube with a message location detail. The main view shows a cross-section of the tube with dimensions in inches and millimeters. The tube has a 90° bend. The dimensions are as follows:

- Top left vertical dimension: $.045 \pm .014$ (1.14)
- Top left horizontal dimension: $.165$ (4.19)
- Top center horizontal dimension: $.310$ (7.87)
- Top right horizontal dimension: $.108$ (2.74)
- Bottom left horizontal dimension: $.150$ (3.81)
- Bottom center horizontal dimension: $.225$ (5.72)
- Bottom right horizontal dimension: $.525$ (13.34)
- Right vertical dimension: $.110$ (2.79)
- Wall thickness: $.020 \pm .005$ (0.51 $\pm$ 0.13) WALL TYP.
- Feature: 6 Interior of the Tube
- Feature: A

A detail view of the message location is shown on the right, with dimensions:

- Horizontal dimension: $20.000 \pm .030$ (508.00 $\pm$ 0.76)

Dimensions are in inches (and millimeters)

© 2017 Littelfuse, Inc.
Specifications are subject to change without notice.
Revised: 02/23/17

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Littelfuse:

[B1201UA4LTP](#) [B1161UA4LTP](#) [B1101UA4LTP](#) [B1201UC4LTP](#) [B1201UC4LRP](#) [B1101UC4LTP](#) [B1161UC4LTP](#)
[B1101UC4LRP](#) [B1161UC4LRP](#) [B1201UA4RP](#) [B1101UA4LRP](#) [B1201UA4TP](#) [B1161UA4RP](#) [B1161UA4LRP](#)
[B1161UA4TP](#) [B1201UC4RP](#) [B1201UA4LRP](#) [B1201UC4TP](#) [B1161UC4RP](#) [B1101UA4TP](#) [B1101UC4RP](#)
[B1161UC4TP](#) [B1101UA4RP](#) [B1101UC4TP](#)