

## USP12920 Thermistor Probe




### Description

Littelfuse offers Stainless probe assemblies suitable for a wide range of temperature sensing applications. If the dimensions and electrical characteristics on this product won't work for your requirements, please contact us for further assistance.

### Features

- Tight Tolerance
- High Temperature Capability to 300°C
- Glass Braid Insulated, Glass Braid Jacketed Cable


### Dimensions



Dimensions in inches.

A	B	C	D
Strip: 0.375" ± 0.250"	0.250" ± 0.005"	2.00" ± 0.070"	12.0" ± 1.00"

### Part Numbering System



**Note:** Not all combinations of Part Number codes are available. Contact Littelfuse for details.

### Specifications

Part Number	Resistance Ohms @25°C	Resistance Tol. ± % @ 25°C	R-T Curve	Temperature Coefficient (% / °C) @ 25°C	Beta (K) 0-50°C	Temperature Rating (°C)
USP12920	100000	1	J	-4.4	3892	-55 to +300

**Disclaimer Notice** - Information furnished is believed to be accurate and reliable. However, users should independently evaluate the suitability of and test each product selected for their own applications. Littelfuse products are not designed for, and may not be used in, all applications. Read complete Disclaimer Notice at: [www.littelfuse.com/disclaimer-electronics](http://www.littelfuse.com/disclaimer-electronics)

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Littelfuse:](#)

[USP12920](#)