


USP10978 Thermistor Probe



Dimensions



Dimensions in inches.

A	B	C	D
24.0" ± 1.50"	0.880" ± 0.015"	0.650" ± 0.050"	0.250" ± 0.005"

E	F	G	H
1/4" - 18 NPT Thread (RHT)	0.250" ± 0.020"	Strip: 0.250" ± 0.070"	0.562" ± 0.035" Hex

Specifications

Part Number	Resistance Ohms @25°C	Resistance Tol. ± % @ 25°C	R-T Curve	Temperature Coefficient (% / °C) @ 25°C	Beta (K) 0-50°C	Temperature Rating (°C)
USP10978	10000	1	J	-4.4	3892	-55 to +105

Disclaimer Notice - Information furnished is believed to be accurate and reliable. However, users should independently evaluate the suitability of and test each product selected for their own applications. Littelfuse products are not designed for, and may not be used in, all applications. Read complete Disclaimer Notice at: www.littelfuse.com/disclaimer-electronics

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Littelfuse:](#)

[USP10978](#)