


Features/Benefits

- Chassis or panel mount
- Various buttons and illumination
- Various contact configurations

Typical Applications

- Mains/power switching
- Consumer electronics
- Audio equipment
- Digital products



A

Pushbutton

Specifications

POWER CONTACT:

SWITCHING POWER MAX. AC/DC: NE18: 1500/100 W,
NE18CTII: 1000/100 W; AC (Inductive $\cos \phi = 0.6$): NE18: 900W,
NE18CTII: 600W.

SWITCHING VOLTAGE MAX. AC/DC: 250/100V

SWITCHING CURRENT MAX. AC/DC

AC (Inductive $\cos \phi = 0.6$): NE18: $6 A^2/4/1 A$, NE18CTII: $4 A^2/1 A$

INRUSH CURRENT MAX. AC¹: NE18: 36 A, NE18CTII: 64 A

DIELECTRIC STRENGTH (50 Hz, 1 min.): 2000 V

OPERATING LIFE AT MAX. LOAD AND AT MAX. INRUSH
CURRENT: $\wedge 10^4$ operations⁵

CONTACT RESISTANCE: Initial: 50m Ω ; After 10^4 operations: 70m Ω .

INSULATION RESISTANCE: $\wedge 10^{12} \Omega$ chassis – nearest contact;

$\wedge 10^{12} \Omega$ mains contact – mains contact; $\wedge 10^{12} \Omega$ mains contact –
mains contact after 10^4 operations.

LOW VOLTAGE CONTACT:

SWITCHING POWER MAX.: 12W

SWITCHING VOLTAGE MAX.: 24V

SWITCHING CURRENT MAX.: 0.5A

TOTAL TRAVEL: 4.7mm (.185 inch)

LATCHING TRAVEL: 3.3mm (.130 inch)

OPERATING FORCE: Without auxiliary low voltage contacts:
NE18: 7N (700 grams); NE18CTII: 9.5N (950 grams).

With auxiliary low voltage contacts: NE18: 8N (800 grams);
NE18CTII: 11N (1100 grams).

SEALING: Dust proof.

Materials

HOUSING, ACTUATOR & TERMINAL BOARD: Thermoplastic
polyester (UL 94V-0).

MOVABLE CONTACT: Silver nickel alloy, silver plated.

FIXED CONTACTS: Silver nickel alloy, silver plated.

COMMON CONTACTS & TERMINALS: Copper alloy, silver plated.


RETURN SPRING: Music wire.

NOTE: Specifications and materials listed above are for switches with standard options.
For information on specific and custom switches, consult Customer Service Center.

Build-A-Switch

To order, simply select desired option from each category and place in the appropriate box. Available options are shown and described on pages A-79 thru A-106. For additional options not shown in catalog, consult Customer Service Center.

If requesting only a switch, select the switch as noted below. Buttons are sold separately.



C&K NE-18 Series Mains / Power Switches



A

Pushbutton

Order Code - Buttons

Solid Buttons



Style


F01 FMR
F02 FG*
F03 F1.12-H-5
F06 F1.12-H-4
F07 F1.15-H-4
F12 FSC
F13 FSD
F14 FU12
F15 FSB
F16 FE
F19 FA
F21 F001

Button Color

01 (STD.) Black
02 White
03 Red
04 Light gray
09 Chrome, standard for F03 only

*Black/chrome, standard for F06 & F07 only

Illuminated Buttons with Chassis



Style

F21 FRV
F22 FSR

Shell Color

01 (STD.) Black
02 White
03 Red
06 Yellow
08 Green
12 Orange
16 Clear / White

North American Lamp

01 6V / 30ma
02 12V / 30ma
03 24V / 30ma

European Lamp

04 5V / 60ma
05 6V / 40ma
06 12V / 40ma
07 24V / 20ma

Lamp Holder

FL1
FL2

Mechanical Indicator Buttons



Style

F01 FA100
F02 FA101
F05 FA110
F07 FA120
F08 FA201
F11 FA200*

Shell Color

01 (STD.) Black

Out Position Color

01 (STD.) Black

In Position Color

02 White
06 Yellow
07 Blue
08 Green
12 Orange

Central Mounted Illuminated Buttons



Style

F24 FLB* (F200)
F25 FLC*

Shell Color

01 (STD.) Black
02 White
05 Gray

Lens Color

03 Red
06 Yellow
07 Blue
08 Green
12 Orange
16 Clear / White

Light Type

01 Lamp, 6V
02 Lamp, 12V
03 Lamp, 28V
04 LED, green
05 LED, red
06 LED, yellow
07 Neon, 110-220AC

Lamp Holder

LZ1
LZ2

*Button options for central mounting configurations, use 'FG' for central mount with chrome dress nut, use 'FA200', 'FLB' or 'FLC' for central mount with black dress nut.




BUTTON REMOVAL

A button of a push-push switch should only be removed in the "OFF" non-latching position.

DESIGNATION & SWITCHES WITH STANDARD OPTIONS



ZNE1838EECF0201



Third Angle Projection
Dimensions are shown: IN (mm)
Dimensions subject to change

C&K NE-18 Series Mains / Power Switches



DESIGNATION & SWITCHES WITH STANDARD OPTIONS





A

Pushbutton

NE1839EE



NE1845EE



C&K NE-18 Series


Mains / Power Switches



A

Pushbutton

CONTACT ARRANGEMENT



OPTION CODE Contact capacity and availability	STYLE	ELECTRICAL CIRCUIT
37	NE18 — 2AX	DPST
38	NE18 — 2UX	DPDT
51	2U + NE18 — 2AX	DPST*
52 (4A/64)	NE18CTII — 2AX	DPST
39	2U + NE18 — 2UX	DPDT*
41	NE18 — 2AP	DPST
42	NE18 — 2UP	DPDT
43	NE18 — 2AW	DPST
44	NE18 — 2UW	DPDT
45	NE18 — 2ASX	DPST

* 2U + Denotes auxiliary set of low current contacts DPDT
 2A = DPST
 2U = DPDT
 S = Snap-in mounting
 X = Solder lug/PC pins
 W = Solder lugs only
 P = PC pins only

OPTION CODE Contact capacity and availability	STYLE	ELECTRICAL CIRCUIT
46	NE18 — 2USX	DPDT
47	NE18 — 2ASP	DPST
48	NE18 — 2USP	DPDT
49	NE18 — 2ASW	DPST
50	NE18 — 2USW	DPDT
53 (4A/64)	2U + NE18CTII — 2AX	DPST
54	2U + NE18 — 2AW	DPST
55	2U + NE18 — 2AP	DPST
56	2U + NE18 — 2UW	DPDT
57	2U + NE18 — 2UP	DPDT

NOTES

- Contact plating is silver on all Power Switches.
- The electrical function is Break Before Make (BBM) on all Power Switches.
- The terminals will be epoxy sealed.

TYPE	POSSIBLE CONTACT ARRANGEMENT		CONTACT SPACING	PROTECTION CLASS (CEE 24)	APPROVALS
	POWER CONTACTS ¹⁾	AUXILIARY CONTACTS			
NE18	2A ²⁾	2U	> 3mm (.118 inch)	II	VDE, BSI, DEMKO, NEMKO, SEMKO, SEV, CSA, UL
NE18	2A ²⁾ 2R 2U	2U	> 3mm (m) (.118 inch)	I	VDE, MEEI, BSI ³⁾ , DEMKO, NEMKO, SEMKO, SEV, CSA, UL
NE18CTII	2A ²⁾	2U	> 3mm (.118 inch)	II	VDE, BSI, DEMKO, CSA, SEMKO, SEV, UL, NEMKO

- 1) A = make contact, R = break contact, U = changeover contact, m = VDE sign for switches with a contact spacing (air gap) < 3mm (.118 inch) according to VDE 0630/CEE 24.
 2) With 2A mains contacts: Mounting only by PC pins is not sufficient.
 3) BSI only for 2U mains contacts.

MECHANICAL FUNCTION



OPTION CODE	FUNCTION
OA	Momentary
EE	Alternate (push-push)

C&K NE-18 Series Mains / Power Switches

SINGLE STATION CHASSIS





A

Pushbutton

01 (STD.) WITH .094 MOUNTING HOLES

(NONE) NO CHASSIS

02 WITH 4-40 TAPPED MOUNTING HOLES




03 SPECIAL CHASSIS (CONSULT FACTORY)

DRESS NUT




(NONE) (STD.) NO DRESS NUT

B BLACK




PANEL CUTOUT




NOTE: Available with ZNE18 designation and FA200, FLB or FLC buttons.

C CHROME



PANEL CUTOUT



NOTE: Available with ZNE18 designation and FG button.



Dimensions are shown: IN (mm)
Dimensions subject to change

C&K NE-18 Series Mains / Power Switches




A

Pushbutton


SOLID BUTTON

STYLE


F01 FMR




F02 FG




F12 FSC




F13 FSD




F14 FU12




F15 FSB



F16 FE



F19 FA



OPTION CODE	COLOR
01	(STD.) BLACK
02	WHITE
03	RED
04	LT. GRAY


C&K NE-18 Series Mains / Power Switches

SOLID BUTTON




STYLE


F21 F001




F03 F1.12-H-5



F06 F1.12-H-4




F07 F1.15-H-4




OPTION CODE	COLOR
01	(STD.) BLACK
02	WHITE
03	RED
04	LT. GRAY
09	BLACK/CHROME (F03, F06 & F07 buttons only)

MECHANICAL BUTTON





STYLE

F01 FA100



F02 FA101



Third Angle
Projection
Dimensions are shown: IN (mm)
Dimensions subject to change



A

Pushbutton


C&K NE-18 Series Mains / Power Switches



A


Pushbutton

MECHANICAL BUTTON




STYLE


F05 FA110




F07 FA120



F08 FA201



F11 FA200



SHELL COLOR

01 (STD.) BLACK

OUT POSITION COLOR

01 (STD.) BLACK


IN POSITION COLOR

OPTION CODE	COLOR
02	WHITE
06	YELLOW
07	BLUE
08	GREEN
12	ORANGE

Pushbutton

C&K NE-18 Series Mains / Power Switches



CENTRAL MOUNTED ILLUMINATED BUTTON



STYLE

F24 FLB (F200)

F25 FLC



SHELL COLOR

OPTION CODE	COLOR
01	(STD.) BLACK
02	WHITE
05	GRAY

LENS COLOR


OPTION CODE	COLOR
03	RED
06	YELLOW
07	BLUE
08	GREEN
12	ORANGE
16	CLEAR / WT.

LIGHT TYPE

OPTION CODE	DESCRIPTION
01	Lamp, 6V
02	Lamp, 12V
03	Lamp, 28V
04	LED, green
05	LED, red
06	LED, yellow
07	Neon, 110-220AC

LAMP HOLDER

OPTION CODE	DESCRIPTION
LZ1	Illumination dependent on button position. Button depressed, lamp on.
LZ2	Illumination independent of button position.



Third Angle
Projection

Dimensions are shown: IN (mm)
Dimensions subject to change



A

Pushbutton

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[C&K Switches:](#)

[NE1839EE](#) [NE1845EE](#) [NE18/2AOAX](#) [130230](#) [NE1848EE](#) [104-0101-004](#)