


Features

- ID1 full size card acceptance
- Card detection sealed switch
- Compatible with pick and place and lead free soldering

Typical Applications

- Transaction
- POS
- Identification



Mechanical

Number of contacts	6 or 8
Mechanical life	50,000 cycles
Card insertion force	10N max
Card extraction force	1N min / 10N max
Contact force	0,4N to 0,7N
Card detection switch	0,8 N max for actuation (end travel switch actuation force actuates when card is 0,9mm from card stop) 1,8 N max for complete depression
Vibration Frequency	10 to 500 Hz. Acceleration 50m/s ² Duration 6 hours - amplitude 0,35mm
Shock	Peak value 500 m/s ² - Duration 11 ms 3 shocks in each direction of each axis
Max elect. discontinuity	1µs

Packaging

See table below

Soldering Process

Compatible with lead free SMT reflow soldering process

Contact Electrical Data

Insulation resistance	1000 MΩ min
Contact resistance max	100 mΩ max
Switching current	10 µA min / 1 A max
Dielectric strength	750 Vrms min

Switch Electrical Data

Card detection switch	Normally open
Rc card detection switch	100 mΩ max
Dielectric strength	250 Vrms min
Switch current rating	1 mA min / 10 mA max
Maximum switch power	0.2 VA

Environmental Data

Operating temperature	-40°C to +85°C
Salt mist	IEC 512 test number 11f (96 hours)
Damp heat	IEC 512 test number 11c (10 days)
Card detection switch	Sealed against dust
RoHS compliant	

Designation	Housing Type	# of Contacts	Contact Force	Total Height (mm)	Total Dim. (mm)	Packaging
CCM04-5427LFT	standard	8	0,4N to 0,7N	2,65	18,75 X 25	reels of 1,000 pcs
CCM04-5436LFT	standard	8	0,4N to 0,7N	0,90	18,75 X 26,9	reels of 1,000 pcs
CCM04-5454LFT	standard	8	0,4N to 0,7N	0,90	18,75 X 26,9	reels of 1,000 pcs
CCM04-5455LFT	standard	8	0,4N to 0,7N	0,90	18,75 X 26,9	reels of 1,000 pcs

Full Size

[illegible]


Technical drawing of a contact layout for a 12-pin connector. The drawing shows a grid of 8 rows (C5-C8) and 4 columns. Dimensions are provided in millimeters.

Key dimensions include:

- Vertical spacing: 2.54mm between rows.
- Horizontal spacing: 13mm between columns.
- Rightmost column width: 1.7mm.
- Bottom horizontal dimensions: 3.81mm, 3.81mm, 2.79mm, and a total of 15.15mm.
- Stand-off area for switch contacts.

Labels include:

- Contact foot area 0,8 x 0,7
- Plastic outline
- Pad
- C5-C8
- C1-C4
- SW
- ISO/IEC 7816-2



Full Size


CCM04-5436 LFT



www.ckwitches.com

Full Size



CCM04-5454 LFT

[illegible]

www.ckwitches.com

Full Size

CCM04-5455 LFT



www.ckwitches.com

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

C&K Aerospace:

[CCM045436LFTR102A](#) [CCM045455LFTR801](#) [CCM045454LFTR102A](#) [CCM045458LFTR601](#) [CCM045468LFTR601](#)
[CCM045436LFTR901](#) [CCM045427LFTR901](#)

C&K Switches:

[CCM04-5427LFT R901](#) [CCM04-5436LFT R901](#)