

# LCA Series Subminiature Snap-acting Switches



## Features/Benefits

- Compact design
- Long life and high electrical capacity
- Quick connect, solder terminals, PC terminals
- Wide variety of actuator styles
- RoHS compatible

## Typical Applications

- Motorized equipment
- Sump pump
- Thermostatic controls

UL61058-1



## Specifications

CONTACT RATING: From low level to 10.1 AMPS @ 125/250 V AC  
ELECTRICAL LIFE: see chart below  
MECHANICAL LIFE: 300,000 cycles.  
INSULATION RESISTANCE: 100 M ohm min.  
DIELECTRIC STRENGTH: 1,500 Vrms min. @ sea level.  
OPERATING TEMPERATURE: -40°C to +125°C  
OPERATING FORCE: 150 grams at actuator button MAX.  
Forces are less at free end of lever actuators; (see ACTUATOR'S option sections).  
MOUNTING: 2-56 screws, torque 2.3 in/lbs max.


## Materials

SWITCH HOUSING: Thermoplastic polyester  
ACTUATOR BUTTON: Thermoplastic polyester.  
SPRING: Copper alloy.  
PIVOT: Copper alloy.  
MOVABLE CONTACTS: Silver alloy  
STATIONARY CONTACTS: Silver alloy  
TERMINALS: Copper alloy.  
ACTUATOR LEVER: Stainless steel.

**NOTE:** Specifications and materials listed above are for switches with standard options.  
For information on specific and custom switches, consult Customer Service center.

## Build-A-Switch

To order, simply select desired option from each category and place in the appropriate box. Available options are shown and described on pages J-36 thru J-39. For additional options not shown in catalog, consult Customer Service Center.



Option Code	UL 1054	UL 61058-1	UL 14
<b>01</b>	0.1 A 125/250 V AC 1E4	0.1 A 125/250 V AC 1E4	0.1 A 125/250 V AC 1E4
<b>06</b>	6 A 125/250 V AC 1E4	6 A 125/250 V AC 1E4	6 (2)A 125/250 V AC 1E4
<b>10</b>	10.1 A 125/250 V AC 1E4	10.1 A 125/250 V AC 1E4	10.1 A 125/250 V AC 1E4
<b>S5</b>	NA	5 A 125/250 V AC 1E5	NA

### Actuator

**P00** Pin plunger  
**T05** 4.8 mm short lever  
**T06** 6.8 mm lever  
**T09** 8.8 mm lever  
**T12** 12.9 mm lever  
**T16** 15.2 mm lever  
**T18** 18.1 mm lever  
**T21** 20.1 mm lever  
**T23** 23.4 mm lever  
**T43** 43.5 mm lever  
**S06** 6.0 mm simulated lever  
**S09** 9.2 mm simulated lever  
**A05** 5.0 mm lever roller


### Terminations

**S** Solder  
**Q** .110 Quick Connect  
**P** PC Thru Hole  
**L** Left Form PC  
**R** Right Form PC

### Circuitry

**C** SPDT  
**W** SPST N.C.  
**Y** SPST N.O.

Snap-acting




Dimensions are shown: mm  
Specifications and dimensions subject to change

# LCA Series Subminiature Snap-acting Switches

SERIES 

LCA



ELECTRICAL RATING 

RoHS COMPLIANT *	RoHS COMPATIBLE *	OPTION CODE	ELECTRICAL RATING
YES	YES	01	0.1A, 125/250 VAC
YES	YES	06	6A, 125/250 VAC
YES	YES	10	10.1A, 125/250 VAC
YES	YES	S5	5A, 125/250 VAC


\* Note: See Technical Data section of this catalog for RoHS compliant and compatible definition and specifications.

OPERATING FORCE 

OPTION CODE	OPERATING FORCES (grams)
150	150 grams max.



Snap-acting



Dimensions are shown: mm  
Specifications and dimensions subject to change



# LCA Series

## Subminiature Snap-acting Switches

ACTUATOR 



**A05** LEVER ROLLER

**SXX** SIMULATED ROLLER



**TXX** LEVER

**P00**



ACTUATOR OPTION CODE	A mm	B r mm	eC mm	D mm	E mm	Diff. Motion mm	Oper. Force max. grams	Release Force min. grams	Over Travel min.
	LENGTH OF LEVER	Lever length for front mtg. hole to OP	PRE TRAVEL (MAX)	OPERATING POSITION	FREE POSITION (MAX)	max			
P00	NA	NA	1.10	8.55 ± 0.3	9.35	0.20	150	25	0.4
T05	16.70	4.80	3.60	8.95 ± 0.8	11.75	0.80	50	6	0.6
T06	18.70	6.80	4.03	8.9 ± 0.9	12.09	0.90	45	5	0.67
T09	20.60	9.10	5.64	9.15 ± 1.35	13.45	1.83	33	2	0.75
T12	24.80	12.90	3.35	8.95 ± 1.5	13.10	1.19	34	2	0.89
T16	27.10	15.20	7.20	9.15 ± 1.7	15.15	1.30	40	1	0.70
T18	30.00	18.10	7.70	8.95 ± 1.9	14.65	1.50	32	1	1.2
T21	32.00	20.10	8.00	8.15 ± 1.85	15.55	1.60	35	1	1.0
T23	35.20	23.40	8.60	8.95 ± 2.0	15.55	1.80	25	1	1.5
T43	55.20	43.50	10.45	8.95 ± 3.0	19.25	2.90	15	1	1.0
S06	17.90	6.00	3.86	10.85 ± 0.9	17.81	0.86	47	5	0.64
S09	21.10	9.20	5.7	16.15 ± 1.5	20.35	1.00	42	2	1.0
A05	16.60	5.00	3.8	14.65 ± 0.8	17.65	0.80	50	6	0.6



Third Angle  
Projection

Dimensions are shown: mm  
Specifications and dimensions subject to change





**C&K**

# LCA Series Subminiature Snap-acting Switches

## TERMINATIONS





**S** SOLDER

**Q** QUICK CONNECT






**P** PC THRU HOLE

**L** LEFT FORM PC



**R** RIGHT FORM PC




## CIRCUITRY

**C** SPDT (Single Pole, Double Throw)

**W** SPST N.C. (Single Pole, Single Throw, Normally Closed)

**Y** SPST N.O. (Single Pole, Single Throw, Normally Open)



Dimensions are shown: mm  
Specifications and dimensions subject to change

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

## C&K Switches:

[LCA01150T05SW](#) [LCA06150S09PC](#) [LCAS5150T23PY](#) [LCAS5150T05RW](#) [LCAS5150T43QY](#) [LCA01150S09SY](#)  
[LCA10150S06RW](#) [LCAS5150T12SW](#) [LCA01150T05SY](#) [LCA06150P00RC](#) [LCAS5150T06SY](#) [LCAS5150A05QC](#)  
[LCA01150T23QC](#) [LCAS5150S09RW](#) [LCA01150T09PW](#) [LCAS5150T18LC](#) [LCA06150S06SC](#) [LCA10150S06PY](#)  
[LCAS5150T23QC](#) [LCA01150T09PC](#) [LCAS5150S09SC](#) [LCAS5150T21PW](#) [LCAS5150T21LY](#) [LCAS5150T05SY](#)  
[LCAS5150T21PC](#) [LCAS5150S09RY](#) [LCAS5150S06RW](#) [LCAS5150T16LC](#) [LCAS5150T21QY](#) [LCAS5150S06SY](#)  
[LCAS5150S06QW](#) [LCAS5150T18QC](#) [LCA10150P00SW](#) [LCAS5150A05QW](#) [LCAS5150S09PY](#) [LCAS5150T05LW](#)  
[LCA06150A05PW](#) [LCA01150P00RW](#) [LCAS5150T05RY](#) [LCAS5150T43PY](#) [LCAS5150T16RW](#) [LCAS5150T21SY](#)  
[LCAS5150T05QW](#) [LCAS5150T43RY](#) [LCAS5150S06RY](#) [LCAS5150T06LW](#) [LCAS5150T23LY](#) [LCAS5150S09QY](#)  
[LCA01150T09SW](#) [LCAS5150T16QW](#) [LCA01150P00QY](#) [LCAS5150T16PW](#) [LCA01150T05PY](#) [LCA01150P00RC](#)  
[LCAS5150T43PC](#) [LCAS5150T12LY](#) [LCAS5150T18QY](#) [LCAS5150T23QY](#) [LCAS5150T06RC](#) [LCAS5150T21LC](#)  
[LCAS5150A05RY](#) [LCAS5150A05SW](#) [LCAS5150T18RC](#) [LCA01150S09SC](#) [LCA01150S06LC](#) [LCAS5150T16PC](#)  
[LCAS5150T21SW](#) [LCAS5150T12LW](#) [LCAS5150S09PW](#) [LCAS5150S09QW](#) [LCA06150T12QC](#) [LCA10150S06LY](#)  
[LCA10150S06SC](#) [LCA06150S06LY](#) [LCAS5150T12PY](#) [LCAS5150T05RC](#) [LCAS5150T18RY](#) [LCAS5150T43RW](#)  
[LCA06150A05QC](#) [LCAS5150T05QC](#) [LCAS5150S09SW](#) [LCAS5150T12RW](#) [LCAS5150T16SC](#) [LCA10150T06SC](#)  
[LCAS5150T23LW](#) [LCAS5150A05PC](#) [LCAS5150T06LC](#) [LCA10150A05RY](#) [LCAS5150T06QC](#) [LCAS5150T23SW](#)  
[LCAS5150T06PC](#) [LCAS5150T43SW](#) [LCAS5150T21RY](#) [LCAS5150S09LY](#) [LCA01150T09QW](#) [LCA01150S06RC](#)  
[LCAS5150T05PW](#) [LCA01150T23SC](#) [LCAS5150T16QC](#) [LCA06150T43RC](#)