

## X3-Class HiPerFET™ Power MOSFET

**IXFP80N25X3**  
**IXFQ80N25X3**  
**IXFH80N25X3**

$V_{DSS} = 250V$   
 $I_{D25} = 80A$   
 $R_{DS(on)} \leq 16m\Omega$


N-Channel Enhancement Mode  
Avalanche Rated




| Symbol     | Test Conditions                                                    | Maximum Ratings |            |
|------------|--------------------------------------------------------------------|-----------------|------------|
| $V_{DSS}$  | $T_J = 25^\circ C$ to $150^\circ C$                                | 250             | V          |
| $V_{DGR}$  | $T_J = 25^\circ C$ to $150^\circ C$ , $R_{GS} = 1M\Omega$          | 250             | V          |
| $V_{GSS}$  | Continuous                                                         | $\pm 20$        | V          |
| $V_{GSM}$  | Transient                                                          | $\pm 30$        | V          |
| $I_{D25}$  | $T_C = 25^\circ C$                                                 | 80              | A          |
| $I_{DM}$   | $T_C = 25^\circ C$ , Pulse Width Limited by $T_{JM}$               | 220             | A          |
| $I_A$      | $T_C = 25^\circ C$                                                 | 40              | A          |
| $E_{AS}$   | $T_C = 25^\circ C$                                                 | 1.2             | J          |
| $dv/dt$    | $I_S \leq I_{DM}$ , $V_{DD} \leq V_{DSS}$ , $T_J \leq 150^\circ C$ | 20              | V/ns       |
| $P_D$      | $T_C = 25^\circ C$                                                 | 390             | W          |
| $T_J$      |                                                                    | -55 ... +150    | $^\circ C$ |
| $T_{JM}$   |                                                                    | 150             | $^\circ C$ |
| $T_{stg}$  |                                                                    | -55 ... +150    | $^\circ C$ |
| $T_L$      | Maximum Lead Temperature for Soldering                             | 300             | $^\circ C$ |
| $T_{SOLD}$ | 1.6 mm (0.062in.) from Case for 10s                                | 260             | $^\circ C$ |
| $M_d$      | Mounting Torque                                                    | 1.13 / 10       | Nm/lb.in   |
| Weight     | TO-220                                                             | 3.0             | g          |
|            | TO-3P                                                              | 5.5             | g          |
|            | TO-247                                                             | 6.0             | g          |

| Symbol       | Test Conditions<br>( $T_J = 25^\circ C$ , Unless Otherwise Specified) | Characteristic Values |      |                          |
|--------------|-----------------------------------------------------------------------|-----------------------|------|--------------------------|
|              |                                                                       | Min.                  | Typ. | Max.                     |
| $BV_{DSS}$   | $V_{GS} = 0V$ , $I_D = 250\mu A$                                      | 250                   |      | V                        |
| $V_{GS(th)}$ | $V_{DS} = V_{GS}$ , $I_D = 1.5mA$                                     | 2.5                   |      | 4.5 V                    |
| $I_{GSS}$    | $V_{GS} = \pm 20V$ , $V_{DS} = 0V$                                    |                       |      | $\pm 100$ nA             |
| $I_{DSS}$    | $V_{DS} = V_{DSS}$ , $V_{GS} = 0V$<br>$T_J = 125^\circ C$             |                       |      | 5 $\mu A$<br>350 $\mu A$ |
| $R_{DS(on)}$ | $V_{GS} = 10V$ , $I_D = 0.5 \cdot I_{D25}$ , Note 1                   |                       | 13   | 16 m $\Omega$            |


### TO-220 (IXFP)



### TO-3P (IXFQ)



### TO-247 (IXFH)



G = Gate      D = Drain  
S = Source    Tab = Drain

### Features

- International Standard Packages
- Low  $R_{DS(ON)}$  and  $Q_G$
- Avalanche Rated
- Low Package Inductance

### Advantages

- High Power Density
- Easy to Mount
- Space Savings

### Applications

- Switch-Mode and Resonant-Mode Power Supplies
- DC-DC Converters
- PFC Circuits
- AC and DC Motor Drives
- Robotics and Servo Controls

| Symbol                       | Test Conditions<br>(T <sub>J</sub> = 25°C, Unless Otherwise Specified)                                                                                                   | Characteristic Values                                            |              |              |
|------------------------------|--------------------------------------------------------------------------------------------------------------------------------------------------------------------------|------------------------------------------------------------------|--------------|--------------|
|                              |                                                                                                                                                                          | Min.                                                             | Typ.         | Max          |
| g <sub>fs</sub>              | V <sub>DS</sub> = 10V, I <sub>D</sub> = 0.5 • I <sub>D25</sub> , Note 1                                                                                                  | 38                                                               | 64           | S            |
| R <sub>Gi</sub>              | Gate Input Resistance                                                                                                                                                    |                                                                  | 1.6          | Ω            |
| C <sub>iss</sub>             | V <sub>GS</sub> = 0V, V <sub>DS</sub> = 25V, f = 1MHz                                                                                                                    |                                                                  | 5430         | pF           |
| C <sub>oss</sub>             |                                                                                                                                                                          |                                                                  | 890          | pF           |
| C <sub>rss</sub>             |                                                                                                                                                                          |                                                                  | 1.6          | pF           |
| Effective Output Capacitance |                                                                                                                                                                          |                                                                  |              |              |
| C <sub>o(er)</sub>           | Energy related                                                                                                                                                           | V <sub>GS</sub> = 0V<br>V <sub>DS</sub> = 0.8 • V <sub>DSS</sub> | 320          | pF           |
| C <sub>o(tr)</sub>           | Time related                                                                                                                                                             |                                                                  | 1410         | pF           |
| t <sub>d(on)</sub>           | Resistive Switching Times<br>V <sub>GS</sub> = 10V, V <sub>DS</sub> = 0.5 • V <sub>DSS</sub> , I <sub>D</sub> = 0.5 • I <sub>D25</sub><br>R <sub>G</sub> = 5Ω (External) |                                                                  | 30           | ns           |
| t <sub>r</sub>               |                                                                                                                                                                          |                                                                  | 17           | ns           |
| t <sub>d(off)</sub>          |                                                                                                                                                                          |                                                                  | 65           | ns           |
| t <sub>f</sub>               |                                                                                                                                                                          |                                                                  | 8            | ns           |
| Q <sub>g(on)</sub>           | V <sub>GS</sub> = 10V, V <sub>DS</sub> = 0.5 • V <sub>DSS</sub> , I <sub>D</sub> = 0.5 • I <sub>D25</sub>                                                                |                                                                  | 83           | nC           |
| Q <sub>gs</sub>              |                                                                                                                                                                          |                                                                  | 27           | nC           |
| Q <sub>gd</sub>              |                                                                                                                                                                          |                                                                  | 24           | nC           |
| R <sub>thJC</sub>            | TO-220<br>TO-247& TO-3P                                                                                                                                                  |                                                                  |              | 0.32 °C/W    |
| R <sub>thCS</sub>            |                                                                                                                                                                          |                                                                  | 0.50<br>0.25 | °C/W<br>°C/W |

### Source-Drain Diode

| Symbol   | Test Conditions<br>( $T_J = 25^\circ\text{C}$ , Unless Otherwise Specified)    | Characteristic Values |      |       |
|----------|--------------------------------------------------------------------------------|-----------------------|------|-------|
|          |                                                                                | Min.                  | Typ. | Max   |
| $I_S$    | $V_{GS} = 0\text{V}$                                                           |                       |      | 80 A  |
| $I_{SM}$ | Repetitive, pulse Width Limited by $T_{JM}$                                    |                       |      | 320 A |
| $V_{SD}$ | $I_F = I_S$ , $V_{GS} = 0\text{V}$ , Note 1                                    |                       |      | 1.4 V |
| $t_{rr}$ | $I_F = 40\text{A}$ , $-di/dt = 100\text{A}/\mu\text{s}$<br>$V_R = 100\text{V}$ |                       | 120  | ns    |
| $Q_{RM}$ |                                                                                |                       | 600  | nC    |
| $I_{RM}$ |                                                                                |                       | 10   | A     |

Note 1. Pulse test,  $t \leq 300\mu\text{s}$ , duty cycle,  $d \leq 2\%$ .

IXYS Reserves the Right to Change Limits, Test Conditions, and Dimensions.

|                                                                                  |           |           |           |           |             |             |             |             |             |             |
|----------------------------------------------------------------------------------|-----------|-----------|-----------|-----------|-------------|-------------|-------------|-------------|-------------|-------------|
| IXYS MOSFETs and IGBTs are covered by one or more of the following U.S. patents: | 4,835,592 | 4,931,844 | 5,049,961 | 5,237,481 | 6,162,665   | 6,404,065B1 | 6,683,344   | 6,727,585   | 7,005,734B2 | 7,157,338B2 |
|                                                                                  | 4,860,072 | 5,017,508 | 5,063,307 | 5,381,025 | 6,259,123B1 | 6,534,343   | 6,710,405B2 | 6,759,692   | 7,063,975B2 |             |
|                                                                                  | 4,881,106 | 5,034,796 | 5,187,117 | 5,486,715 | 6,306,728B1 | 6,583,505   | 6,710,463   | 6,771,478B2 | 7,071,537   |             |

Fig. 1. Output Characteristics @  $T_J = 25^\circ\text{C}$




Fig. 2. Extended Output Characteristics @  $T_J = 25^\circ\text{C}$




Fig. 3. Output Characteristics @  $T_J = 125^\circ\text{C}$




Fig. 4.  $R_{DS(on)}$  Normalized to  $I_D = 40A$  Value vs. Junction Temperature




Fig. 5.  $R_{DS(on)}$  Normalized to  $I_D = 40A$  Value vs. Drain Current




Fig. 6. Normalized Breakdown & Threshold Voltages vs. Junction Temperature




Fig. 7. Maximum Drain Current vs. Case Temperature




Fig. 8. Input Admittance




Fig. 9. Transconductance




Fig. 10. Forward Voltage Drop of Intrinsic Diode




Fig. 11. Gate Charge




Fig. 12. Capacitance




Fig. 13. Output Capacitance Stored Energy




Fig. 14. Forward-Bias Safe Operating Area







Fig. 15. Maximum Transient Thermal Impedance




**TO-220 Outline**


| SYM  | INCHES   |      | MILLIMETERS |       |
|------|----------|------|-------------|-------|
|      | MIN      | MAX  | MIN         | MAX   |
| A    | .169     | .185 | 4.30        | 4.70  |
| A1   | .047     | .055 | 1.20        | 1.40  |
| A2   | .079     | .106 | 2.00        | 2.70  |
| b    | .024     | .039 | 0.60        | 1.00  |
| b2   | .045     | .057 | 1.15        | 1.45  |
| c    | .014     | .026 | 0.35        | 0.65  |
| D    | .587     | .626 | 14.90       | 15.90 |
| D1   | .335     | .370 | 8.50        | 9.40  |
| (D2) | .500     | .531 | 12.70       | 13.50 |
| E    | .382     | .406 | 9.70        | 10.30 |
| (E1) | .283     | .323 | 7.20        | 8.20  |
| e    | .100 BSC |      | 2.54 BSC    |       |
| e1   | .200 BSC |      | 5.08 BSC    |       |
| H1   | .244     | .268 | 6.20        | 6.80  |
| L    | .492     | .547 | 12.50       | 13.90 |
| L1   | .110     | .154 | 2.80        | 3.90  |
| ØP   | .134     | .150 | 3.40        | 3.80  |
| Q    | .106     | .126 | 2.70        | 3.20  |

**TO-3P Outline**


| SYM | INCHES   |      | MILLIMETERS |       |
|-----|----------|------|-------------|-------|
|     | MIN      | MAX  | MIN         | MAX   |
| A   | .181     | .197 | 4.60        | 5.00  |
| A1  | .087     | 1.02 | 2.20        | 2.60  |
| A2  | .057     | .065 | 1.45        | 1.65  |
| b   | .031     | .047 | 0.80        | 1.20  |
| b2  | .071     | .087 | 1.80        | 2.20  |
| b4  | .110     | .126 | 2.80        | 3.20  |
| c   | .022     | .031 | 0.55        | 0.80  |
| D   | .776     | .791 | 19.70       | 20.10 |
| D1  | .640     | .680 | 16.26       | 17.27 |
| E   | .606     | .622 | 15.40       | 15.80 |
| E1  | .531     | .539 | 13.50       | 13.70 |
| e   | .215 BSC |      | 5.45 BSC    |       |
| L   | .779     | .795 | 19.80       | 20.20 |
| L1  | .130     | .146 | 3.30        | 3.70  |
| ØP  | .122     | .134 | 3.10        | 3.40  |
| ØP1 | .272     | .280 | 6.90        | 7.10  |
| S   | .189     | .205 | 4.80        | 5.20  |

**TO-247 Outline**


| SYM | INCHES   |      | MILLIMETERS |       |
|-----|----------|------|-------------|-------|
|     | MIN      | MAX  | MIN         | MAX   |
| A   | .190     | .205 | 4.83        | 5.21  |
| A1  | .090     | .100 | 2.29        | 2.54  |
| A2  | .075     | .085 | 1.91        | 2.16  |
| b   | .045     | .055 | 1.14        | 1.40  |
| b2  | .075     | .087 | 1.91        | 2.20  |
| b4  | .115     | .126 | 2.92        | 3.20  |
| C   | .024     | .031 | 0.61        | 0.80  |
| D   | .819     | .840 | 20.80       | 21.34 |
| D1  | .650     | .690 | 16.51       | 17.53 |
| D2  | .035     | .050 | 0.89        | 1.27  |
| E   | .620     | .635 | 15.75       | 16.13 |
| E1  | .545     | .565 | 13.84       | 14.35 |
| e   | .215 BSC |      | 5.45 BSC    |       |
| J   | --       | .010 | --          | 0.25  |
| K   | --       | .025 | --          | 0.64  |
| L   | .780     | .810 | 19.81       | 20.57 |
| L1  | .150     | .170 | 3.81        | 4.32  |
| ØP  | .140     | .144 | 3.55        | 3.65  |
| ØP1 | .275     | .290 | 6.99        | 7.37  |
| Q   | .220     | .244 | 5.59        | 6.20  |
| R   | .170     | .190 | 4.32        | 4.83  |
| S   | .242 BSC |      | 6.15 BSC    |       |

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[IXYS:](#)

[IXFP80N25X3](#) [IXFH80N25X3](#) [IXFQ80N25X3](#)