


250A-350A • SPST • IP65 • M10/M12 Studs • Electrical bistable remote control



Technical drawing of a rectangular frame with rounded corners. The drawing includes dimensions: 100 (width), 100 (height), 10 (radius of the rounded corners), and 10 (radius of the central circular feature). The central feature is a circle with a diameter of 10. The frame has a thickness of 10. The drawing is labeled with '100', '100', '10', '10', and '10'.

## 1

[illegible]

3

2

The diagram shows a 3-phase 4-wire system. Three phase conductors are labeled 30A - 31A, 30 - 31, and 85-NEG.BOB. A fourth conductor, labeled 86-POS.BOB, is connected to the neutral point of the three-phase system, which is represented by a star symbol. The neutral point connection is enclosed in a dashed box.

4

5



6

PART NUMBER	VOLTAGE	AMPERAGE	CIRCUITRY	MOUNTING	INGRESS	TERMINAL NUTS	IMAGE	DIAGRAM	NOTES
08097160	12V DC	350A	SPST	Bolt-Down	IP65-IPX7	M12 Tin-plated brass	B	2	manual remote control
08097161	12V DC	350A	SPST	Bolt-Down	IP65-IPX7	M12 Tin-plated brass	E	1	manual remote control
08097200	24V DC	250A	SPST	Bolt-Down	IP65-IPX7	M10 Tin-plated brass	C	4	separate ON-OFF switch
08097260	24V DC	250A	SPST	Bolt-Down	IP65-IPX7	M10 Tin-plated brass	C	4	protection cover
08097261	24V DC	350A	SPST	Bolt-Down	IP65-IPX7	M12 Tin-plated brass	B	2	manual remote control
08097262	24V DC	350A	SPST	Bolt-Down	IP65-IPX7	M12 Tin-plated brass	E	1	manual remote control
08091761	24V DC	250A	SPST	Bolt-Down	IP65-IPX7	M10-M12 Tin-plated brass	F	6	stif protection sheath
08097860	24V DC	250A	SPST	Bolt-Down	IP65-IPX7	M10-M12 Tin-plated brass	D	3	manual remote control
08098100	24V DC	250A	SPST	Bolt-Down	IP65-IPX7	M10 Tin-plated brass	A	5	disconnection the alternator



## 08097160 & 08098100 BATTERY DISCONNECT SWITCHES

### Dimensions in millimeters



**08097160  
08097261**





**08091761**





**08097200  
08097260 (with cover)**





**08098100**



**08097860**



**08097161  
08097262**



Visit [Littelfuse.com](http://Littelfuse.com) for the most up-to-date product information. Littelfuse reserves the right to make product changes, without notice. Material in this document is as accurate as known at the time of publication.

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Littelfuse:

[08097200](#) [08097261](#) [08097262](#) [08098100](#) [08097260](#) [08097860](#) [08091761](#) [08097160](#) [08097161](#)