

08098700 & 08099080 BATTERY DISCONNECT SWITCHES

100-150A • SPST • UP4X/IP43 • M8-M10 Studs • Compact



Description


08098700 is Standard Compact Manual Battery Disconnect Switch that features a removable handle with a plastic body. Rated to 100A continuous current this switch is ideal light-duty applications.

08099080 is a newer design with bigger contacts (M10) and improved components for heavier 150A current loads even if keeping the compact dimensions, which make it one of the more popular products for 12V applications. This Manual Battery Disconnect Switch features a removable handle with a plastic body. Rubbed cap is included for protection while switch is removed from the socket.

Features/Benefits

- 100-150A continuous current rating
- Heavy Construction for up to 150A loads in compact design
- Highly visible bright red handle
- Weatherproof to IP43

Mounting Diagram



Specifications

Max Operating Voltage:	24V DC
Max Continuous Current:	100A 150A
Intermittent Current:	500A at 5 sec 1000A at 5 sec
Operating Temp:	-40°C to +85°C
Ingress Protection:	IP4X IP43
Contacts:	Copper
Terminals:	M8 (brass nuts) M10 (zinc-plated steel nuts)


Applications

- Heavy Truck
- Off-Road
- Emergency Vehicles
- Material Handling
- Mining
- Agricultural
- Marine
- Construction

Web Resources

Download 2D prints and additional technical resources at:
littelfuse.com/ManualBatterySwitches

Electrical Diagram




Ordering Information

PART NUMBERS		VOLTAGE	AMPERAGE	CIRCUITRY	MOUNTING	INGRESS	TERMINAL NUTS
BULK	BOXED						
08098700	08098700-BX	12-24V DC	100A	SPST	Flange Mount	IP4X	—
08098780	08098780-BX	12-24V DC	150A	SPST	Flange Mount	IP4X	Brass
08099080	08099080-BX	12-24V DC	150A	SPST	Flange Mount	IP43	Zinc-plated steel

08098700 & 08099080 BATTERY DISCONNECT SWITCHES

Dimensions in millimeters



Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Littelfuse:

[08098780](#) [08098700](#) [08099080](#)