


SP4338-02WTG

5V, 0.18pF, 15kV, 2CH-Bidirectional TVS, Ultra Low Capacitance ESD protection

PRELIMINARY & CONFIDENTIAL

Littelfuse, Inc. has characterized initial samples of this device and is currently conducting reliability testing. Parts numbers and specifications are subject to change until the datasheet is made final.


HF **RoHS** **Pb**

Description

The SP4338-02WTG provides ultra-low capacitance, bidirectional and a high level of protection for 2 channel electronic equipment that may experience destructive electrostatic discharges (ESD). The typical capacitance of 0.18pF helps ensure excellent signal integrity on the most challenging consumer electronics interfaces, such as DisplayPort interfaces, Thunderbolt and high speed USB.

It can safely absorb repetitive ESD strikes at $\pm 15\text{kV}$ (contact discharge, IEC 61000-4-2) without performance degradation and safely dissipate 7A of 8/20 μs surge current (IEC 61000-4-5 2nd edition).


Pinout



Features

- ESD, IEC 61000-4-2, $\pm 15\text{kV}$ contact/air
- EFT, IEC 61000-4-4, 40A (5/50ns)
- Maximum surge tolerance, IEC 61000-4-5, 2nd Edition, 7A (8/20 μs)
- Low leakage current of 0.1 μA (MAX) at 5V
- Ultra low capacitance of 0.18pF (Typ @ $V_R = 0\text{V}$)
- Space efficient 0201
- Halogen-free, lead-free and RoHS compliant

Functional Block Diagram



Applications

- USB 2.0 to 4.0
- Computing
- MIPI
- DisplayPort
- Thunderbolt
- S-ATA
- Cell phone

Life Support Note:

Not Intended for Use in Life Support or Life Saving Applications

The products shown herein are not designed for use in life sustaining or life saving applications unless otherwise expressly indicated.

SP4338-02WTG

5V, 0.18pF, 15kV, 2CH-Bidirectional TVS, Ultra Low Capacitance ESD protection

PRELIMINARY & CONFIDENTIAL

Littelfuse, Inc. has characterized initial samples of this device and is currently conducting reliability testing. Parts numbers and specifications are subject to change until the datasheet is made final.

Absolute Maximum Ratings

Symbol	Parameter	Value	Units
I_{PP}	Peak Current ($t_p=8/20\mu s$)	7.0	A
T_{OP}	Operating Temperature	-40 to 125	°C
T_{STOR}	Storage Temperature	-55 to 150	°C



CAUTION: Stresses above those listed in "Absolute Maximum Ratings" may cause permanent damage to the component. This is a stress only rating and operation of the component at these or any other conditions above those indicated in the operational sections of this specification is not implied.

Electrical Characteristics ($T_{OP}=25^\circ C$)

Parameter	Symbol	Test Conditions	Min	Typ	Max	Units
Reverse Standoff Voltage	V_{RWM}				5	V
Breakdown Voltage	V_{BR}	$I_R=1mA$	6.0	8.0		V
Reverse Leakage Current	I_{LEAK}	$V_R=5V$		10	100	nA
Clamp Voltage ¹	V_C	$I_{PP}=1A, t_p=8/20\mu s$		3.3		V
		$I_{PP}=7A, t_p=8/20\mu s$		6.0		V
Dynamic Resistance ²	R_{DYN}	TLP, $t_p=100ns$		0.23		Ω
ESD Withstand Voltage ^{1,3}	V_{ESD}	IEC 61000-4-2 (Contact Discharge)	± 15			kV
		IEC 61000-4-2 (Air Discharge)	± 15			kV
Diode Capacitance ¹	$C_{IO-I/O}$	Reverse Bias=0V, $f=1MHz$		0.18		pF

Note:

- Parameter is guaranteed by design and/or component characterization.
- Transmission Line Pulse (TLP) with 100ns width, 0.2ns rise time, and average window $t_1=70ns$ to $t_2=90ns$
- Device stressed with ten non-repetitive ESD pulses.




Capacitance vs. Reverse Bias**Clamping Voltage vs. I_{PP}** 

SP4338-02WTG

5V, 0.18pF, 15kV, 2CH-Bidirectional TVS, Ultra Low Capacitance ESD protection

PRELIMINARY & CONFIDENTIAL

Littelfuse, Inc. has characterized initial samples of this device and is currently conducting reliability testing. Parts numbers and specifications are subject to change until the datasheet is made final.

Positive Transmission Line Pulsing (TLP) Plot**Negative Transmission Line Pulsing (TLP) Plot****IEC 61000-4-2 +8 kV Contact ESD Clamping Voltage****IEC 61000-4-2 -8 kV Contact ESD Clamping Voltage**

SP4338-02WTG


5V, 0.18pF, 15kV, 2CH-Bidirectional TVS, Ultra Low Capacitance ESD protection

PRELIMINARY & CONFIDENTIAL

Littelfuse, Inc. has characterized initial samples of this device and is currently conducting reliability testing. Parts numbers and specifications are subject to change until the datasheet is made final.

Soldering Parameters

Reflow Condition		Pb – Free assembly
Pre Heat	- Temperature Min ($T_{s(min)}$)	150°C
	- Temperature Max ($T_{s(max)}$)	200°C
	- Time (min to max) (t_s)	60 – 120 secs
Average ramp up rate (Liquidus) Temp (T_L) to peak		3°C/second max
$T_{s(max)}$ to T_L - Ramp-up Rate		3°C/second max
Reflow	- Temperature (T_L) (Liquidus)	217°C
	- Temperature (t_L)	60 – 150 seconds
Peak Temperature (T_p)		260 ^{+0/-5} °C
Time within 5°C of actual peak Temperature (t_p)		30 seconds
Ramp-down Rate		6°C/second max
Time 25°C to peak Temperature (T_p)		8 minutes Max.
Do not exceed		260°C



Product Characteristics

Lead Plating	Matte Tin Plating
Lead material	Copper Bump
Flammability	UL Recognized compound meeting flammability rating V-0


Ordering Information

Part Number	Package	Min. Order Qty.
SP4338-02WTG	Flipchip	10000

Part Marking System



Part Numbering System




SP4338-02WTG


5V, 0.18pF, 15kV, 2CH-Bidirectional TVS, Ultra Low Capacitance ESD protection

PRELIMINARY & CONFIDENTIAL

Littelfuse, Inc. has characterized initial samples of this device and is currently conducting reliability testing. Parts numbers and specifications are subject to change until the datasheet is made final.

Package Dimensions — Flipchip

Symbol	Millimeters			Inches		
	Min	Nom	Max	Min	Nom	Max
A	0.234	0.250	0.266	0.0092	0.0098	0.0105
A1	0.008	0.011	0.014	0.0003	0.0004	0.0006
A2	0.226	0.239	0.242	0.0089	0.0094	0.0095
e	0.225 BSC			0.0089 BSC		
D	0.605	0.620	0.635	0.0238	0.0244	0.0250
E	0.305	0.320	0.335	0.0120	0.0126	0.0132
F	0.094	0.100	0.106	0.0037	0.0039	0.0042
G	0.244	0.250	0.256	0.0096	0.0098	0.0101

Embossed Carrier Tape & Reel Specification — Flipchip

Symbol	Millimeters
A0	0.38+/-0.03
B0	0.68+/-0.03
D	ø 1.50 + 0.10
D1	ø 0.17 +/- 0.05
E	1.75+/-0.10
F	3.50+/-0.05
K0	0.30+/-0.03
P0	4.00+/-0.10
P1	2.00+/-0.05
P2	2.00+/-0.05
W	8.00+0.30/-0.10
T	0.23+/-0.02

Product Disclaimer: Littelfuse products are not designed for, and shall not be used for, any purpose (including, without limitation, automotive, military, aerospace, medical, life-saving, life-sustaining or nuclear facility applications, devices intended for surgical implant into the body, or any other application in which the failure or lack of desired operation of the product may result in personal injury, death, or property damage) other than those expressly set forth in applicable Littelfuse product documentation. Warranties granted by Littelfuse shall be deemed void for products used for any purpose not expressly set forth in applicable Littelfuse documentation. Littelfuse shall not be liable for any claims or damages arising out of products used in applications not expressly intended by Littelfuse as set forth in applicable Littelfuse documentation. The sale and use of Littelfuse products is subject to Littelfuse Terms and Conditions of Sale, unless otherwise agreed by Littelfuse. "Littelfuse" includes Littelfuse, Inc., and all of its affiliate entities. <http://www.littelfuse.com/disclaimer-electronics>.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Littelfuse:

[SP4338-02WTG](#)