

### LSIC2SD120C10




#### Description

This series of silicon carbide (SiC) Schottky diodes has negligible reverse recovery current, high surge capability, and a maximum operating junction temperature of 175 °C. These diodes series are ideal for applications where improvements in efficiency, reliability, and thermal management are desired.

#### Features

- Positive temperature coefficient for safe operation and ease of paralleling
- 175 °C maximum operating junction temperature
- Excellent surge capability
- Extremely fast, temperature-independent switching behavior
- Dramatically reduced switching losses compared to Si bipolar diodes

#### Circuit Diagram TO-252-2L (DPAK)



#### Applications

- Boost diodes in PFC or DC/DC stages
- Switch-mode power supplies
- Uninterruptible power supplies
- Solar inverters
- Industrial motor drives
- EV charging stations

#### Environmental

- Littelfuse "RoHS" logo = RoHS conform
- Littelfuse "HF" logo = **HF** Halogen Free
- Littelfuse "PB-free" logo = PB-free lead plating

#### Maximum Ratings

| Characteristics                      | Symbol     | Conditions                                                | Value      | Unit |
|--------------------------------------|------------|-----------------------------------------------------------|------------|------|
| Repetitive Peak Reverse Voltage      | $V_{RRM}$  | -                                                         | 1200       | V    |
| DC Blocking Voltage                  | $V_R$      | $T_J = 25\text{ °C}$                                      | 1200       | V    |
| Continuous Forward Current           | $I_F$      | $T_C = 25\text{ °C}$                                      | 33         | A    |
|                                      |            | $T_C = 135\text{ °C}$                                     | 16         |      |
|                                      |            | $T_C = 156\text{ °C}$                                     | 10         |      |
| Non-Repetitive Forward Surge Current | $I_{FSM}$  | $T_C = 25\text{ °C}, T_P = 10\text{ ms, Half sine pulse}$ | 80         | A    |
| Power Dissipation                    | $P_{Tot}$  | $T_C = 25\text{ °C}$                                      | 176        | W    |
|                                      |            | $T_C = 110\text{ °C}$                                     | 76         |      |
| Operating Junction Temperature       | $T_J$      | -                                                         | -55 to 175 | °C   |
| Storage Temperature                  | $T_{STG}$  | -                                                         | -55 to 150 | °C   |
| Soldering Temperature                | $T_{sold}$ | -                                                         | 260        | °C   |

### Electrical Characteristics

| Characteristics         | Symbol | Conditions                                        | Value |      |      | Unit          |
|-------------------------|--------|---------------------------------------------------|-------|------|------|---------------|
|                         |        |                                                   | Min.  | Typ. | Max. |               |
| Forward Voltage         | $V_F$  | $I_F = 10 \text{ A}, T_J = 25^\circ\text{C}$      | -     | 1.5  | 1.8  | V             |
|                         |        | $I_F = 10 \text{ A}, T_J = 175^\circ\text{C}$     | -     | 2.2  |      |               |
| Reverse Current         | $I_R$  | $V_R = 1200 \text{ V}, T_J = 25^\circ\text{C}$    | -     | <1   | 100  | $\mu\text{A}$ |
|                         |        | $V_R = 1200 \text{ V}, T_J = 175^\circ\text{C}$   | -     | 10   |      |               |
| Total Capacitance       | C      | $V_R = 1 \text{ V}, f = 1 \text{ MHz}$            | -     | 582  |      | pF            |
|                         |        | $V_R = 400 \text{ V}, f = 1 \text{ MHz}$          | -     | 53   |      |               |
|                         |        | $V_R = 800 \text{ V}, f = 1 \text{ MHz}$          | -     | 40   |      |               |
| Total Capacitive Charge | $Q_C$  | $V_R = 800 \text{ V}, Q_C = \int_0^{V_R} C(V) dV$ | -     | 57   |      | nC            |

Footnote:  $T_J = +25^\circ\text{C}$  unless otherwise specified

### Thermal Characteristics

| Characteristics    | Symbol          | Conditions | Value |      |      | Unit                      |
|--------------------|-----------------|------------|-------|------|------|---------------------------|
|                    |                 |            | Min.  | Typ. | Max. |                           |
| Thermal Resistance | $R_{\theta JC}$ | -          | -     | 0.85 |      | $^\circ\text{C}/\text{W}$ |

Figure 1: Typical Forward Characteristics







Figure 2: Typical Reverse Characteristics




**Figure 3: Power Derating**



**Figure 4: Current Derating**



**Figure 5: Capacitance vs. Reverse Voltage**



**Figure 6: Capacitive Charge vs. Reverse Voltage**




Figure 7: Stored Energy vs. Reverse Voltage






Figure 8: Transient Thermal Impedance



### Part Numbering and Marking System




SIC = SiC Diode  
 2 = Gen2  
 SD = Schottky Diode  
 120 = Voltage Rating (1200 V)  
 C = TO-252-2L (DPAK)  
 10 = Current Rating ( 10 A)  
 YY = Year  
 WW = Week  
 D = Special code (fixed)  
 ZZZZZZ-ZZ = Lot Number


### Packing Options

| Part Number   | Marking      | Packing Mode  | M.O.Q |
|---------------|--------------|---------------|-------|
| LSIC2SD120C10 | SIC2SD120C10 | Tape and Reel | 2500  |

### Dimensions TO-252-2L (DPAK)




#### Recommended Solder Pattern Layout



| Symbol | Inches    |       |       | Millimeters |      |       |
|--------|-----------|-------|-------|-------------|------|-------|
|        | Min       | Nom   | Max   | Min         | Nom  | Max   |
| A      | 0.085     | 0.090 | 0.095 | 2.16        | 2.29 | 2.41  |
| A1     | 0         | 0.003 | 0.005 | 0           | 0.08 | 0.13  |
| b      | 0.025     | 0.030 | 0.035 | 0.64        | 0.76 | 0.89  |
| b3     | 0.195     | 0.200 | 0.215 | 4.95        | 5.08 | 5.46  |
| c      | 0.018     | 0.020 | 0.024 | 0.46        | 0.51 | 0.61  |
| C2     | 0.018     | 0.032 | 0.035 | 0.46        | 0.81 | 0.89  |
| D      | 0.235     | 0.240 | 0.245 | 5.97        | 6.10 | 6.22  |
| D1     | 0.205     | -     | -     | 5.21        | -    | -     |
| E      | 0.250     | 0.260 | 0.265 | 6.35        | 6.60 | 6.73  |
| E1     | 0.170     | -     | -     | 4.32        | -    | -     |
| e      | 0.090 BSC |       |       | 2.29 BSC    |      |       |
| H      | 0.370     | 0.387 | 0.410 | 9.40        | 9.83 | 10.41 |
| L      | 0.040     | 0.045 | 0.050 | 1.02        | 1.14 | 1.27  |
| L2     | 0.010 BSC |       |       | 0.25 BSC    |      |       |
| L3     | 0.035     | -     | 0.050 | 0.89        | -    | 1.27  |
| L4     | 0         | -     | 0.006 | 0           | -    | 0.15  |
| P      | 0°        | -     | 8°    | 0°          | -    | 8°    |

### Carrier Tape & Reel Specification TO-252-2L (DPAK)




1. Material: Black Conductive Polyester
2. 10 sprocket hole pitch cumulative tolerance  $\pm 0.20$
3. Camber not to exceed 1 mm in 100 mm.
4. Pocket position relative to sprocket hole measured as true position of pocket, not pocket hole.
5. Device orientation: TRL (leads perpendicular to the sprocket)
6. General tolerance is  $\pm 0.10$  mm unless otherwise specified.

#### COVER TAPE SPECS:

|                  |                                                                                           |
|------------------|-------------------------------------------------------------------------------------------|
| Width            | : 13.5 mm                                                                                 |
| Base Material    | : less than $1.2 \times 10^{-9}$ ohms/square<br>Transparent polyester, static dissipative |
| Adhesive Layer   | : Polyethylene                                                                            |
| Total Thickness  | : 60 Micron                                                                               |
| Tensile Strength | : 4-6 kg/mm <sup>2</sup>                                                                  |
| Elongation       | : 91%                                                                                     |
| Tearing Strength | : 11 kg/mm <sup>2</sup>                                                                   |
| Shelf life       | : 2 years                                                                                 |

### Carrier Tape & Reel Specification TO-252-2L (DPAK)



**Disclaimer Notice** - Littelfuse products are not designed for, and shall not be used for, any purpose (including, without limitation, automotive, military, aerospace, medical, life-saving, life-sustaining or nuclear facility applications, devices intended for surgical implant into the body, or any other application in which the failure or lack of desired operation of the product may result in personal injury, death, or property damage) other than those expressly set forth in applicable Littelfuse product documentation. Warranties granted by Littelfuse shall be deemed void for products used for any purpose not expressly set forth in applicable Littelfuse documentation. Littelfuse shall not be liable for any claims or damages arising out of products used in applications not expressly intended by Littelfuse as set forth in applicable Littelfuse documentation. The sale and use of Littelfuse products is subject to Littelfuse Terms and Conditions of Sale, unless otherwise agreed by Littelfuse. Information furnished is believed to be accurate and reliable. However, users should independently evaluate the suitability of and test each product selected for their own applications. Littelfuse products are not designed for, and may not be used in, all applications. Read complete Disclaimer Notice at [www.littelfuse.com/disclaimer-electronics](http://www.littelfuse.com/disclaimer-electronics).

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Littelfuse:](#)

[LSIC2SD120C10](#)