

224/225 Series Lead-Free 2AG, Fast-Acting



Agency Approvals

Agency	Agency File Number	Ampere Range
	E10480	0.375A - 3.5A
	E10480	4A - 10A
	29862	0.375A - 10A
	225 (Cartridge Version) NBK200405-E10480A NBK200405-E10480C NBK110512-E10480A NBK190619-E10480A	1A 1.5A - 3.5A 4A - 5A 6A - 10A
	224 (Axial Leaded Version) NBK200405-E10480B NBK200405-E10480D NBK110512-E10480B NBK190619-E10480B	1A 1.5A - 3.5A 4A - 5A 6A - 10A
	N/A	0.375A - 10A

Electrical Characteristics for Series

% of Ampere Rating	Opening Time
100%	4 hours, Minimum
135%	1 hour, Maximum
200%	1 sec., Maximum

Electrical Characteristic Specifications by Item

Amp Code	Ampere Rating (A)	Voltage Rating (V)	Interrupting Rating**	Nominal Cold Resistance (Ohms)	Nominal Melting I ² t (A ² sec)	Agency Approvals				
										
.375	0.375	250	35A@250Vac 10KA@125Vac 10KA@125Vdc	0.3950	0.171	x			x	x
.500	0.5	250		0.2650	0.365	x			x	x
.750	0.75	250		0.1520	1.050	x			x	x
001.	1	250	100A@250Vac 10KA@125Vac 10KA@125Vdc	0.1027	2.220	x			x	x
01.5	1.5	250		0.0712	0.800	x			x	x
002.	2	250		0.0497	2.180	x			x	x
02.5	2.5	250		0.0372	3.820	x			x	x
003.	3	250		0.0317	4.620	x			x	x
03.5	3.5	250	100A@250Vac 500A@125Vac	0.0265	6.700	x			x	x
004.	4	125		0.0240	9.400		x		x	x
005.	5	125		0.0186	17.0		x		x	x
005.	5	250		0.0186	17.0		x		x	x
006.	6	125		0.0154	22.1		x		x	x
007.	7	125	500A@125Vac	0.0130	40.0		x		x	x
008.	8	125		0.0107	56.0		x		x	x
010.	10	125		0.0075	116.0		x		x	x
							x		x	x

* 10A with 500A @ 125 Vdc internal breaking capacity testing

** Interrupting Rating may differ based on Agency Approval. See Agency Approval certificate for more details..

Description

The 2AG Fast-Acting Fuses are available in cartridge form or with axial leads. 2AG Fuses provide the same performance characteristics as their 3AG counterpart, while occupying one-third the space. Sleeved fuses are available.

Features

- In accordance with Underwriter's Laboratories Standard UL/CSA/NMX 248-14
- Available in cartridge and axial lead form and
- with various forming dimensions
- RoHS compliant and Lead-free

Applications

Used as supplementary protection in appliance or utilization equipment to provide individual protection for components or internal circuits.

Additional Information



**Resources
224 Series**



**Resources
225 Series**



**Samples
224 Series**




**Samples
225 Series**



**Accessories
224 & 225 Series**


For recommended fuse accessories for this product series, see 'Recommended Accessories' section.

Temperature Re-rating Curve




Note:
Derating depicted in this curve is in addition to the standard derating of 25% for continuous operation.

Average Time Current Curves



Soldering Parameters - Wave Soldering



Recommended Process Parameters:

Wave Parameter	Lead-Free Recommendation
Preheat: (Depends on Flux Activation Temperature)	(Typical Industry Recommendation)
Temperature Minimum:	100°C
Temperature Maximum:	150°C
Preheat Time:	60-180 seconds
Solder Pot Temperature:	260°C Maximum
Solder Dwell Time:	2-5 seconds

Recommended Hand-Solder Parameters:

Solder Iron Temperature: 350°C +/- 5°C
Heating Time: 5 seconds max.


Note: These devices are not recommended for IR or Convection Reflow process.

Product Characteristics


Materials	Body : Glass Cap : Nickel-plated brass Leads: Tin-plated Copper
Terminal Strength	MIL-STD-202, Method 211, Test Condition A
Solderability	MIL-STD-202 Method 208
Product Marking	Cap1 : Brand logo, current and voltage ratings Cap2 : Series and agency approval marks

Operating Temperature:	-55°C to 125°C.
Thermal Shock:	MIL-STD-202, Method 107, Test Condition B (5 Cycles -65°C to +125°C).
Vibration	MIL-STD-202, Method 201
Humidity	MIL-STD-202, Method 103, Test Condition A: High RH (95%) and elevated temp (40°C) for 240 hours
Salt Spray	MIL-STD-202, Method 101, Test Condition B

Dimensions



Part Numbering System



Packaging

Packaging Option	Packaging Specification	Quantity	Quantity & Packaging Code	Taping Width
224 Series				
Bulk	N/A	1000	MX	N/A
Bulk	N/A	100	HX	N/A
Reel and Tape	EIA 296-E	1500	DRT1	T1=53mm (2.087")
225 Series				
Bulk	N/A	1000	MX	N/A
Bulk	N/A	100	HX	N/A

Recommended Accessories

Accessory Type	Series	Description	Max Application Voltage	Max Application Amperage
Holder	245	Panel Mount Shock-Safe Fuseholder	300	10
	150	In-Line Fuseholder	350	10
	286	Panel Mount Flip-Top Shock-Safe Fuseholder	250	10
Block	254	OMNI-BLOCK® Fuse Block	400	10
Clip	111	PC Board Mount Fuse Clip	250	10

Notes:

- Do not use in applications above rating.
- Please refer to fuseholder data sheet for specific re-rating information.
- Please contact factory for applications greater than the max voltage and amperage shown.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Littelfuse:](#)

[0225010.MXUP](#) [0225004.MXUP](#) [0225010.HXUP](#) [0225006.MXUP](#) [0225004.HXUP](#) [0225005.HXUP](#) [0225.375MXP](#)
[022501.5HXP](#) [0225.750MXP](#) [0225006.HXP](#) [0225004.HXP](#) [0225001.MXP](#) [0225005.MXP](#) [0225.125MXP](#)
[0225010.HXP](#) [0225.250HXP](#) [0225001.HXP](#) [0225007.HXP](#) [0225008.HXP](#) [0225.125HXP](#) [022501.5MXP](#)
[0225005.HXP](#) [0225010.MXP](#) [0225002.MXP](#) [0225005.MXUP](#) [0225006.HXUP](#) [0225007.HXUP](#) [0225008.HXUP](#)
[0225.375HXP](#) [0225.100HXP](#) [0225004.MXP](#) [0225.500HXP](#) [0225003.MXP](#) [022502.5MXP](#) [0225.100MXP](#)
[0225002.HXP](#) [0225003.HXP](#) [0225008.MXP](#) [022503.5HXP](#) [0225.750HXP](#) [0225.250MXP](#) [0225007.MXP](#)
[0225006.MXP](#) [022503.5MXP](#) [022502.5HXP](#) [0225.500MXP](#) [0225007.MXUP](#) [0225008.MXUP](#) [0225.750VXP](#)
[022503.5VXP](#) [0225002.VXP](#) [022501.5VXP](#) [0225003.VXP](#) [0225.500VXP](#) [022502.5VXP](#) [0225001.VXP](#)
[0225.375VXP](#) [0225004.VXUP](#) [0225006.VXUP](#) [0225007.VXUP](#) [0225005.VXUP](#) [0225008.VXUP](#) [0225010.VXUP](#)