MM Series Mini Size Precision Snap-acting Switches

Features/Benefits

- Low level and power switching
- Long electrical and mechanical life
- Increased overtravel
- Reliable snap-acting mechanism

Typical Applications

- Limited space constraints
- Communication devices





Specifications

CONTACT RATING: From low level* to 7 AMPS @ 250 V AC. ELECTRICAL LIFE: 100,000 cycles at full rated load. INSULATION RESISTANCE: 1,000 ohm min. DIELECTRIC STRENGTH: 1,000 V RMS min. @ sea level. OPERATING TEMPERATURE: -67 F to 275 F (-55 C to 135 C). OPERATING FORCE: 5 oz. (142 grams) max. at actuator button. MOUNTING: 2-56 screws, torque 2 in/lbs max.

*Low Level=conditions where no arcing occurs during switching, i.e., 0.4 VA max. @ 20 V AC or DC max.

NOTE: Specifications and materials listed above are for switches with standard options. For information on specific and custom switches, consult Customer Service center.

Materials

SWITCH HOUSING: Heat resistant phenolic (UL 94V-0).
ACTUATOR BUTTON: Heat resistant phenolic (UL 94V-0).
SPRING: Beryllium copper CDA alloy C17200.
PIVOT: Brass CDA alloy 260.
MOVABLE CONTACTS: Fine silver for ratings greater than 1 AMP @ 125 V AC. 24K gold for 1 AMP @ 125 V AC or less.

STATIONARY CONTACTS: Fine silver inlay on copper CDA alloy C10200 for ratings greater than 1 AMP @ 125 V AC. 24K gold on copper CDA alloy C10200 for 1 AMP @ 125 V AC or less.


TERMINALS: Copper CDA alloy C18700.

Build-A-Switch

J

Snap-acting

To order, simply select desired option from each category and place in the appropriate box. For additional options not shown in catalog, consult Customer Service Center.




* Only available in Electrical Rating D1 and Actuator P0





www.ckswitches.com

MM Series Mini Size Precision Snap-acting Switches

SWITCH WITH STANDARD OPTIONS







MM	SPDT MOMENTARY

SERIES

MMGGD1P0C

OPERATING FORCE

OPTION CODE	BASIC SWITCH OPERATING FORCE	
GG	5 oz. (142 grams) maximum for basic switch with pin plunger actuator ('P0' actuator option).	

NOTE : Operating force varies with actuator option, see ACTUATOR option section.

ELECTRICAL RATING

		RoHS COMPATIBLE*	c	CONTACT MATERIAL	
OPTION CODE	RoHS COMPLIANT*		MOVABLE CONTACT	STATIONARY CONTACT	ELECTRICAL RATING
D1	Yes	Yes	Fine silver.	Fine silver inlay on copper alloy.	7A 125, 250 VAC; 7A 28 VDC resistance 4A 28 VDC inductive; 2.5A 28 VDC (lamp)
F5	Yes	Yes	24K Gold.	24K Gold on copper alloy.	From low level* to 1 AMP @ 125 V AC, 30 V DC.


Note: See Technical Data section of this catalog for RoHS compliant and compatible definition and specifications.


All models chus with all options.

Consult Customer Service Center for availability and delivery of nonstandard ratings.


 * Low Level=conditions where no arcing occurs during switching, i.e., 0.4 VA max. @ 20 V AC or DC max.


A - B B C + C + FIG. 1 Pin Plunger





Leaf





OPTION CODE	FIG.	DIM. A	DIM. B	DIM. C
P0	1	.19 (4,8)	$\begin{array}{c} .320 \pm .015 \\ (8,13 \pm 0,38) \end{array}$	-
D0	3	.19 (4,8)	$\begin{array}{c} .475 \pm .031 \\ (12,07 \pm 0,79) \end{array}$	-
LO	2	.34 (8,6)	$\begin{array}{c} .330 \pm .015 \\ (8,38 \pm 0,38) \end{array}$	-
L2	5	.53 (13,5)	$\begin{array}{c} .330 \pm .015 \\ (8,38 \pm 0,38) \end{array}$	-
wo	4	.27 (6,9)	$\begin{array}{c} .532 \pm .025 \\ (13,51 \pm 0,64) \end{array}$.188 dia. (4,78Ø)
W2	6	.46 (11,7)	$\begin{array}{c} .532 \pm .025 \\ (13, 51 \pm 0, 64) \end{array}$.188 dia. (4,78Ø)



Dimensions are shown: Inches (mm) Specifications and dimensions subject to change

www.ckswitches.com



MM Series Mini Size Precision Snap-acting Switches

ACTUATOR

SWITCH CHARACTERISTICS

OPTION CODE	MAXIMUM OPERATING FORCE (OZ./GRAMS)	MINIMUM RELEASE FORCE (OZ./GRAMS)	MAXIMUM DIFFERENTIAL TRAVEL	MAXIMUM PRETRAVEL	MINIMUM OVERTRAVEL
D0	5	.7	.004	.030	.040
	142	20	(0,10)	(0,76)	(1,02)
LO	4	.7	.025	.090	.045
	115	20	(0,64)	(2,29)	(1,14)
L2	6	.7	.012	.075	.015
	170	20	(0,30)	(1,90)	(0,38)
P0	5	1	.002	.020	.004
	142	28	(0,05)	(0,51)	(0,10)
W0	4	.7	.025	.090	.045
	115	20	(0,64)	(2,29)	(1,14)
W2	6	.7	.012	.075	.015
	170	20	(0,30)	(1,90)	(0,38)

NOTE : For basic switch operating forces, see page J-44

TERMINATIONS




С



L LEFT FORMED PC THRU-HOLE

R RIGHT FORMED PC THRU-HOLE



PC THRU-HOLE, .035 "

SINGLE TURRET SOLDER


.180 TYP. (4,57)

1

.090 (2,29)

> .063 (1,60)

.187 (4,75)



÷ (+)

ਸ ਸ

Н


.040 DIA. TYP.


.060 DIA. TYP.

(1,02ø)

(1,52ø)

.374 (9,50)





Dimensions are shown: Inch (mm) Specifications and dimensions subject to change

24 Mar 21

www.ckswitches.com

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

C&K Switches:

MMGGD1L2CMMGGD1D0CMMGGD1L0CMMGGD1L0RMMGGD1L2RMMGGD1P0CMMGGF5D0CMMGGF5W0CMMGGF5L0TMMGGF5D0TMMGGD1W2CMMGGF5P0CMMGGF5P0T