

# HiPerFET™

## Power MOSFETs

IXFK100N10  
IXFN150N10


N-Channel Enhancement Mode  
Avalanche Rated, High dv/dt, Low  $t_{rr}$

| $V_{DSS}$ | $I_{D25}$ | $R_{DS(on)}$ |
|-----------|-----------|--------------|
| 100 V     | 100 A     | 12 mΩ        |
| 100 V     | 150 A     | 12 mΩ        |


$$t_{rr} \leq 200 \text{ ns}$$

| Symbol     | Test Conditions                                                                                                                         | Maximum Ratings |          |                  |
|------------|-----------------------------------------------------------------------------------------------------------------------------------------|-----------------|----------|------------------|
|            |                                                                                                                                         | IXFK            | IXFN     |                  |
| $V_{DSS}$  | $T_J = 25^\circ\text{C}$ to $150^\circ\text{C}$                                                                                         | 100             | 100      | V                |
| $V_{DGR}$  | $T_J = 25^\circ\text{C}$ to $150^\circ\text{C}$ ; $R_{GS} = 1 \text{ M}\Omega$                                                          | 100             | 100      | V                |
| $V_{GS}$   | Continuous                                                                                                                              | $\pm 20$        | $\pm 20$ | V                |
| $V_{GSM}$  | Transient                                                                                                                               | $\pm 30$        | $\pm 30$ | V                |
| $I_{D25}$  | $T_C = 25^\circ\text{C}$                                                                                                                | 100 ①           | 150      | A                |
| $I_{D120}$ | $T_C = 120^\circ\text{C}$ , limited by external leads                                                                                   | 76              | -        | A                |
| $I_{DM}$   | $T_C = 25^\circ\text{C}$ , pulse width limited by $T_{JM}$                                                                              | 560             | 560      | A                |
| $I_{AR}$   | $T_C = 25^\circ\text{C}$                                                                                                                | 75              | 75       | A                |
| $E_{AR}$   | $T_C = 25^\circ\text{C}$                                                                                                                | 30              | 30       | mJ               |
| dv/dt      | $I_S \leq I_{DM}$ , $di/dt \leq 100 \text{ A}/\mu\text{s}$ , $V_{DD} \leq V_{DSS}$ ,<br>$T_J \leq 150^\circ\text{C}$ , $R_G = 2 \Omega$ | 5               | 5        | V/ns             |
| $P_D$      | $T_C = 25^\circ\text{C}$                                                                                                                | 500             | 520      | W                |
| $T_J$      |                                                                                                                                         | -55 ... +150    |          | $^\circ\text{C}$ |
| $T_{JM}$   |                                                                                                                                         | 150             |          | $^\circ\text{C}$ |
| $T_{stg}$  |                                                                                                                                         | -55 ... +150    |          | $^\circ\text{C}$ |
| $T_L$      | 1.6 mm (0.063 in) from case for 10 s                                                                                                    | 300             | -        | $^\circ\text{C}$ |
| $V_{ISOL}$ | 50/60 Hz, RMS $t = 1 \text{ min}$                                                                                                       | -               | 2500     | V~               |
|            | $I_{ISOL} \leq 1 \text{ mA}$ $t = 1 \text{ s}$                                                                                          | -               | 3000     | V~               |
| $M_d$      | Mounting torque                                                                                                                         | 0.9/6           | 1.5/13   | Nm/lb.in.        |
|            | Terminal connection torque                                                                                                              | -               | 1.5/13   | Nm/lb.in.        |
| Weight     |                                                                                                                                         | 10              | 30       | g                |

TO-264 AA (IXFK)



miniBLOC, SOT-227 B (IXFN)  
E153432



G = Gate  
S = Source

D = Drain  
TAB = Drain

Either Source terminal at miniBLOC can be used as Main or Kelvin Source

### Features

- International standard packages
- JEDEC TO-264 AA, epoxy meet UL 94 V-0, flammability classification
- miniBLOC with Aluminium nitride isolation
- Low  $R_{DS(on)}$  HDMOS™ process
- Rugged polysilicon gate cell structure
- Unclamped Inductive Switching (UIS) rated
- Low package inductance
- Fast intrinsic Rectifier

### Applications

- DC-DC converters
- Synchronous rectification
- Battery chargers
- Switched-mode and resonant-mode power supplies
- DC choppers
- Temperature and lighting controls
- Low voltage relays

### Advantages


- Easy to mount
- Space savings
- High power density

| Symbol       | Test Conditions                                                                                                   | Characteristic Values<br>( $T_J = 25^\circ\text{C}$ , unless otherwise specified) |      |                      |
|--------------|-------------------------------------------------------------------------------------------------------------------|-----------------------------------------------------------------------------------|------|----------------------|
|              |                                                                                                                   | min.                                                                              | typ. | max.                 |
| $V_{DSS}$    | $V_{GS} = 0 \text{ V}$ , $I_D = 1 \text{ mA}$                                                                     | 100                                                                               |      | V                    |
| $V_{GH(th)}$ | $V_{DS} = V_{GS}$ , $I_D = 8 \text{ mA}$                                                                          | 2                                                                                 |      | V                    |
| $I_{GSS}$    | $V_{GS} = \pm 20 \text{ V}$ , $V_{DS} = 0$                                                                        |                                                                                   |      | $\pm 200 \text{ nA}$ |
| $I_{DSS}$    | $V_{DS} = 0.8 \cdot V_{DSS}$                                                                                      |                                                                                   |      | 400 $\mu\text{A}$    |
|              | $V_{GS} = 0 \text{ V}$                                                                                            |                                                                                   |      | 2 mA                 |
| $R_{DS(on)}$ | $V_{GS} = 10 \text{ V}$ , $I_D = 75 \text{ A}$<br>Pulse test, $t \leq 300 \mu\text{s}$ , duty cycle $d \leq 2 \%$ |                                                                                   |      | 12 mΩ                |

| Symbol       | Test Conditions                                                                                        | Characteristic Values<br>( $T_J = 25^\circ\text{C}$ , unless otherwise specified) |      |      |
|--------------|--------------------------------------------------------------------------------------------------------|-----------------------------------------------------------------------------------|------|------|
|              |                                                                                                        | min.                                                                              | typ. | max. |
| $g_{fs}$     | $V_{DS} = 10\text{ V}; I_D = 50\text{ A}$ , pulse test                                                 |                                                                                   | 80   | S    |
| $C_{iss}$    | $V_{GS} = 0\text{ V}, V_{DS} = 25\text{ V}, f = 1\text{ MHz}$                                          |                                                                                   | 9000 | pF   |
| $C_{oss}$    |                                                                                                        |                                                                                   | 3200 | pF   |
| $C_{rss}$    |                                                                                                        |                                                                                   | 1800 | pF   |
| $t_{d(on)}$  | $V_{GS} = 10\text{ V}, V_{DS} = 0.5 \cdot V_{DSS}, I_D = 75\text{ A}$<br>$R_G = 1\ \Omega$ (External), |                                                                                   | 30   | ns   |
| $t_r$        |                                                                                                        |                                                                                   | 60   | ns   |
| $t_{d(off)}$ |                                                                                                        |                                                                                   | 100  | ns   |
| $t_f$        |                                                                                                        |                                                                                   | 60   | ns   |
| $Q_{g(on)}$  | $V_{GS} = 10\text{ V}, V_{DS} = 0.5 \cdot V_{DSS}, I_D = 75\text{ A}$                                  |                                                                                   | 360  | nC   |
| $Q_{gs}$     |                                                                                                        |                                                                                   | 75   | nC   |
| $Q_{gd}$     |                                                                                                        |                                                                                   | 180  | nC   |
| $R_{thJC}$   | TO-264 AA                                                                                              |                                                                                   | 0.25 | K/W  |
| $R_{thCK}$   | TO-264 AA                                                                                              |                                                                                   | 0.15 | K/W  |
| $R_{thJC}$   | miniBLOC, SOT-227 B                                                                                    |                                                                                   | 0.24 | K/W  |
| $R_{thCK}$   | miniBLOC, SOT-227 B                                                                                    |                                                                                   | 0.05 | K/W  |


| Symbol   | Test Conditions                                                                                                | Characteristic Values<br>( $T_J = 25^\circ\text{C}$ , unless otherwise specified) |      |                |
|----------|----------------------------------------------------------------------------------------------------------------|-----------------------------------------------------------------------------------|------|----------------|
|          |                                                                                                                | min.                                                                              | typ. | max.           |
| $I_S$    | $V_{GS} = 0\text{ V}$                                                                                          | IXFK 100<br>IXFN 150                                                              |      | 100 A<br>150 A |
| $I_{SM}$ | Repetitive;<br>pulse width limited by $T_{JM}$                                                                 | IXFK 100<br>IXFN 150                                                              |      | 400 A<br>600 A |
| $V_{SD}$ | $I_F = 100\text{ A}, V_{GS} = 0\text{ V}$ ,<br>Pulse test, $t \leq 300\ \mu\text{s}$ , duty cycle $d \leq 2\%$ |                                                                                   |      | 1.75 V         |
| $t_{rr}$ | $I_F = 25\text{ A}$<br>$-di/dt = 100\text{ A}/\mu\text{s}$ ,<br>$V_R = 50\text{ V}$                            |                                                                                   | 150  | 200 ns         |
| $Q_{RM}$ |                                                                                                                |                                                                                   | 0.6  | $\mu\text{C}$  |
| $I_{RM}$ |                                                                                                                |                                                                                   | 8    | A              |

### TO-264 AA Outline



| Dim. | Millimeter |       | Inches |       |
|------|------------|-------|--------|-------|
|      | Min.       | Max.  | Min.   | Max.  |
| A    | 4.82       | 5.13  | .190   | .202  |
| A1   | 2.54       | 2.89  | .100   | .114  |
| A2   | 2.00       | 2.10  | .079   | .083  |
| b    | 1.12       | 1.42  | .044   | .056  |
| b1   | 2.39       | 2.69  | .094   | .106  |
| b2   | 2.90       | 3.09  | .114   | .122  |
| c    | 0.53       | 0.83  | .021   | .033  |
| D    | 25.91      | 26.16 | 1.020  | 1.030 |
| E    | 19.81      | 19.96 | .780   | .786  |
| e    | 5.46       | BSC   | .215   | BSC   |
| J    | 0.00       | 0.25  | .000   | .010  |
| K    | 0.00       | 0.25  | .000   | .010  |
| L    | 20.32      | 20.83 | .800   | .820  |
| L1   | 2.29       | 2.59  | .090   | .102  |
| P    | 3.17       | 3.66  | .125   | .144  |
| Q    | 6.07       | 6.27  | .239   | .247  |
| Q1   | 8.38       | 8.69  | .330   | .342  |
| R    | 3.81       | 4.32  | .150   | .170  |
| R1   | 1.78       | 2.29  | .070   | .090  |
| S    | 6.04       | 6.30  | .238   | .248  |
| T    | 1.57       | 1.83  | .062   | .072  |

### miniBLOC, SOT-227 B



M4 screws (4x) supplied

| Dim. | Millimeter |       | Inches |       |
|------|------------|-------|--------|-------|
|      | Min.       | Max.  | Min.   | Max.  |
| A    | 31.50      | 31.88 | 1.240  | 1.255 |
| B    | 7.80       | 8.20  | 0.307  | 0.323 |
| C    | 4.09       | 4.29  | 0.161  | 0.169 |
| D    | 4.09       | 4.29  | 0.161  | 0.169 |
| E    | 4.09       | 4.29  | 0.161  | 0.169 |
| F    | 14.91      | 15.11 | 0.587  | 0.595 |
| G    | 30.12      | 30.30 | 1.186  | 1.193 |
| H    | 38.00      | 38.23 | 1.496  | 1.505 |
| J    | 11.68      | 12.22 | 0.460  | 0.481 |
| K    | 8.92       | 9.60  | 0.351  | 0.378 |
| L    | 0.76       | 0.84  | 0.030  | 0.033 |
| M    | 12.60      | 12.85 | 0.496  | 0.506 |
| N    | 25.15      | 25.42 | 0.990  | 1.001 |
| O    | 1.98       | 2.13  | 0.078  | 0.084 |
| P    | 4.95       | 5.97  | 0.195  | 0.235 |
| Q    | 26.54      | 26.90 | 1.045  | 1.059 |
| R    | 3.94       | 4.42  | 0.155  | 0.174 |
| S    | 4.72       | 4.85  | 0.186  | 0.191 |
| T    | 24.59      | 25.07 | 0.968  | 0.987 |
| U    | -0.05      | 0.1   | -0.002 | 0.004 |

Fig. 1 Output Characteristics




Fig. 2 Input Admittance




Fig. 3  $R_{DS(on)}$  vs. Drain Current




Fig. 4 Temperature Dependence of Drain to Source Resistance




Fig. 5 Drain Current vs. Case Temperature




Fig. 6 Temperature Dependence of Breakdown and Threshold Voltage




Fig.7 Gate Charge Characteristic Curve




Fig.8 Capacitance Curves




Fig.9 Source Current vs. Source to Drain Voltage





Fig.10 Transient Thermal Impedance





---

Disclaimer Notice - Information furnished is believed to be accurate and reliable. However, users should independently evaluate the suitability of and test each product selected for their own applications. Littelfuse products are not designed for, and may not be used in, all applications. Read complete Disclaimer Notice at [www.littelfuse.com/disclaimer-electronics](http://www.littelfuse.com/disclaimer-electronics).

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[IXYS:](#)

[IXFK150N10](#)