

TLN SERIES TELCOM POWER FUSE

170 VDC • Current-Limiting • 1-600 A



Description

The TLN Series fuses are specifically designed for the protection of telecommunications DC power distribution circuits.

Features

- 170 VDC rating
- Fast-acting and current-limiting
- 1 to 600 amperes rating
- Dimensionally similar to 250 V Class R fuses

Dimensions Inches (mm)


Figure 1
FIG. 1

Specifications

Voltage Rating	170 VDC
Interrupting Rating	100 kA
Ampere Range	1 – 600 A
Approvals	UL Recognized (File: E71611)

Ordering Information

AMPERE RATINGS						
1	15	40	80	150	300	600
3	20	45	90	175	350	—
5	25	50	100	200	400	—
6	30	60	110	225	450	—
10	35	70	125	250	500	—

SERIES	VOLTAGE	AMPERAGE	CATALOG NUMBER	ORDERING NUMBER
TLN	170VDC	6	TLN006	OTLN006.T


Replaces competitors' TPN and TGN Series.

Web Resources

For additional information, visit:
Littelfuse.com/tln

Recommended Fuse Holders

LFR25 Series


FIG. 2

AMPERE RATING	DIMENSIONS INCHES (mm)									
	A	B	C	D	E	F	G	H	J	K
1 – 30	2 (50.8)	½ (12.7)	½ (12.7)	⅜ (14.3)	⅝ (2.0)	⅝ (4.0)	⅜ (9.5)	—	—	—
35 – 60	3 (76.2)	¾ (19.1)	⅝ (15.9)	13/16 (20.6)	⅜ (2.4)	⅜ (4.8)	⅝ (15.9)	—	—	—

Figure 2

AMPERE RATING	DIMENSIONS INCHES (mm)									
	A	B	C	D	E	F	G	H	J	K
70 – 100	5⅞ (149.2)	1 (25.4)	1⅞ (27.0)	1⅞ (27.0)	⅞ (3.2)	¾ (19.1)	1¼ (31.6)	¼ (6.4)	⅝ (7.1)	½ (12.7)
110 – 200	7⅞ (181.0)	1½ (38.1)	1⅞ (37.3)	1⅞ (40.5)	⅞ (4.8)	1⅞ (28.6)	1⅞ (46.8)	⅞ (11.1)	⅝ (7.1)	1⅞ (17.5)
225 – 400	8⅞ (219.1)	2 (50.8)	1⅞ (49.2)	2⅞ (53.2)	¾ (6.4)	1⅞ (41.3)	2⅞ (59.5)	⅞ (15.9)	1⅞ (10.3)	1⅞ (23.8)
450 – 600	10⅞ (263.5)	2½ (63.5)	2⅞ (60.3)	2⅞ (65.9)	¾ (6.4)	2 (50.8)	2⅞ (72.2)	¾ (19.1)	1⅞ (13.5)	1⅞ (28.6)

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Littelfuse:

[OTLN250.X](#) [OTLN001.T](#) [OTLN100.V](#) [OTLN080.V](#) [OTLN125.X](#) [OTLN110.X](#) [OTLN045.T](#) [OTLN040.T](#) [OTLN025.T](#)
[OTLN005.T](#) [OTLN015.T](#) [OTLN350.X](#) [OTLN070.V](#) [OTLN500.X](#) [OTLN450.X](#) [OTLN050.T](#) [OTLN200.X](#) [OTLN010.T](#)
[OTLN006.T](#) [OTLN060.T](#) [OTLN600.X](#) [OTLN175.X](#) [OTLN300.X](#) [OTLN150.X](#) [OTLN035.T](#) [OTLN003.T](#) [OTLN090.V](#)
[OTLN020.T](#) [OTLN225.X](#) [OTLN030.T](#) [OTLN400.X](#)