



LED Displays ~ Seven Segment ~ Numeric



Four Digit




Features/Options

- ▶ Standard and high brightness chips
- ▶ Intensity grading available
- ▶ Custom sizes at minimal tooling
- ▶ Face and segment off colors in grey and milky white

Applications/Uses


- ▶ Panel meter displays
- ▶ Time lapsed panels
- ▶ Diagnostic equipment
- ▶ Counter displays

0.22" four digit



Part Number	Wave Length (nm)	Brightness (μcd) @ 10mA	Vf (typ) 10mA	Vf (max) 10mA	Emitted Color	Polarity (column)
LDQ-M2212RI	565	2500	2.2	2.6	Green	Anode
LDQ-M2214RI	635	2500	2.0	2.5	Red	Anode
LDQ-M2216RI	660	8000	1.7	2.2	Red	Anode
LDQ-M2212RI-SUG	574	7000	2.2	2.6	Green	Anode
LDQ-M2214RI-SI	636	15,000	2.0	2.6	Red	Anode
LDQ-M2217RI-USB	470	6000	3.5	4.0	Blue	Anode
LDQ-N2212RI	565	2500	2.2	2.6	Green	Cathode
LDQ-N2214RI	635	2500	2.0	2.5	Red	Cathode
LDQ-N2216RI	660	8000	1.7	2.2	Red	Cathode
LDQ-N2212RI-SUG	574	7000	2.2	2.6	Green	Cathode
LDQ-N2214RI-SI	636	15,000	2.0	2.6	Red	Cathode
LDQ-N2217RI-USB	470	6000	3.5	4.0	Blue	Cathode

0.28" four digit



Part Number	Wave Length (nm)	Brightness (μcd) @ 10mA	Vf (typ) 10mA	Vf (max) 10mA	Emitted Color	Polarity (common)
LDQ-M282RI	565	2500	2.2	2.6	Green	Anode
LDQ-M284RI	635	2500	2.0	2.5	Red	Anode
LDQ-M286RI	660	8000	1.7	2.2	Red	Anode
LDQ-M282RI-SUG	574	7000	2.2	2.6	Green	Anode
LDQ-M284RI-SI	636	15,000	2.0	2.6	Red	Anode
LDQ-M287RI-USB	470	6000	3.5	4.0	Blue	Anode
LDQ-N282RI	565	2500	2.2	2.6	Green	Cathode
LDQ-N284RI	635	2500	2.0	2.5	Red	Cathode
LDQ-N286RI	660	8000	1.7	2.2	Red	Cathode
LDQ-N282RI-SUG	574	7000	2.2	2.6	Green	Cathode
LDQ-N284RI-SI	636	15,000	2.0	2.6	Red	Cathode
LDQ-N287RI-USB	470	6000	3.5	4.0	Blue	Cathode



USA/Canada +1-800-278-5666
Europe +49-6081-964380
Asia +886-3-5821124



www.lumex.com



USA/Canada +1-847-359-8904
Europe +49-6081-964381
Asia +886-3-5821154

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Lumex:

[LDQ-M286RI](#) [LDQ-N284RI](#) [LDQ-N286RI](#)