

# AK1 Series

## Axial Leaded – 1kA



### Additional Information



Resources



Accessories



Samples

### Maximum Ratings and Thermal Characteristics

( $T_A = 25^\circ\text{C}$  unless otherwise noted)

Parameter	Symbol	Value	Unit
Operating Storage Temperature Range	$T_{STG}$	-55 to 150	$^\circ\text{C}$
Operating Junction Temperature Range	$T_J$	-55 to 125	$^\circ\text{C}$
Current Rating <sup>1</sup>	$I_{PP}$	1	kA

**Note:**

1. Rated  $I_{PP}$  measured with 8/20 $\mu\text{s}$  pulse.

### Description

The AK1 series of high power TVS diode is specially designed for meeting severe surge test environment of both AC and DC line protection applications. It features a very fast response and ultra low clamping characteristics over traditional metal oxide varistor (MOV) solutions. They can be connected in series and / or parallel to create a very high surge current protection solution.


### Features

- Very low clamping voltage
- Ultra compact: less than one-tenth the size of traditional discrete solutions
- Sharp breakdown voltage
- Low slope resistance
- Bi-directional
- IEC 61000-4-2 ESD 15kV(Air), 8kV (Contact)
- Symmetric in leads width for easier soldering during assembly.
- ESD protection of data lines in accordance with IEC 61000-4-2
- EFT protection of data lines in accordance with IEC 61000-4-4
- Halogen-free
- RoHS compliant
- Glass passivated junction
- Pb-free E4 means 2nd level interconnect is Pb-free and the terminal finish material is Silver

### Agency Approvals

Agency	Agency File/Certificate Number
	E128662

### Functional Diagram



### Electrical Characteristics ( $T_A = 25^\circ\text{C}$ unless otherwise noted)

Part Numbers	Part Marking	Standoff Voltage ( $V_{SO}$ ) Volts	Max. Reverse Leakage ( $I_R$ ) @ $V_{SO}$ $\mu\text{A}$	Typical $I_R$ @ $85^\circ\text{C}$ ( $\mu\text{A}$ )	Reverse Breakdown Voltage ( $V_{BR}$ ) @ $I_T$		Test Current $I_T$ (mA)	Max. Clamping Voltage $V_{CL}$ @ $I_{PP}$ Peak Pulse Current ( $I_{PP}$ ) (Note 1)		Max. Temp Coefficient OF $V_{BR}$ (%/ $^\circ\text{C}$ )	Max. Capacitance 0 Bias 10kHz (nF)	Agency Approval
					Min Volts	Max Volts		$V_{CL}$ Volts	$I_{PP}$ Amps			
AK1 - 076C	1-076C	76	10	15	85	95	10	140	1,000	0.1	8.5	X

**Note:** Using 8/20 $\mu\text{s}$  wave shape as defined in IEC 61000-4-5.

# AK1 Series

## Axial Leaded – 1kA

### Physical Specifications


<b>Weight</b>	Contact manufacturer
<b>Case</b>	Epoxy encapsulated
<b>Terminal</b>	Silver plated leads, solderable per MIL-STD-750 Method 2026

### Flow/Wave Soldering (Solder Dipping)


<b>Peak Temperature :</b>	265°C
<b>Dipping Time :</b>	10 seconds
<b>Soldering :</b>	1 time

### Wave Solder Profile

**Figure 1 -**  
Non Lead-free Profile




**Figure 2 -**  
Lead-free Profile




### Ratings and Characteristic Curves ( $T_A=25^\circ\text{C}$ unless otherwise noted)

**Figure 3 -**  
Peak Power Derating



**Figure 4 -**  
Typical Peak Pulse Power Rating Curve




continues on next page.

# AK1 Series


## Axial Leaded – 1kA

### Ratings and Characteristic Curves ( $T_A=25^\circ\text{C}$ unless otherwise noted) (Continued)


**Figure 5 -**  
Typical  $V_{BR}$  Vs Junction Temperature



**Figure 6 -**  
Pulse Waveform




### Dimensions




Dimensions	Inches	Millimeters
<b>A</b>	0.950 +/- 0.040	24.15 +/- 1.00
<b>B</b>	0.095 +/- 0.024	2.4 +/- 0.60
<b>C</b>	0.236 +/- 0.039	6.00 +/- 1.00
<b>D</b>	0.570 max.	14.48 max.
<b>E</b>	0.050 +/- 0.002	1.270 +/- 0.05
<b>F</b>	0.500 max.	12.70 max.
<b>G</b>	0.096 +/- 0.040	2.44 +/- 1.00
<b>L1/L2</b>	L1= L2 tolerance +/- 0.04 inch (1.0 mm)	

### Part Marking System



Side View

### Part Numbering System



### Packing Options

Part Number	Component Package	Quantity	Packaging Option
AK1-XXXX	AK Package	56pcs/Box	Bulk
AK1-XXXX-12	AK Package	12pcs/Box	Bulk

**Disclaimer Notice** - Information furnished is believed to be accurate and reliable. However, users should independently evaluate the suitability of and test each product selected for their own applications. Littelfuse products are not designed for, and may not be used in, all applications. Read complete Disclaimer Notice at [www.littelfuse.com/disclaimer-electronics](http://www.littelfuse.com/disclaimer-electronics).

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Littelfuse:](#)

[AK1-430C](#)