SMCG-HR Series





Agency Approvals

Agency	Agency File Number
71 2	E230531

Maximum Ratings and Thermal Characteristics $(T_{\Delta}=25^{\circ}\text{C unless otherwise noted})$

Parameter	Symbol	Value	Unit
Peak Pulse Power Dissipation by 10/1000µs waveform (Fig.2)(Note 1), (Note 2)	P _{PPM}	1500	W
Power Dissipation on infinite heat sink at $T_A = 50^{\circ}C$	P _{M(AV)}	6.5	W
Peak Forward Surge Current, 8.3ms Single Half Sine Wave (Note 3)	I _{FSM}	200	А
Maximum Instantaneous Forward Voltage at 100A for Unidirectional only	V _F	3.5	V
Operating Junction and Storage Temperature Range	T _J , T _{STG}	-65 to 150	°C
Typical Thermal Resistance Junction to Lead	R _{eyl}	15	°C/W
Typical Thermal Resistance Junction to Ambient	R _{eJA}	75	°C/W

Notes

- Non-repetitive current pulse per Fig. 4 and derated above T_A = 25°C per Fig. 3.
- 2. Mounted on copper pad area of 0.31x0.31" (8.0 x 8.0mm) to each terminal.
- Measured on 8.3ms single half sine wave or equivalent square wave for unidirectional device only, duty cycle=4 per minute maximum.

Description


The SMCG-HR series is designed specifically to protect sensitive electronic equipment from voltage transients induced by lightning and other transient voltage events.

Features

- High-Reliability upscreened for critical applications require higher reliability performance and low infant mortality failures.
- Excellent clamping capability
- Low incremental surge resistance
- Typical I_R less than 1μA above 12V
- For surface mounted applications to optimize board space
- L bend lead forming gives best solderbility for Hi reliability application
- Typical failure mode is short from over-specified voltage or current
- Whisker test is conducted based on JEDEC JESD201A per its table 4a and 4c
- IEC-61000-4-2 ESD 30kV(Air), 30kV (Contact)
- ESD protection of data lines in accordance with IEC 61000-4-2
- EFT protection of data lines in accordance with IEC 61000-4-4

- Built-in strain relief
- Fast response time: typically less than 1.0ps from 0V to VB_R min
- 1500W peak pulse power capability at 10/1000µs waveform, repetition rate (duty cycles):0.01%
- V_{BR} @T_J = V_{BR}@25°C x (1+ aT x (T_J 25)) (aT:Temperature Coefficient, typical value is 0.1%)
- Glass passivated chip junction
- High temperature soldering guaranteed: 260°C/10 seconds at terminals
- Meet MSL level1, per J-STD-020, high temperature soldering guaranteed.
- Matte tin lead-free plated
- Halogen free
- RoHS compliant with exemption 7a and 7c-l
- Pb-free E3 means 2nd level interconnect is Pbfree and the terminal finish material is tin(Sn) (IPC/ JEDEC J-STD-609A.01)

Functional Diagram



Applications

TVS Components are ideal for the protection of I/O Interfaces, $V_{\rm cc}$ bus and other vulnerable circuits used in Telecom, Computer, Industrial and Consumer electronic applications.



Electrical Characteristics

Part Number (Uni)	Part Number (Bi)	Mar	king	Reverse Stand off Voltage V _R	Volta	kdown nge V _{BR} rs) @ I _T	Test Current I _T	Maximum Clamping Voltage V _c @ I	Maximum Peak Pulse Current	Maximum Reverse Leakage I _R @ V _R	Agency Approval
(3,	(=,,	UNI	ВІ	(Volts)	MIN	MAX	(mA)	(V) ^{pp}	I _{pp} (A)	(μA)	
SMCG5.0A-HR	SMCG5.0CA-HR	GDE	BDE	5.0	6.40	7.00	10	9.2	163.0	800	X
SMCG6.0A-HR	SMCG6.0CA-HR	GDG	BDG	6.0	6.67	7.37	10	10.3	145.7	800	Х
SMCG6.5A-HR	SMCG6.5CA-HR	GDK	BDK	6.5	7.22	7.98	10	11.2	134.0	500	X
SMCG7.0A-HR	SMCG7.0CA-HR	GDM	BDM	7.0	7.78	8.60	10	12.0	125.0	200	X
SMCG7.5A-HR	SMCG7.5CA-HR	GDP	BDP	7.5	8.33	9.21	1	12.9	116.3	100	X
SMCG8.0A-HR	SMCG8.0CA-HR	GDR	BDR	8.0	8.89	9.83	1	13.6	110.3	50	X
SMCG8.5A-HR	SMCG8.5CA-HR	GDT	BDT	8.5	9.44	10.40	1	14.4	104.2	20	X
SMCG9.0A-HR	SMCG9.0CA-HR	GDV	BDV	9.0	10.00	11.10	1	15.4	97.4	10	X
SMCG10A-HR	SMCG10CA-HR	GDX	BDX	10.0	11.10	12.30	1	17.0	88.3	5	X
SMCG11A-HR	SMCG11CA-HR	GDZ	BDZ	11.0	12.20	13.50	1	18.2	82.5	1	X
SMCG12A-HR	SMCG12CA-HR	GEE	BEE	12.0	13.30	14.70	1	19.9	75.4	1	X
SMCG13A-HR	SMCG13CA-HR	GEG	BEG	13.0	14.40	15.90	1	21.5	69.8	1	X
SMCG14A-HR	SMCG14CA-HR	GEK	BEK	14.0	15.60	17.20	1	23.2	64.7	1	X
SMCG15A-HR	SMCG15CA-HR	GEM	BEM	15.0	16.70	18.50	1	24.4	61.5	1	X
SMCG16A-HR	SMCG16CA-HR	GEP	BEP	16.0	17.80	19.70	1	26.0	57.7	1	X
SMCG17A-HR	SMCG17CA-HR	GER	BER	17.0	18.90	20.90	1	27.6	54.4	1	X
SMCG18A-HR	SMCG18CA-HR	GET	BET	18.0	20.00	22.10	1	29.2	51.4	1	X
SMCG20A-HR	SMCG20CA-HR	GEV	BEV	20.0	22.20	24.50	1	32.4	46.3	1	X
SMCG22A-HR	SMCG22CA-HR	GEX	BEX	22.0	24.40	26.90	1	35.5	42.3	1	X
SMCG24A-HR	SMCG24CA-HR	GEZ GFE	BEZ BFE	24.0	26.70	29.50	1	38.9 42.1	38.6	1	X
SMCG26A-HR SMCG28A-HR	SMCG26CA-HR SMCG28CA-HR	GFG	BFG	26.0	28.90	31.90	1	45.4	35.7	1	X
SMCG30A-HR	SMCG30CA-HR	GFK	BFK	28.0	31.10	34.40 36.80	1	45.4	33.1	1	X
SMCG33A-HR	SMCG33CA-HR	GFM	BFM	30.0	36.70	40.60	1	53.3	31.0 28.2	1	X
SMCG36A-HR	SMCG36CA-HR	GFP	BFP	36.0	40.00	44.20	1	58.1	25.9	1	X
SMCG40A-HR	SMCG40CA-HR	GFR	BFR	40.0	44.40	49.10	1	64.5	23.3	1	X
SMCG43A-HR	SMCG43CA-HR	GFT	BFT	43.0	47.80	52.80	1	69.4	21.7	1	X
SMCG45A-HR	SMCG45CA-HR	GFV	BFV	45.0	50.00	55.30	1	72.7	20.6	1	X
SMCG48A-HR	SMCG48CA-HR	GFX	BFX	48.0	53.30	58.90	1	77.4	19.4	1	X
SMCG51A-HR	SMCG51CA-HR	GFZ	BFZ	51.0	56.70	62.70	1	82.4	18.2	1	X
SMCG54A-HR	SMCG54CA-HR	GGE	BGE	54.0	60.00	66.30	1	87.1	17.3	1	X
SMCG58A-HR	SMCG58CA-HR	GGG	BGG	58.0	64.40	71.20	1	93.6	16.1	1	X
SMCG60A-HR	SMCG60CA-HR	GGK	BGK	60.0	66.70	73.70	1	96.8	15.5	1	X
SMCG64A-HR	SMCG64CA-HR	GGM	BGM	64.0	71.10	78.60	1	103.0	14.6	1	X
SMCG70A-HR	SMCG70CA-HR	GGP	BGP	70.0	77.80	86.00	1	113.0	13.3	1	Х
SMCG75A-HR	SMCG75CA-HR	GGR	BGR	75.0	83.30	92.10	1	121.0	12.4	1	Х
SMCG78A-HR	SMCG78CA-HR	GGT	BGT	78.0	86.70	95.80	1	126.0	11.9	1	Х
SMCG85A-HR	SMCG85CA-HR	GGV	BGV	85.0	94.40	104.00	1	137.0	11.0	1	Х
SMCG90A-HR	SMCG90CA-HR	GGX	BGX	90.0	100.00	111.00	1	146.0	10.3	1	Х
SMCG100A-HR	SMCG100CA-HR	GGZ	BGZ	100.0	111.00	123.00	1	162.0	9.3	1	Х
SMCG110A-HR	SMCG110CA-HR	GHE	BHE	110.0	122.00	135.00	1	177.0	8.5	1	Х
SMCG120A-HR	SMCG120CA-HR	GHG	BHG	120.0	133.00	147.00	1	193.0	7.8	1	X


Screen Process	
100% vision inspection	MIL-STD-750 method 2074
100%High Temperature Storage Life (168hrs,175C°)	MIL-STD-750 method 1031
100% X-RAY inspection	MIL-STD-750 method 2076
100% Temperature cycle test (-55-150C°, 20 cycles, dwell time 15 min)	MIL-STD-750 method 1051
100% Reflow (2x)	JEDEC J-STD-020
100% surge test (2x)	MIL-STD-750 method 4066
100% HTRB(150C°, Bias=V _R (80% breakdown voltage), 96hrs),for Bi-direction products, 96hrs for each direction	MIL-STD-750 method 1038
Final electrical test(100% 3 sigma limit, 100% dynamic test and PAT limit)	MIL-STD-750 method 4016.4021.4011


Note: Up-screen program can be specified by customer's request via contacting Littelfuse service

Group B Test Requirement

Screen	Method	Condition	Requirement
Surge Test	10/1000 µS Peak Pulse Waveform	Maximum Clamping Voltage (V _C) @ Peak Pulse Current (I _{PP})	Sample Size 45 Perform 10x Accept 0 Failures
Burn - In (HTRB)	MIL - STD - 750, Method 1038.5	Applied Voltage 100% V _R @150°C	Sample Size 45 For Unidirectional, 150C°/V _R /340hours, for Bidirectional, 150C°/V _R /680hrs(340hours for each direction) Accept 0 Failures
Electrical Tests	-	I _R @V _R , V(_{BR})@I _T	Sample Size 45 Accept 0 Failures

I-V Curve Characteristics





- P_{PPM} Peak Pulse Power Dissipation -- Max power dissipation
- **Stand-off Voltage** -- Maximum voltage that can be applied to the TVS without operation
- Breakdown Voltage Maximum voltagethat flows though the TVS at a specified test current (IT)
 Clamping Voltage Peak voltage measured across the TVS at a specified lppm (peak impulse current)
- Reverse Leakage Current Current measured at V_R
 Forward Voltage Drop for Uni-directional



Ratings and Characteristic Curves (T_A=25°C unless otherwise noted)

Figure 1 - TVS Transients Clamping Waveform




Figure 2 - Peak Pulse Power Rating




Figure 3 - Peak Pulse Power Derating Curve




Figure 4 - Pulse Waveform




Figure 5 - Typical Junction Capacitance




Figure 6 - Typical Transient Thermal Impedance








Figure 7 - Maximum Non-Repetitive Peak Forward Surge Current Uni-Directional Only



Soldering Parameters

Reflow Cond	Lead-free assembly		
	-Temperature Min (T _{s(min)})	150°C	
Pre Heat	-Temperature Max (T _{s(max)})	200°C	
	-Time (min to max) (t _s)	60 – 120 secs	
Average ram	np up rate (Liquidus Temp (T_L) to peak	3°C/second max	
T _{S(max)} to T _L -	3°C/second max		
Reflow	-Temperature (T _L) (Liquidus)	217°C	
nellow	-Time (min to max) (t _s)	60 – 150 seconds	
Peak Temper	rature (T _P)	260 ^{+0/-5} °C	
Time within	5°C of actual peak Temperature (t_p)	30 seconds	
Ramp-down	6°C/second max		
Time 25°C to	8 minutes Max.		
Do not exce	ed	260°C	




Physical Specifications

Weight	0.007 ounce, 0.21 grams
Case	JEDEC DO-215AB. Molded plastic body over glass passivated junction
Polarity	Color band denotes positive end (cathode) except Bidirectional.
Terminal	Matte Tin-plated leads, Solderable per JESD22-B102

Environmental Specifications


High Temp. Storage	JESD22-A103
HTRB	JESD22-A108
Thermal Shock	JESD22-A106
MSL	JEDEC-J-STD-020, Level 1
H3TRB	JESD22-A101
RSH	JESD22-A111

Dimensions




	Inc	hes	Millimeters		
Dimensions	Min	Max	Min	Max	
Α	0.115	0.125	2.920	3.170	
В	0.260	0.280	6.600	7.110	
С	0.220	0.245	5.590	6.220	
D	0.075	0.095	1.900	2.410	
E	0.038	0.058	0.970	1.470	
F	-	0.020	-	0.510	
G	0.380	0.400	9.640	10.160	
Н	0.024	0.040	0.610	1.020	
I	0.006	0.016	0.150	0.410	
J	-	0.050	-	1.270	
K	-	0.310	-	7.870	
L	-	0.050	-	1.270	
М	-	0.125	-	3.170	
N	0.002	0.008	0.050	0.200	

Part Numbering System




Part Marking System




Packaging

Part number	Component Package	Quantity	Packaging Option	Packaging Specification
SMCGxxxXX-HR	DO-215AB	1500	Tape & Reel – 24mm tape /13" reel	EIA STD RS-481

Tape and Reel Specification





Disclaimer Notice - Information furnished is believed to be accurate and reliable. However, users should independently evaluate the suitability of and test each product selected for their own applications. Littelfuse products are not designed for, and may not be used in, all applications. Read complete Disclaimer Notice at https://www.littelfuse.com/disclaimer-electronics.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Littelfuse:

SMCG5.0A-HRA SMCG5.0CA-HRA SMCG6.0A-HRA SMCG6.0CA-HRA SMCG6.5A-HRA SMCG6.5CA-HRA SMCG7.0A-HRA SMCG7.0CA-HRA SMCG7.5A-HRA SMCG7.5CA-HRA SMCG8.0A-HRA SMCG8.0CA-HRA SMCG8.5A-HRA SMCG8.5CA-HRA SMCG9.0A-HRA SMCG9.0CA-HRA SMCG10A-HRA SMCG10CA-HRA SMCG11A-HRA SMCG11CA-HRA SMCG12A-HRA SMCG12CA-HRA SMCG13A-HRA SMCG13CA-HRA SMCG14A-HRA SMCG14CA-HRA SMCG15A-HRA SMCG15CA-HRA SMCG16A-HRA SMCG16CA-HRA SMCG17A-HRA SMCG17CA-HRA SMCG18A-HRA SMCG18CA-HRA SMCG20A-HRA SMCG20CA-HRA SMCG22A-HRA SMCG22CA-HRA SMCG24A-HRA SMCG24CA-HRA SMCG26A-HRA SMCG26CA-HRA SMCG28A-HRA SMCG28CA-HRA SMCG30A-HRA SMCG30CA-HRA SMCG33A-HRA SMCG33CA-HRA SMCG36A-HRA SMCG36CA-HRA SMCG40A-HRA SMCG40CA-HRA SMCG43A-HRA SMCG43CA-HRA SMCG45A-HRA SMCG45CA-HRA SMCG48A-HRA SMCG48CA-HRA SMCG51A-HRA SMCG51CA-HRA SMCG54A-HRA SMCG54CA-HRA SMCG58A-HRA SMCG58CA-HRA SMCG60A-HRA SMCG60CA-HRA SMCG64A-HRA SMCG64CA-HRA SMCG70A-HRA SMCG70CA-HRA SMCG75A-HRA SMCG75CA-HRA SMCG78A-HRA SMCG78CA-HRA SMCG85A-HRA SMCG85CA-HRA SMCG90A-HRA SMCG90CA-HRA SMCG100A-HRA SMCG100CA-HRA SMCG110A-HRA SMCG110CA-HRA SMCG120A-HRA SMCG120CA-HRA SMCGA-HR SMCGCA-HR SMCG10A-HR SMCG110A-HR SMCG51CA-HR SMCG17CA-HR SMCG36A-HR SMCG100CA-HR SMCG58A-HR SMCG7.0A-HR SMCG60CA-HR SMCG12A-HR SMCG16A-HR SMCG30A-HR SMCG43CA-HR SMCG5.0A-HR